

CAT. NO. & DIMENSIONS

NOTE3	NO. OF CONTACTS (n)	CAT. NO.	DIMENSIONS (NOTE2)		
			A ±0.2	B ±0.2	C ±0.2
	4	SFW4S-2ST__LF	10.4	5.24	3
	5	SFW5S-2ST__LF	11.4	6.24	4
	6	SFW6S-2ST__LF	12.4	7.24	5
*	7	SFW7S-2ST__LF	13.4	8.24	6
	8	SFW8S-2ST__LF	14.4	9.24	7
*	9	SFW9S-2ST__LF	15.4	10.24	8
	10	SFW10S-2ST__LF	16.4	11.24	9
	11	SFW11S-2ST__LF	17.4	12.24	10
*	12	SFW12S-2ST__LF	18.4	13.24	11
	13	SFW13S-2ST__LF	19.4	14.24	12
	14	SFW14S-2ST__LF	20.4	15.24	13
	15	SFW15S-2ST__LF	21.4	16.24	14
	16	SFW16S-2ST__LF	22.4	17.24	15
	17	SFW17S-2ST__LF	23.4	18.24	16
*	18	SFW18S-2ST__LF	24.4	19.24	17
*	19	SFW19S-2ST__LF	25.4	20.24	18
	20	SFW20S-2ST__LF	26.4	21.24	19
*	21	SFW21S-2ST__LF	27.4	22.24	20
	22	SFW22S-2ST__LF	28.4	23.24	21
	23	SFW23S-2ST__LF	29.4	24.24	22
	24	SFW24S-2ST__LF	30.4	25.24	23
*	25	SFW25S-2ST__LF	31.4	26.24	24
	26	SFW26S-2ST__LF	32.4	27.24	25
*	27	SFW27S-2ST__LF	33.4	28.24	26
	28	SFW28S-2ST__LF	34.4	29.24	27
	29	SFW29S-2ST__LF	35.4	30.24	28
	30	SFW30S-2ST__LF	36.4	31.24	29
*	31	SFW31S-2ST__LF	37.4	32.24	30
*	32	SFW32S-2ST__LF	38.4	33.24	31

CAT. NO. SFW (n) S - 2 ST__ LF

SERIES

NO. OF CONTACTS

STRAIGHT TYPE

FOR FPC / FFC

VARIATION

STM : FOR AUTOMATIC MOUNTING (SMT)
WITH MOUNTING PLATE

ST : FOR AUTOMATIC MOUNTING (SMT)
WITHOUT MOUNTING PLATE

PACKAGE STYLE




LEAD FREE

NOTES

- THIS PRODUCT IS THE CONNECTOR, DESIGNED TO TERMINATE FPC/FFC AND COPER WITH AUTOMATIC MOUNTING (SMT).
- SEE PART DRAWINGS FOR DIMENSIONS A.B.C.
- PLEASE CONSULT US IN CASE OF USING PARTS WITH * MARK

mat'l. code				surface 58 / tolerance ISO 1302 ✓ ISO 406 ISO 1101		projection		product family 58SF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title CAT. NO. TABLE FOR 1mm SPACING SMT CONNECTOR (CAT.No.SFW__S-2ST__LF)			
A	J05-0377	H.T	2005-6-22	angles	linear						
B	J05-0547	H.T	2005-8-30			scale X		dwg no sheet 1 of 1 size JSA 96516 A4			
C	J06-0430	H.T	2006-10-19								
D	J07-0407	H.T	2007-8-9	dr	engr	FCI		type Product Customer Drawing			
				chr	appd						
sheet index	revision	D	1								Rev. D

SC-SFWS 03 JSA96517 96518 96519 96520 93340 93341
form: A4




PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	GLASS FILLED THERMOPLASTIC RATED. (UL94V-0)	1	COLOR : BROWN
2	SLIDER		1	COLOR : BLACK
3	CONTACT	PHOSPHOR BRONZE	n	PLATING : TIN Ni UNDER PLATED(LEAD FREE)

n : NO. OF CONTACTS

NOTES


1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
2. FLATNESS OF CONTACT TERMINAL MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING.
3. THIS DIMENSION IS SPACE FOR THE NOZZLE OF MOUNTER.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN.

RECOMMENDED PC BOARD LAYOUT (COMPONENT SIDE)



mat'l. code				surface 58	tolerance	projection	product family	58SF	CODE	JP
				ISO 1302	ISO 406	mm	title			1mm SPACING SURFACE MOUNT FPC/FFC CONNECTOR (CAT.No.SFW__S-2ST__LF)
				tolerances unless otherwise specified	ISO 1101					
ltr	ecn no	dr	date	angles	linear	scale	dwg no			sheet 1 of 1
A	J05-0377	H.T	6/22/05							
B	J05-0731	H.T	10/28/05			X	JSA 96517			A4
C	J06-0430	H.T	10/19/06							
				dr	10/19/06	FCI	type			Product Customer Drawing
				enr	10/19/06					
				chr	10/19/06					
				appd	10/19/06					
sheet index	revision	C								Rev
	sheet	1								C

SC-SFWS 03 JSA96516
form: A4



NOTES

1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND COPES WITH AUTOMATIC MOUNTING (SMT).
2. FLATNESS OF CONTACT TERMINAL AND MOUNTING PLATE MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING.
3. THIS DIMENSION IS SPACE FOR THE NOZZLE OF MOUNTER.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN.

CONNECTOR OUTLINE

1x(n+1)±0.05

1±0.05

0.6^{+0.2}_{-0.03}

0.95 REF.

1.85±0.05

3.85±0.05

5.5±0.05

BASIC PATTERN

NO.1 CONTACT POSITION

1±0.05

2±0.05

0.6^{+0.2}_{-0.03}

1x(n-1)±0.05

PATTERN FOR MOUNTING PLATE FIXING

[illegible]

CAT. NO. & DIMENSIONS

(NOTE4)	NO. OF CONTACTS (n)	CAT. NO. (NOTE2)	DIMENSIONS (NOTE3)		
			D MAX.	E ± 0.3	F ± 0.1
	4	SFW4S-2ST_E9LF	30.4	24	—
	5	SFW5S-2ST_E9LF	30.4	24	—
	6	SFW6S-2ST_E9LF	30.4	24	—
*	7	SFW7S-2ST_E9LF	30.4	24	—
	8	SFW8S-2ST_E9LF	30.4	24	—
*	9	SFW9S-2ST_E9LF	30.4	24	—
	10	SFW10S-2ST_E9LF	30.4	24	—
	11	SFW11S-2ST_E9LF	30.4	24	—
*	12	SFW12S-2ST_E9LF	38.4	32	28.4
	13	SFW13S-2ST_E9LF	38.4	32	28.4
	14	SFW14S-2ST_E9LF	38.4	32	28.4
	15	SFW15S-2ST_E9LF	38.4	32	28.4
	16	SFW16S-2ST_E9LF	50.4	44	40.4
	17	SFW17S-2ST_E9LF	50.4	44	40.4
*	18	SFW18S-2ST_E9LF	50.4	44	40.4
*	19	SFW19S-2ST_E9LF	50.4	44	40.4
	20	SFW20S-2ST_E9LF	50.4	44	40.4
*	21	SFW21S-2ST_E9LF	50.4	44	40.4
	22	SFW22S-2ST_E9LF	50.4	44	40.4
	23	SFW23S-2ST_E9LF	50.4	44	40.4
	24	SFW24S-2ST_E9LF	50.4	44	40.4
*	25	SFW25S-2ST_E9LF	50.4	44	40.4
	26	SFW26S-2ST_E9LF	50.4	44	40.4
*	27	SFW27S-2ST_E9LF	62.4	56	52.4
	28	SFW28S-2ST_E9LF	62.4	56	52.4
	29	SFW29S-2ST_E9LF	62.4	56	52.4
	30	SFW30S-2ST_E9LF	62.4	56	52.4
*	31	SFW31S-2ST_E9LF	62.4	56	52.4
*	32	SFW32S-2ST_E9LF	62.4	56	52.4

CAT. NO. SFW (n) S - 2 ST_ _ _ LF

SERIES

NO. OF CONTACTS

STRAIGHT TYPE

FOR FPC / FFC

VARIATION

STM:FOR AUTOMATIC MOUNTING (SMT)
WITH MOUNTING PLATEST:FOR AUTOMATIC MOUNTING (SMT)
WITHOUT MOUNTING PLATE


PACKAGE STYLE

LEAD FREE


NOTES

1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND COTES WITH AUTOMATIC MOUNTING (SMT).
2. THIS CATALOG NO. INDICATES PLASTIC TAPE PACKAGED CONNECTOR.
3. SEE PART DRAWINGS FOR DIMENSIONS D~F.
4. PLEASE CONSULT US IN CASE OF USING PARTS WITH * MARK.


mat'l. code				surface 58/ tolerance ISO 1302 406 ISO 1101		projection		product family 58SF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title CAT NO. TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONN. (CAT.No.SFW__S-2ST_E9LF)			
A	J09-0202	M.Y	2009-5-25	angles	linear						
				dr	H.YAMASHITA	2009-5-25	FCI		dwg no sheet 1 of 1 size JSA 97526 A4		
				engr	H.YAMASHITA	2009-5-25					
				chr	S. Nishida	2009-5-25					
				appd	S. Nishida	2009-5-25					
sheet index		revision sheet		A 1						Rev. A	



DRAWING DIRECTION



CONNECTOR PACKAGING STYLE



PT. NO.	PARTS NAME	CAT. NO.	MATERIAL	Q'TY	NOTE
1	REEL	—	POLYSTYRENE	1	COLOR : WHITE or BLACK
2	PLASTIC (EMBOSSED) TAPE	—	PET	—	COLOR : TRANSPARENCY
3	COVER	—	POLYESTER	—	COLOR : TRANSPARENCY
4	CONNECTOR	SFW__S-2ST_LF	SEE ATTACHED DWG.	500	—

NOTES


- THIS IS PLASTIC TAPE PACKAGED CONNECTOR USED FOR FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
- SEE JIS C 0806 (PACKING OF ELECTRONIC COMPONENTS ON CONTINUOUS TAPES (SURFACE MOUNTING DEVICES)) FOR SHAPE AND DIMENSIONS OF PLASTIC (EMBOSSED) TAPE AND REEL.
- F DIMENSION IS PORTION OF THE CORE.

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family 58SF	CODE JP
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (Cat. No. SFW__S-2ST_E9LF)	
A	J09-0202	M.Y	2009-5-25	angles	linear			
				±5°		scale	dwg no	
				dr	2009-5-25		sheet 1 of 1	
				engr	2009-5-25		JSA 97527	
				chr	2009-5-25		size	
				appd	2009-5-25		A4	
sheet index	revision	A					type Product Customer Drawing	
	sheet	1					Rev. A	

SC-SFWS03 JSA97525 97526
form: A4

RECOMMENDED CABLE (FPC)

n : NO. OF CONDUCTORS



PT. NO.	DESCRIPTION	MATERIAL	THICKNESS (μm)
1	BASE FILM	POLYIMIDE OR POLYESTER OR EQUIVALENT	25
2	CONDUCTOR	COPPER FOIL(PLATING : SOLDER $1\mu\text{m}$ MIN.)	35
3	OVERLAY	POLYIMIDE OR POLYESTER OR EQUIVALENT	—
4	SUPPORTING TAPE	POLYESTER OR POLYIMIDE OR EQUIVALENT	188

NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. TOTAL THICKNESS LIMIT OF EACH MATERIAL (INCLUDING ADHESIVE AGENT) IS SPECIFIED.

mat'l. code				surface 58 / tolerance ISO 406 / ISO 1101		projection		product family 58SF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title			
AA	J04-0333	H.T	Oct.13/04					RECOMMENDED CABLE			
AB	J06-0430	H.T	10/19/06	angles	linear			(CAT.No.SFW__S-2ST__)			
						scale X		dwg no sheet 1 of 1 size			
						FCI		JSA 93340 A4			
								type Product Customer Drawing			
sheet index		revision	AB							Rev. AB	
		sheet	1								


form: A4

1

2

RECOMMENDED CABLE (FFC)

n : NO. OF CONDUCTORS



PT. NO.	DESCRIPTION	MATERIAL	NOTE
1	INSULATOR	FLAME RESISTING POLYESTER OR EQUIVALENT	_____
2	CONDUCTOR	COPPER FOIL	PLATING: TIN OR SOLDER 1µm MIN.
3	SUPPORTING TAPE	FLAME RESISTING POLYESTER OR EQUIVALENT	_____

NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.

mat'l. code				surface 58 / tolerance ISO 406 ISO 1101		projection		product family 58SF		CODE JP	
ltr ecn no dr date				tolerances unless otherwise specified		mm		title			
AA J04-0333 H.T. 06/13/04				angles linear		mm		RECOMMENDED CABLE (CAT.No.SFW__S-2ST__)			
AB J06-0430 H.T. 10/19/06						scale X		dwg no sheet 1 of 1 size			
				dr 10/19/06		FCI		JSA 93341 A4			
				enr 10/19/06				type Product Customer Drawing			
				chr 10/19/06							
				appd 10/20/06							
sheet index		revision AB								Rev. AB	
sheet 1											

form: A4

1

2