



5mm Infrared LED

MODEL NO : IR333C-A

■ Features :

- High radiant intensity
- Peak wavelength $\lambda_p=940\text{nm}$
- View angle 20°
- High reliability
- 2.54mm Lead spacing

■ Description :

- EVERLIGHT's Infrared Emitting Diode (IR333C-A) is a high intensity diode, molded in a water clear plastic package.

The device is spectrally matched with phototransistor, photodiode and infrared receiver module.

■ Applications :

- Free air transmission system
- Optoelectronic switch
- Floppy disk drive
- Infrared applied system
- Smoke detector


PART NO.	CHIP	LENS COLOR
	MATERIAL	
IR	GaAlAs	Water clear



5mm Infrared LED

MODEL NO : IR333C-A

■ Package Dimensions :



■ Notes :

1. All dimensions are in millimeter.
2. Protruded resin under flange 1.5 mm Max.
3. Lead spacing is measured where the lead emerge from the package.
4. Lens color : Water clear.
5. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
6. These specification sheets include materials protected under copyright of EVERLIGHT corporation . Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.
7. When using this product , please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

**5mm Infrared LED**MODEL NO : IR333C-A**■ Absolute Maximum Ratings at T_A = 25°C**

Parameter	Symbol	Rating	Unit	Notice
Continuous Forward Current	I _F	50	mA	
Peak Forward Current Pulse width=100 μ s, Duty cycle=1%	I _{FP}	1.0	A	
Reverse Voltage	V _R	5	V	
Operating Temperature	Topr	-40 ~ +85	°C	
Storage Temperature	Tstg	-40 ~ +85	°C	
Soldering Temperature	Tsol	260	°C	4mm from mold body less than 5 seconds
Power Dissipation at(or below) 25°C Free Air Temperature	Pd	100	mW	

■ Electronic Optical Characteristics :

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Radiant Intensity	Ee	7.8	20	----	mW/sr	I _F =20mA
		----	85	----		I _F =100mA, tp=100 μ s, t _p /T=0.01
		----	750	----		I _F =1A, tp=100 μ s, t _p /T=0.01
Peak Wavelength	λ_p	----	940	----	nm	I _F =20mA
Spectral Bandwidth	$\Delta \lambda$	----	45	----	nm	I _F =20mA
Forward Voltage	V _F	----	1.2	1.5	V	I _F =20mA
		----	1.4	1.85		I _F =100mA, tp=100 μ s, t _p /T=0.01
		----	2.6	4.0		I _F =1A, tp=100 μ s, t _p /T=0.01
Reverse Current	I _R	----	----	10	μ A	V _R =5V
View Angle	2 θ 1/2	----	20	----	deg	I _F =20mA



5mm Infrared LED

MODEL NO : IR333C-A

Typical Electrical/Optical/Characteristics Curves

Fig. 1 Forward Current vs. Ambient Temperature




Fig. 2 Spectral Distribution




Fig. 3 Peak Emission Wavelength vs. Ambient Temperature





Fig. 4 Forward Current vs. Forward Voltage





5mm Infrared LED

MODEL NO : IR333C-A

■ Typical Electrical/Optical/Characteristics Curves

Fig. 5 Relative Intensity vs.
Forward Current




Fig. 6 Relative Radiant Intensity vs.
Angular Displacement




Fig. 7 Relative Intensity vs.
Ambient Temperature (°C)





Fig. 8 Forward Current vs.
Ambient Temperature (°C)





EVERLIGHT ELECTRONICS CO., LTD.

DEVICE NUMBER : DIR-033-007

REV : 1.2

ECN : _____

PAGE : 6/8

5mm Infrared LED

MODEL NO : IR333C-A

■ Reliability Test Item And Condition

The reliability of products shall be satisfied with items listed below.

Confidence level:90%

LTPD:10%

NO.	Item	Test Conditions	Test Hours/ Cycles	Sample Size	Failure Judgement Criteria	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 secs	22 pcs	$I_R \geq U \times 2$ $E_e \leq L \times 0.8$ $V_F \geq U \times 1.2$ U :Upper specification limit L :Lower specification limit	0/1
2	Temperature Cycle	H : +85°C 30 mins ↑ 5 mins ↓ L : -55°C 30 mins	50 cycles	22 pcs		0/1
3	Thermal Shock	H : +100°C 5 mins ↑ 10 secs ↓ L : -10°C 5 mins	50 cycles	22 pcs		0/1
4	High Temperature Storage	TEMP. : +100°C	1000 hrs	22 pcs		0/1
5	Low Temperature Storage	TEMP. : -55°C	1000 hrs	22 pcs		0/1
6	DC Operating Life	I _F =20mA	1000 hrs	22 pcs		0/1
7	High Temperature / High Humidity	85°C / 85% R.H.	1000 hrs	22 pcs		0/1




5mm Infrared LED

MODEL NO : IR333C-A

■ Test Method For Power :

Condition : $I_F=20\text{ mA}$
Test Item : Radiant Intensity
Unit : mW/sr



■ To Distinguish Intensity:

Condition: $I_F=20\text{mA}$


Bin Number	M	N	P	Q
Min	7.80	11.00	15.00	21.00
Max	12.50	17.60	24.00	34.00



5mm Infrared LED

MODEL NO : IR333C-A

■ Packing Specifications



EVERLIGHT

CPN:
P/N:

IR333C-A

QTY:
LOT NO:

CAT:
HUE:
REF:

MADE IN TAIWAN

CPN : Customer's Production Number
P/N : Production Number
QTY : Packing Quantity
CAT : Ranks
HUE : Peak Wavelength
REF : Reference
LOT NO : Lot Number
MADE IN TAIWAN : Production place

■ Packing Quantity Specification

- 1. 500 Pcs/1Bag , 6 Bags/1Box
- 2. 10 Boxes/1Carton