


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	"A" HEIGHT	IMPRINT AREA "B"	"C" REPEAT	LABELS PER ROW	ROWS PER FANFOLD	STANDARD PKG. QTY.
S050X125VAD	GMV3	1.250 [31.8]	0.38 +/- .031 [9.53]	1.50 [38.1]	16	8	5000
S050X150VAD	GMV3	1.500 [38.1]	0.50 +/- .031 [12.7]	2.00 [50.8]	16	6	5000
S050X125TAD	GMT1	1.250 [31.8]	0.38 +/- .031 [9.53]	1.50 [38.1]	16	8	5000
S050X150TAD	GMT1	1.500 [38.1]	0.50 +/- .031 [12.7]	2.00 [50.8]	16	6	5000
S050X125VADY	GMV3	1.250 [31.8]	0.38 +/- .031 [9.53]	1.50 [38.1]	16	8	5000
S050X150VADY	GMV3	1.500 [38.1]	0.50 +/- .031 [12.7]	2.00 [50.8]	16	6	5000



- NOTES:
1. ALL LABELS TO BE BUTT-CUT AS SHOWN.
2. MILLIMETERS ARE IN [].
3. SEE MFG. DWG. A61149.

										CAG FILENAME/LAYERS I00472LN_C10378_S050XxxxVADTAD_00.prt	
										PANDUIT CORP TINLEY PARK, ILLINOIS	
										CUSTOMER DRAWING OPTIMUM SELF-LAM. S050X***VAD, S050X***VADY, AND S050X***TAD COMPUTER PRINTABLE LABELS	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (,.XXX) ± .005 (.XX) ± .015 ANGLES ± 1°	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
										DRAWN BY RVU	MAT'L: SEE TABLE
										DATE 9-7-05	SCALE NTS
										DRAWING NO. C10378	DWG B
REV	DATE	BY	CHK	DESCRIPTION			ECN	R	CUST	SUP	SIZE
0	9-7-05	RVU		RELEASED TO PRODUCTION.			4162	R			