TOSHIBA Photocoupler GaAs Ired & Photo−Transistor

TLP620, TLP620−2, TLP620−4

Programmable Controllers
AC / DC−Input Module
Telecommunication

The TOSHIBA TLP620, −2 and −4 consists of a photo−transistor optically coupled to two gallium arsenide infrared emitting diode connected in inverse parallel.
The TLP620−2 offers two isolated channels in an eight lead plastic DIP, while the TLP620−4 provides four isolated channels in a sixteen plastic DIP.

- Collector−emitter voltage: 55V (min.)
- Current transfer ratio: 50% (min.)
  Rank GB: 100% (min.)

Unit: mm



TOSHIBA	11−5B2

Weight: 0.26 g (typ.)

Unit: mm



TOSHIBA	11−10C4

Weight: 0.54 g (typ.)

Unit: mm



TOSHIBA	11−20A3

Weight: 1.1 g (typ.)

Pin Configurations (top view)

TLP620



1 : ANODE
CATHODE
2 : CATHODE
ANODE
3 : EMITTER
4 : COLLECTOR

TLP620-2



1, 3 : ANODE
CATHODE
2, 4 : CATHODE
ANODE
5, 7 : EMITTER
6, 8 : COLLECTOR

TLP620-4



1, 3, 5, 7 : ANODE, CATHODE
2, 4, 6, 8 : CATHODE, ANODE
9, 11, 13, 15 : EMITTER
10, 12, 14, 16 : COLLECTOR

Start of commercial production
1984/01

- Isolation voltage: 5000V_{rms} (min.)
- Safety Standards
- UL recognized : UL1577, File No. E67349
- cUL recognized : CSA Component Acceptance Service No. 5A
  File No.E67349
- Option (D4) type

  VDE approved : EN60747-5-5

  Maximum operating insulation voltage: 890V_{PK}

  Highest permissible over voltage: 8000V_{PK}

  (Note) When an EN 60747-5-5 approved type is needed, please designate the "Option(D4)".

	7.62 mm pitch standard type	10.16 mm pitch TLP×××F type
• Creepage distance	: 6.4 mm (min)	8.0 mm (min)
Clearance	: 6.4 mm (min)	8.0 mm (min)
Insulation thickness	: 0.4 mm (min)	0.4 mm (min)

Absolute Maximum Ratings (Ta = 25°C)

Characteristic		Symbol	Rating		Unit
			TLP620	TLP620−2 TLP620−4	
LED	Forward current	$I_{F\ (RMS)}$	60	50	mA
	Forward current derating	ΔI_F / °C	−0.7 (Ta ≥ 39°C)	−0.5 (Ta ≥ 25°C)	mA / °C
	Pulse forward current	I_{FP}	±1 (100μs pulse, 100pps)		A
	Power dissipation (1 circuit)	P_D	100	70	mW
	Power dissipation derating (1 circuit)	ΔP_D / °C	−1.2 (Ta ≥ 39°C)	−0.7 (Ta ≥ 25°C)	mW / °C
	Junction temperature	T_j	125		°C
Detector	Collector−emitter voltage	V_{CEO}	55		V
	Emitter−collector voltage	V_{ECO}	7		V
	Collector current	I_C	50		mA
	Collector power dissipation (1 circuit)	P_C	150	100	mW
	Collector power dissipation derating (1 circuit) (Ta ≥ 25°C)	ΔP_C / °C	−1.5	−1.0	mW / °C
	Junction temperature	T_j	125		°C
Storage temperature range		T_{stg}	−55~125		°C
Operating temperature range		T_{opr}	−55~100		°C
Lead soldering temperature		T_{sold}	260 (10s)		°C
Total package power dissipation (1 circuit)		P_T	250	150	mW
Total package power dissipation derating (Ta ≥ 25°C, 1 circuit)		ΔP_T / °C	−2.5	−1.5	mW / °C
Isolation voltage (Note1)		BV_S	5000 (AC, 1 min., RH ≤ 60%)		V_{rms}

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.
Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook (“Handling Precautions”/“Derating Concept and Methods”) and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Note1: Device considered a two terminal device: LED side pins shorted together and detector side pins shorted together.

Recommended Operating Conditions

Characteristic	Symbol	Min	Typ.	Max	Unit
Supply voltage	V_{CC}	—	5	24	V
Forward current	$I_{F\ (RMS)}$	—	16	25	mA
Collector current	I_C	—	1	10	mA
Operating temperature	T_{opr}	−25	—	85	°C

Note: Recommended operating conditions are given as a design guideline to obtain expected performance of the device. Additionally, each item is an independent guideline respectively. In developing designs using this product, please confirm specified characteristics shown in this document.

Individual Electrical Characteristics (Ta = 25°C)

Characteristic		Symbol	Test Condition	Min	Typ.	Max	Unit
LED	Forward voltage	V_F	I_F = ±10mA	1.0	1.15	1.3	V
	Forward current	I_F	V_F = ±0.7V	—	2.5	20	μA
	Capacitance	C_T	V = 0V, f = 1MHz	—	60	—	pF
Detector	Collector−emitter breakdown voltage	$V_{(BR)\ CEO}$	I_C = 0.5mA	55	—	—	V
	Emitter−collector breakdown voltage	$V_{(BR)\ ECO}$	I_E = 0.1mA	7	—	—	V
	Collector dark current	I_{CEO}	V_{CE} = 24V	—	10	100	nA
			V_{CE} = 24V, Ta = 85°C	—	2	50	μA
	Capacitance (collector to emitter)	C_{CE}	V_{CE} = 0V, f = 1MHz	—	10	—	pF

Coupled Electrical Characteristics (Ta = 25°C)

Characteristic	Symbol	Test Condition	Min	Typ.	Max	Unit
Current transfer ratio	I_C / I_F	I_F = ±5mA, V_{CE} = 5V Rank GB	50	—	600	%
			100	—	600	
Saturated CTR	I_C / $I_{F\ (sat)}$	IF = ±1mA, V_{CE} = 0.4V Rank GB	—	60	—	%
			30	—	—	
Collector−emitter saturation voltage	$V_{CE\ (sat)}$	I_C = 2.4mA, I_F = ±8mA	—	—	0.4	V
		I_C = 0.2 mA, I_F = ±1 mA Rank GB	—	0.2	—	
			—	—	0.4	
Off−state collector current	$I_{C\ (off)}$	V_F = ± 0.7V, V_{CE} = 24V	—	1	10	μA
CTR symmetry (Note.)	$I_{C\ (ratio)}$	I_C (I_F = −5mA) / I_C (I_F = +5mA)	0.33	—	3	—

Note : $I_{C(ratio)} = \frac{I_{C2}(I_F = I_{F2}, V_{CE} = 5V)}{I_{C1}(I_F = I_{F1}, V_{CE} = 5V)}$



Isolation Characteristics (Ta = 25°C)

Characteristic	Symbol	Test Condition	Min	Typ.	Max	Unit
Capacitance input to output	C_S	V_S = 0 V, f = 1MHz	—	0.8	—	pF
Isolation resistance	R_S	V_S = 500V, R.H. ≤ 60%	1×10^{12}	10^{14}	—	Ω
Isolation voltage	BV_S	AC, 1 minute	5000	—	—	V_{rms}
		AC, 1 second, in oil	—	10000	—	
		DC, 1 minute, in oil	—	10000	—	V_{dc}

Switching Characteristics (Ta = 25°C)

Characteristic	Symbol	Test Condition	Min	Typ.	Max	Unit
Rise time	t_r	V_{CC} = 10V I_C = 2mA R_L = 100Ω	—	2	—	μs
Fall time	t_f		—	3	—	
Turn−on time	t_{on}		—	3	—	
Turn−off time	t_{off}		—	3	—	
Turn−on time	t_{ON}	R_L = 1.9kΩ (Fig.1) V_{CC} = 5V, I_F = ±16mA	—	2	—	μs
Storage time	t_s		—	15	—	
Turn−off time	t_{OFF}		—	25	—	

Fig. 1 Switching time test circuit

TLP620 $I_{F(RMS)}$ – Ta



TLP620-2
TLP620-4 $I_{F(RMS)}$ – Ta



TLP620 P_C – Ta



TLP620-2
TLP620-4 P_C – Ta



TLP620 I_{FP} – D_R



TLP620-2
TLP620-4 I_{FP} – D_R



$I_F - V_F$



$\Delta V_F / \Delta Ta - I_F$



$I_{FP} - V_{FP}$



$I_D - Ta$



$I_C - V_{CE}$



$I_C - V_{CE}$



$I_F - V_F$



$I_C - V_F$



$I_C - I_F$



$I_C / I_F - I_F$



I_C – Ta



V_{CE} (sat) – Ta



t_{on}, t_{off}, t_s Test condition



Switching Time – R_L



RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as “TOSHIBA”.
Hardware, software and systems described in this document are collectively referred to as “Product”.

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. **TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.**
- **PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").** Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. **IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT.** For details, please contact your TOSHIBA sales representative.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- **ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.**
- GaAs (Gallium Arsenide) is used in Product. GaAs is harmful to humans if consumed or absorbed, whether in the form of dust or vapor. Handle with care and do not break, cut, crush, grind, dissolve chemically or otherwise expose GaAs in Product.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. **TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.**