



RoHS COMPLIANT



Electrical Characteristics

Nominal Impedance: 75 ohms
Frequency Range: DC to 1 GHz
Operating Voltage (rms): 500 V maximum at sea level
Dielectric Withstand Voltage (rms): 1500 V maximum at sea level
Contact Resistance: 1.5 milliohms maximum
Insulation Resistance: 5000 megohms minimum

Mechanical Characteristics


Mating Cycles: 500 cycles minimum
Interface Dimensions: Conform to MIL-C-39012

Environmental Characteristics

Temperature Range: -55 °C to +85 °C

PART	DESCRIPTION
1	Body Brass, nickel plated
2	Insulation ABS
3	Dielectric Delrin
4	Contact PB, gold plated
5	Nut Brass, nickel plated
6	Washer Steel, nickel plated

Added panel cutout details	JW	3	04 Apr 06
CAD Issue	SN	2	12 Jul 01
First Issue	DW	1	23 May 96
DESCRIPTION OF REVISION			APPVD ISS DATE



Connectivity Solutions
7-13 Russel Way,
Widford Industrial Estate,
Chelmsford, Essex,
CM1 3AA, UK.
Tel: +44 (0) 1245 359515
Fax: +44 (0) 1245 358938

SCALE: Not To Scale

DIMENSIONS: mm

TOLERANCES:
± 0.2mm unless
otherwise stated

DRAWN BY:

J Williams

CHECKED BY:

M Terry

APPROVED BY:

A Tusi

DATE:

04 Apr 06

TITLE:
Isolated BNC Bulkhead
Jack to BNC Jack

PART NUMBER:

VBI100-1-75

PAGE: 1 of 1