

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

YZ-RX58-D5

YZ-RX58-D5

M

DRAWING
NUMBER

3

ISSUE

REPLACES X85318-YZ

RELEASE NO. PR-15024

CHECK

REVISIONS

CO	77592
DAW	15 AUG 94
A	0001191
JLH	20AUG03

CHECK

28 AUG 86

CHECK


28 AUG 86

CHECK

28 AUG 86

CHECK

RASTER




NOTE -

△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - - 4 OZ MAX
OVERTRAVEL - - - - - .005 MIN

RESET CHARACTERISTICS

OPERATING FORCE - - - - - 2 - 10 OZ
OVERTRAVEL - - - - - .015 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SINGLE POLE NORMALLY OPEN
MAINTAINED CONTACT

L67

15A 125, 250 OR 480 VAC
1/4 HP 125 VAC, 1/2 HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	
ONE PLACE	X, X	0.4/018	X, X
TWO PLACES	X, XX	0.15/.008	X, XX
THREE PLACES	X, XXX		X, XXX
ANGLES			

SI METRIC

US CUSTOMARY

DESIGN UNITS



WEIGHT