




Clock Oscillator SMD-version


+3,3V

model	KXO-V97T
frequency	156,250 MHz
frequency stability -40° ~ +85°C	± 50 ppm
operating temperature	-40° ~ +85°C
storage temperature	-40° ~ +85°C
symmetry	50% ± 10% at ½ Vcc level
rise & fall time max. (20% to 80%)	1 ns
"O" level max.	+ 0,4V
"1" level min.	Vcc -0,5V
input voltage Vcc	+ 3,3V
input current max.	40 mA
output load	15 pF
start up time max.	4 ms
tristate function	yes
disable delay time	100 ns max.
enable delay time	4 ms max.
RMS Phase Jitter (12kHz to 20MHz):	1ps max.
peak to peak jitter	40ps max.
contents of reel	1000 pcs.
RoHS	according to RoHS 2011/65/EU
part no.	12.92125


Dimensions (mm):




Output waveform:




Reflow soldering condition:




Test circuit:



Tape specification:



Suggested soldering pad:



PIN	CONNECTION
1	"L" (OV) "H" or OPEN
2	GND
3	Z OUTPUT
4	Vcc

Z: high impedance