


# ULTRA MINIATURE RELAY

## 2 POLES - 2 A (Slim Profile Signal Relay)

### FTR-B4 Series

#### ■ FEATURES

- DPDT 2C
- Ultra miniature slim type relay for surface mounting  
Height: 9.3 mm maximum (THT)  
10 mm maximum (SMT)  
Weight: Approximately 1.0 g
- Conforms to Bellcore & FCC part 68, and Telcordia & FCC part 68
- Conforms to UL1950 / CSA 950, IEC 950 / EN60950  
spacing and high breakdown voltage  
Clearance: 1.0mm  
Creepage: 1.6mm  
Basic insulation, 150V working voltage, pollution degree 2
- High reliable bifurcated gold overlay silver contact
- Low power consumption 140 mW (standard), 100 mW (latching)
- RoHS compliant. Please see page 9 for more information
- Plastic sealed



#### ■ PARTNUMBER INFORMATION

[Example]     FTR-B4    C    A    4.5    Z - B    05  
                  (a)    (b)    (c)    (d)    (e)    (f)    (g)

|     |                              |             |                                                                            |
|-----|------------------------------|-------------|----------------------------------------------------------------------------|
| (a) | Relay type                   | FTR-B4      | : FTR-B4-Series                                                            |
| (b) | Terminal type                | C<br>G<br>S | : Through hole<br>: Surface mount<br>: Surface mount, space saving         |
| (c) | Coil type                    | A<br>B      | : Standard type<br>: Latching type (1 coil)                                |
| (d) | Coil rated voltage           | 4.5         | : 1.5.....24 VDC<br>Coil rating table at page 3                            |
| (e) | Contact material             | Z<br>P      | : Gold overlay silver nickel (standard)<br>: Gold overlay silver palladium |
| (f) | Relay enclosing direction *1 | B           | : Standard enclosing direction                                             |
| (g) | Number of relays per reel *2 | 05          | : 500 (standard)                                                           |

Remarks: Actual marking on relay would not carry code FTR and be as below:  
Ordering code: FTR-B4CA4.5Z                      Actual marking: B4CA4.5Z

\*1 - Only surface mount types (G and S) are applicable

\*2 - All relays are packaged in tubes unless part number ends with -B05

# FTR-B4 SERIES

## ■ SPECIFICATION

| Item         |                                         |                   | Standard type                                                     | Latching type                        |
|--------------|-----------------------------------------|-------------------|-------------------------------------------------------------------|--------------------------------------|
|              |                                         |                   | FTR-B4 ( ) A                                                      | FTR-B4 ( ) B                         |
| Contact Data | Configuration                           |                   | 2 form C                                                          |                                      |
|              | Construction                            |                   | Bifurcated contacts (cross-bar)                                   |                                      |
|              | Material                                |                   | Gold overlay silver nickel / Gold overlay silver palladium        |                                      |
|              | Resistance (Initial)                    |                   | Max. 100 mΩ at 1 A, 6 VDC                                         |                                      |
|              | Contact rating (resistive)              |                   | 30VDC, 1A / 125VAC, 0.3A                                          |                                      |
|              | Max. carrying current                   |                   | 2A                                                                |                                      |
|              | Max. switching voltage                  |                   | 250 VAC / 220VDC                                                  |                                      |
|              | Max. switching power                    |                   | 62.5VA / 30W                                                      |                                      |
|              | Min. switching load *                   |                   | 0.01mA, 10mVDC                                                    |                                      |
| Life         | Mechanical                              |                   | Min. 50 x 10 <sup>6</sup> operations                              | Min. 20 x 10 <sup>6</sup> operations |
|              | Electrical                              | DC load           | Min. 100 x 10 <sup>3</sup> operations at 1A, 30VDC (at 0.5 Hz)    |                                      |
|              |                                         | AC load           | Min. 100 x 10 <sup>3</sup> operations at 0.3A, 125VAC (at 0.5 Hz) |                                      |
| Coil Data    | Rated power                             |                   | 140mW - 230mW                                                     | 100mW - 130mW                        |
|              | Operate power                           |                   | 80mW - 130mW                                                      | 57mW - 68mW                          |
|              | Operating temperature range             |                   | -40 °C to +85 °C (no frost)                                       |                                      |
| Timing Data  | Operate (at nominal voltage, no bounce) |                   | Max. 3 ms                                                         | Max. 3 ms (set)                      |
|              | Release (at nominal voltage, no bounce) |                   | Max. 3 ms                                                         | Max. 3 ms (reset)                    |
| Insulation   | Resistance (initial)                    |                   | Min. 1,000MΩ at 500VDC                                            |                                      |
|              | Dielectric strength                     | Open contacts     | 1,000VAC (50/60Hz) 1min                                           |                                      |
|              |                                         | Contacts to coil  | 1,500VAC (50/60Hz) 1min                                           |                                      |
|              |                                         | Adjacent contacts | 1,000VAC (50/60Hz) 1min.                                          |                                      |
|              | Surge strength                          | Coil to contacts  | 2,500V, 2 x 10μs standard wave                                    |                                      |
|              | Clearance                               | Adjacent contacts | 1.0 mm                                                            |                                      |
|              |                                         | Open contacts     | 0.28 mm                                                           |                                      |
|              |                                         | Coil and contacts | 1.0 mm                                                            |                                      |
|              | Creepage                                | Adjacent contacts | 1.0 mm                                                            |                                      |
|              |                                         | Open contacts     | 0.28 mm                                                           |                                      |
|              |                                         | Coil and contacts | 1.60 mm                                                           |                                      |
| Other        | Vibration resistance                    | Misoperation      | 10 to 55 Hz at double amplitude of 3.3 mm                         |                                      |
|              |                                         | Endurance         | 10 to 55 Hz at double amplitude of 5 mm                           |                                      |
|              | Shock                                   | Misoperation      | 750m/s <sup>2</sup>                                               |                                      |
|              |                                         | Endurance         | 1,000m/s <sup>2</sup>                                             |                                      |
|              | Weight                                  |                   | Approximately 1 g                                                 |                                      |
|              | Sealing                                 |                   | RT III (plastic sealed)                                           |                                      |

\* Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

## ■ COIL RATING

Standard type

| Coil Code | Rated Coil Voltage (VDC) | Coil Resistance +/- 10% (Ohm) | Must Operate Voltage (VDC) * | Must Release Voltage (VDC) * | Rated Power (mW) |
|-----------|--------------------------|-------------------------------|------------------------------|------------------------------|------------------|
| 1.5       | 1.5                      | 16.1                          | 1.13                         | 0.15                         | 140              |
| 003       | 3                        | 64.3                          | 2.25                         | 0.3                          |                  |
| 4.5       | 4.5                      | 145                           | 3.38                         | 0.45                         |                  |
| 006       | 6                        | 257                           | 4.5                          | 0.6                          |                  |
| 009       | 9                        | 579                           | 6.75                         | 0.9                          |                  |
| 012       | 12                       | 1,028                         | 9.0                          | 1.2                          | 230              |
| 024       | 24                       | 2,504                         | 18.0                         | 2.4                          |                  |

Latching type (1 coil)

| Coil Code | Rated Coil Voltage (VDC) | Coil Resistance +/- 10% (Ohm) | Set Voltage (VDC) * | Reset Voltage (VDC) * | Set/Reset current (mA) | Rated Power (mW) |
|-----------|--------------------------|-------------------------------|---------------------|-----------------------|------------------------|------------------|
| 1.5       | 1.5                      | 22.5                          | +1.13               | -1.13                 | 50                     | 100              |
| 003       | 3                        | 90                            | +2.25               | -2.25                 | 25                     |                  |
| 4.5       | 4.5                      | 203                           | +3.38               | -3.38                 | 17                     |                  |
| 006       | 6                        | 360                           | +4.5                | -4.5                  | 13                     |                  |
| 009       | 9                        | 810                           | +6.75               | -6.75                 | 8                      |                  |
| 012       | 12                       | 1,440                         | +9.0                | -9.0                  | 6                      |                  |
| 024       | 24                       | 4,800                         | +18.0               | -18.0                 | 4                      | 120              |

Note: All values in the table are valid for 20°C and zero contact current.

\* Specified operate values are valid for pulse wave voltage.

## ■ SAFETY STANDARDS










| Type | Compliance               | Contact rating                                    |
|------|--------------------------|---------------------------------------------------|
| UL   | UL 508                   | Flammability: UL 94-V0 (plastics)                 |
|      | E 63615                  | 0.5A, 125VAC (resistive)<br>1A, 30VDC (resistive) |
| CSA  | C22.2 No. 14<br>LR 40304 | 0.3A, 110VDC (resistive)<br>2A, 30VDC (resistive) |

Comply with Telcordia specifications and FCC part 68 and meet BSI EN60950-1:2006



Marking only for UL, CSA

## CHARACTERISTIC DATA







### Standard type









# FTR-B4 SERIES



- Latching type (1coil)









## ■ DIMENSIONS

FTR-B4C - Through hole type


### ● Dimensions



### ● Schematics (BOTTOM VIEW)




### ● PC board mounting hole layout (BOTTOM VIEW)




FTR-B4G - Surface mount type


### ● Dimensions



### ● Schematics (TOP VIEW)




### ● PC board mounting pad layout (TOP VIEW)




FTR-B4S- Space saving type


### ● Dimensions



### ● Schematics (TOP VIEW)



### ● PC board mounting pad layout (TOP VIEW)



\* Indicates reset state for latching relays (FTR-B4CB, FTR-B4GB and FTR-B4SB versions)  
Indicates non-operate state for standard relays (FTR-B4CA, FTR-B4GA and FTR-B4SA versions)

■ **COIL POLARITY LATCHING TYPE**

|               |   |   |
|---------------|---|---|
| Coil terminal | 1 | 8 |
| Set           | + | - |
| Reset         | - | + |

## ■ RECOMMENDED SOLDERING CONDITIONS FOR SMT (SEE PAGE 9) (TEMPERATURE PROFILE)

Notes:

1. Temperature profiles on page 9 show the temperature of PC board surface.
2. Please perform soldering test with your actual PC board before mass production, since the temperatures of PC board surfaces vary according to the size of PC board, status of parts mounting and heating method.

## ■ PRECAUTIONS


- For details on general precautions, refer to the section on technical descriptions.
- Since this is a polarized relay, follow the instructions of the internal wiring diagram for the  $\pm$  connections of the coil.
- Note that the terminal layout and internal wiring of the surface mount relay are a top view.
- SMT versions of the FTR-B4 relays will be shipped in "dry pack".

## ■ PACKAGING SPECIFICATIONS


- **Packaging method**

- Packaging standard: JIS C 0806
- Taping type: TB 2412
- Reel type: R24D
- Quantity of 1 reel: 500 pieces


- **Packaging orientation code: B**



- **Reel dimensions**



- **Tape dimensions**



Note:

Relays are sold in 500 pieces per box. Minimum order quantity is 1000 pieces for tube packing and 500 pieces for tape & reel packing.



## RoHS Compliance and Lead Free Information


### 1. General Information

- All relays produced by Fujitsu Components are compliant with RoHS directive 2011/65/EU including amendments.
- Cadmium as used in electrical contacts is exempted from the RoHS directives.  
As per Annex III of directive 2011/65/EU.
- All relays are lead-free. Please refer to Lead-Free Status Info for older date codes at:  
<http://www.fujitsu.com/downloads/MICRO/fcai/relays/lead-free-letter.pdf>
- Lead free solder plating on relay terminals is Sn-3.0Ag-0.5Cu, unless otherwise specified.  
This material has been verified to be compatible with PbSn assembly process.

### 2. Recommended Lead Free Solder Condition

- Recommended solder Sn-3.0Ag-0.5Cu.

#### Reflow Solder condition



#### Flow Solder Condition:

Pre-heating: maximum 120°C within 9 sec.  
Soldering: dip within 5 sec. at 255°C ± 5°C solder bath  
Relay must be cooled by air immediately after soldering

#### Solder by Soldering Iron:

Soldering Iron 30-60W  
Temperature: maximum 350-360°C  
Duration: maximum 3 sec.

**We highly recommend that you confirm your actual solder conditions**

### 3. Moisture Sensitivity

- Moisture Sensitivity Level standard is not applicable to electromechanical relays, unless otherwise indicated.

### 4. Tin Whiskers

- Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

## Fujitsu Components International Headquarter Offices

### Japan

Fujitsu Component Limited  
Gotanda-Chuo Building  
3-5, Higashigotanda 2-chome, Shinagawa-ku  
Tokyo 141, Japan  
Tel: (81-3) 5449-7010  
Fax: (81-3) 5449-2626  
Email: [promothq@ft.ed.fujitsu.com](mailto:promothq@ft.ed.fujitsu.com)  
Web: [www.fcl.fujitsu.com](http://www.fcl.fujitsu.com)

### North and South America

Fujitsu Components America, Inc.  
250 E. Caribbean Drive  
Sunnyvale, CA 94089 U.S.A.  
Tel: (1-408) 745-4900  
Fax: (1-408) 745-4970  
Email: [components@us.fujitsu.com](mailto:components@us.fujitsu.com)  
Web: <http://us.fujitsu.com/components>

### Europe

Fujitsu Components Europe B.V.  
Diamantlaan 25  
2132 WV Hoofddorp  
Netherlands  
Tel: (31-23) 5560910  
Fax: (31-23) 5560950  
Email: [info@fceu.fujitsu.com](mailto:info@fceu.fujitsu.com)  
Web: [emea.fujitsu.com/components/](http://emea.fujitsu.com/components/)

### Asia Pacific

Fujitsu Components Asia Ltd.  
102E Pasir Panjang Road  
#01-01 Citilink Warehouse Complex  
Singapore 118529  
Tel: (65) 6375-8560  
Fax: (65) 6273-3021  
Email: [fcal@fcal.fujitsu.com](mailto:fcsl@fcal.fujitsu.com)  
Web: <http://www.fujitsu.com/sq/services/micro/components/>

©2014 Fujitsu Components Europe B.V. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

The contents, data and information in this datasheet are provided by Fujitsu Component Ltd. as a service only to its user and only for general information purposes.

The use of the contents, data and information provided in this datasheet is at the users' own risk.

Fujitsu has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

Fujitsu Components Europe B.V. and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof.

Nor do Fujitsu Components Europe B.V. and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability for any representation or warrant of any kind, express or implied, including warranties of any kind for merchantability or fitness for particular use, with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. June 26, 2014