



Home > Products > Clock / Timing Devices > PC-Notebook-Server Clocks > Clock Synthesizer by Chipset Vendor > Desktop Chipsets > 953401 > 953401CF

[Add to myIDT \[?\]](#)

You may also like...

## 953401CF

**Category:** [Desktop Chipsets](#)**Generic Part:** 953401**Market Group:** PC CLOCK**Description:** PC MAIN CLOCK

The ICS953401 is a two chip clock solution for desktop designs using SIS 656/662 style chipsets. When used with a zero delay buffer such as the ICS9P931 for DDR applications it provides all the necessary clocks signals for such a system.

**Output Features:**

- 2 - Pairs of differential CPUCLKs (differential current mode)
- 1 - Pair of differential SRCCLK (differential current mode)
- 5 - Pairs of differential PCI-Express clocks
- 8 - PCI @ 3.3V, 2 free-running
- 2 - ZCLKs @ 3.3V
- 1- 12/48MHZ @ 3.3V selectable by I2C
- 1- 24/48MHz, @ 3.3V selectable by I2C
- 3 - REF @ 3.3V, 14.318MHz

Time is  
money

**Parameters**

|                         |                |
|-------------------------|----------------|
| Package                 | SSOP 56 (PV56) |
| Voltage                 | 3.3 V          |
| Package                 | SSOP 56        |
| Speed                   | NA             |
| Temperature             | C              |
| Status                  | Active         |
| Sample                  | Yes            |
| Minimum Order Quantity  | 130            |
| Factory Order Increment | 26             |

**Distributor Inventory**

No Pricing information is available from our Distributors at this time.

**Documents**

| Type | Title                  | Size  | Revision Date |
|------|------------------------|-------|---------------|
| Misc | PC Clocks Contact Info | 61 KB | 05/29/2007    |

**Package**

|                                  |                          |
|----------------------------------|--------------------------|
| Description                      | SSOP 300 MIL, 56LD       |
| Class                            | PLASTIC                  |
| Moisture Sensitivity Level (MSL) | 1                        |
| Category                         | Standard                 |
| Moisture Exposure Floor Life     | Unlimited @ <30°C/85% RH |
| Peak Reflow Temperature          | 225°C                    |
| Rebake Conditions                | NA                       |
| Length                           | 18.4                     |
| Mark                             | F                        |
| Width                            | 7.5                      |
| Pitch                            | 0.64                     |
| Thickness                        | 2.3                      |
| Status                           | Active                   |