

FEATURES

- * 1.4 inch (35.76mm) MATRIX HEIGHT.
- * LOW POWER REQUIREMENT.
- * SINGLE PLANE, WIDE VIEWING ANGLE.
- * SOLID STATE RELIABILITY.
- * 5×8 ARRAY WITH X-Y SELECT.
- * COMPATIBLE WITH USASCII AND EBCDIC CODES.
- * STACKABLE HORIZONTALLY.
- * CATEGORIZED FOR LUMINOUS INTENSITY.


DESCRIPTION

The LTP-14058AKD is a 1.4 inch (35.76 mm) matrix height 5×8 dot matrix displays. This device utilizes AlInGaP Hyper Red LED chips, which are made from AlInGaP on a non-transparent GaAs substrate, and has a gray face and white dot color.

DEVICE


| PART NO. | DESCRIPTION |
|-------------------|--------------------|
| AlInGaP HYPER RED | ANODE COLUMN |
| LTP-14058AKD | CATHODE ROW |

PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are ± 0.25 mm (0.01") unless otherwise noted.

INTERNAL CIRCUIT DIAGRAM



PIN CONNECTION

| No. | CONNECTION |
|-----|----------------|
| 1 | CATHODE ROW 6 |
| 2 | CATHODE ROW 8 |
| 3 | ANODE COLUMN 2 |
| 4 | ANODE COLUMN 3 |
| 5 | CATHODE ROW 5 |
| 6 | ANODE COLUMN 5 |
| 7 | CATHODE ROW 7 |
| 8 | CATHODE ROW 3 |
| 9 | CATHODE ROW 1 |
| 10 | ANODE COLUMN 4 |
| 11 | ANODE COLUMN 3 |
| 12 | CATHODE ROW 4 |
| 13 | ANODE COLUMN 1 |
| 14 | CATHODE ROW 2 |

ABSOLUTE MAXIMUM RATING AT Ta=25°C

| PARAMETER | MAXIMUM RATING | UNIT |
|--|----------------|-------|
| Average Power Dissipation Per Dot | 40 | mW |
| Peak Forward Current Per Dot | 90 | mA |
| Average Forward Current Per Dot | 15 | mA |
| Derating Linear From 25°C Per Dot | 0.2 | mA/°C |
| Reverse Voltage Per Dot | 5 | V |
| Operating Temperature Range | -35°C to +85°C | |
| Storage Temperature Range | -35°C to +85°C | |
| Solder Temperature: max 260°C for max 3sec at 1.6mm[1/16inch] below seating plane. | | |

ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C

| PARAMETER | SYMBOL | MIN. | TYP. | MAX. | UNIT | TEST CONDITION |
|-----------------------------------|------------------|------|------|------|------|-------------------------------|
| Average Luminous Intensity | I _v | 800 | 2600 | | μcd | I _p =32mA 1/16Duty |
| Peak Emission Wavelength | λ _p | | 650 | | nm | I _F =20mA |
| Spectral Line Half-Width | Δλ | | 20 | | nm | I _F =20mA |
| Dominant Wavelength | λ _d | | 639 | | nm | I _F =20mA |
| Forward Voltage any Dot | V _F | | 2.1 | 2.6 | V | I _F =20mA |
| | | | 2.3 | 2.8 | | I _F =80mA |
| Reverse Current any Dot | I _R | | | 100 | μA | V _R =5V |
| Luminous Intensity Matching Ratio | I _{v-m} | | | 2:1 | | I _p =32mA 1/16Duty |

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig1. RELATIVE INTENSITY VS. WAVELENGTH




Fig2. RELATIVE LUMINOUS EFFICIENCY (LUMINOUS INTENSITY PER UNIT CURRENT) VS. PEAK CURRENT





Fig3. FORWARD CURRENT VS. FORWARD VOLTAGE

Fig4. RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT





Fig5. MAX. AVERAGE FORWARD CURRENT VS. AMBIENT TEMPERATURE



NOTE : KD=AlInGaP HYPER RED

(REFRESH RATE 1KHz)