




REV.	ZONE	LTR	DESCRIPTION	DATE	REVISER	APPD
5			RENEW DRAWING	7/3-00	Stacy	wenson
6			RENEW DRAWING	9/22-00	tony	wenson

ORDERING INFORMATION

8AT 068 S - $\frac{3}{2} \frac{2}{5} \frac{2}{1} - \frac{10}{9}$
(1) (2) (3) (4)(5)(6)(7)(8) (9)



SPECIFICATION -

- INSULATOR MATERIAL : PBT WITH GLASS-FIBER REINFORCED UL 94V-0
- CONTACT MATERIAL : PHOSPHOR BRONZE , GOLD OVER NICKEL
- RATED CURRENT : 1A
- INSULATION RESISTANCE : 500MΩ MIN.
- CONTACT RESISTANCE : 35mΩ MAX.
- DIELECTRIC WITHSTANDING VOLTAGE : AC 250V FOR 1 MINUTE.
- OPERATING TEMPERATURE : -55°C ~ +105°C.

RECOMMENDED P.C.B. HOLE PATTERN

- SERIES NUMBER :
BAL : HIGH DENSITY 1.27(.050") SPACING
- NO OF CONTACTS :
EX 068 : 68 POSITIONS
- CONTACT TYPE :
S : RECEPTACLE
- COLOR (INSULATOR)
3 : BLACK
- CONTACT FINISH :
0 : SELECTED GOLD FLASH OVER 30μ" NICKEL
2 : 15μ" SELECTED GOLD OVER 50μ" NICKEL
3 : 30μ" SELECTED GOLD OVER 50μ" NICKEL
- METAL SHELL FINISH :
0 : ALL PLASTIC
1 : TIN PLATED SHELL, WITH GROUNDING INDENTS
4 : TIN PLATED SHELL, W/O GROUNDING INDENTS
5 : NICKEL PLATED SHELL, W/O GROUNDING INDENTS
6 : NICKEL PLATED SHELL, WITH GROUNDING INDENTS
- MATING HOLES :
0 : W/O MATING HOLES
2 : 2-56 UNC
3 : M2.6 * 0.45
4 : 4-40 UNC
- BRACKET TYPE :
0 : W/O BRACKET
1 : WITHOUT RAILS, WITH LATCH BLOCKS
2 : WITH RAILS & LATCH BLOCKS
3 : WITHOUT RAILS & LATCH BLOCKS
- SUFFIX NO:

MATERIAL	TOLERANCE UNSPECIFIED	EDA INC.	PART NO.
	0.00 ±0.13(.005) 0.0 ±0.25(.010)		
FINISH	ANGLE	NAME	UNIT
	±	BAT SERIES 1.27(.050)	mm(inch)
DESIGNED	DATE	SCALE	
CHECKED	02/12/96	1:4:1	
APPROVED	TONY 9/22-2000	DRAWING NO	
	WENSON/22-2000	R-STBAT-3	
		A3	RS1BAT31