








△ AMP LOGO AND CAVITY NUMBER LOCATED ON EITHER SURFACE.



MATING CONNECTOR INTERFACE

TYPICAL PLUG CAVITY SECTION
(DIMENSIONS REFERENCE ONLY)

RECOMMENDED CUT OUT
FOR 1.52 MAX THICK PANEL



3-DIMENSIONAL MODEL
NTS

2.13	.084	7.62	.300	24.38	.960
1.57	.062	5.08	.200	19.81	.780
1.52	.060	5.05	.199	15.47	.609
0.64	.025	3.68	.145	11.18	.440
0.51	.020	3.18	.125	8.76	.345
0.25	.010	2.79	.110	8.64	.340
0.13	.005	2.67	.105	8.08	.318
MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

770341-1		
PART NO		
AMP AMP Incorporated Harrisburg, PA 17105-3608		
NAME PLUG, PANEL MOUNT, 2 CIRCUIT, .062 PIN AND SOCKET		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES: ON + 2 PLC DEC ± 0.13 3 PLC DEC ± - ANGLES ± 1°0'	DR 11-4-93 K. WHITAKER CHK 11-4-93 R. SWING APPD 11-4-93 C. CASH APPD 11-4-93 C. CASH PRODUCT SPEC -	SIZE D 00779 CAGE CODE 00779 DRAWING NO C-770341
MATERIAL NYLON, UL 94V-2 NATURAL	FINISH -	SCALE 5:1
WEIGHT -	APPLICATION SPEC -	SHEET 1 OF 1

CUSTOMER DRAWING