





SERIES 75



0.3" Diameter, 200 mA

FEATURES

- Small Size
- Flush, Shafted, or Knobbed Shaft


**DIMENSIONS** In inches (and millimeters)**Screwdriver Actuated**

Rear view shown on next page.




Shaft Actuated

Rear view shown on next page.

All dimensions not shown and front views same as style BP.



Rear view shown on next page.


Integral Knob Actuated

Rear view shown on next page.

All dimensions not shown and front views same as style CP.

Grayhill part number and date code marked on label.
Customer part number marked on request.


CIRCUIT DIAGRAMS AND REAR VIEWS



SPECIFICATIONS

Electrical Ratings

Chart shown for non-shorting (break before make) contacts, resistive load.



One cycle is 360° rotation and a return through all switch positions to the starting position. The data for the curve was measured at sea level, 25°C and 68% relative humidity with the following limiting criteria:

Contact Resistance: 50 millionohms maximum (15 millionohms initially).

Insulation Resistance: 10,000 Mohms minimum between mutually insulated parts.

Voltage Breakdown: 500 Vac between mutually insulated parts.

Life Expectancy: 10,000 cycles at 200 milliamps. One cycle is 360° rotation and a return through all switch positions to the starting position.

Low Level Rating: Make and break a 50 mV, 1 milliamp, resistive load for 10,000 cycles with a maximum contact resistance of 50 millionohms.

Contact Grayhill for information if the life limiting criteria is more critical than those listed, if the required cycles of operation are greater than those listed, if a larger make and break current is required than the one listed for the desired number of cycles, or if elevated temperatures or reduced pressures are part of the operating environment.

Materials and Finishes

Switch Base: Diallyl per MIL-M-14

Detent Cover and Detent Rotor in Styles AP, AF, BP, and BF: Phenolic per MIL-M-14

Bushing: Brass, tin zinc plating

Stop Pin: Stainless steel, passivated

Detent Balls: Steel, nickel-plated

Detent and Contact Springs: Tinned music wire

Rotor Contact: Silver cad-oxide, gold-plated

Terminals and Common: Brass, gold plate .00002" minimum thickness over silver plate .0003" minimum.

Shaft in Style BF or BP: Zinc

Integral Knob and Detent Rotor in Style CF or CP: Red Thermoplastic

Mounting Hardware for Style BF or BP: One mounting nut .062" thick by .312" across flats and one external tooth lockwasher supplied with each switch. Mounting nut is brass, zinc plated and lockwasher is spring steel.

Additional Characteristics

Contact Type: Non-shorting, wiping contacts

Terminals: Switches are provided with the full circle of terminals regardless of the number of active positions.

Stop Strength: 8 ounce-inches minimum

CHOICES AND LIMITATIONS

| Style and Designation | | Angle Of Throw | Stops | Terminal | Poles Per Deck | Number of Decks | | Number of Positions/Pole |
|--|--|----------------|-------|----------|----------------|-----------------|--------------|--------------------------|
| Ø 0.187 (4,75) Circle of Term. | Ø 0.300 (7,62) Circle of Term. | | | | | Shorting | Non-Shorting | |
| AP = Screwdriver Actuated BP = Shaft Operated CP = Integral Knob | AF = Screwdriver Actuated BF = Shaft Operated CF = Integral Knob | 36° | Fixed | Printed | 1 2 | Not Available | 1 1 | 2 thru 10 2 thru 5 |

ORDERING INFORMATION

| | |
|------------------------------|--|
| 75AP36-01-1-10N-C | Series |
| | Style: Letters from Choices and Limitations Chart |
| | Angle of Throw: 36° only |
| | Stop Arrangement: The suffix C or F must be added to a one pole per deck switch to indicate continuous rotation (C) or fixed stop (F) between position 1 and position 10. |
| | Type of Contacts: N=Non-shorting only |
| | Positions per Pole: requires 02 positions as a minimum to maximum allowable dependent on the poles per deck |
| | Poles per Deck: 1 or 2 poles available |
| | Number of Decks: 1 deck only |

Available from your local Grayhill Distributor.

For prices and discounts, contact a local Sales Office, an authorized local Distributor, or Grayhill.