

Precision High-Voltage Reference in SOT23

General Description

The MAX6043 precision voltage reference provides accurate preset +2.5V, +3.3V, +4.096V, +5.0V, and +10V reference voltages from up to +40V input voltages. The MAX6043 features a proprietary temperature coefficient curvature-correction circuit and laser-trimmed thin-film resistors that result in a very low temperature coefficient of 15ppm/°C (max) and excellent initial accuracy of 0.05% (max). Low temperature drift and low noise make the MAX6043 ideal for use with high-resolution A/D or D/A converters.

The MAX6043 draws 320μA of supply current and sources 10mA or sinks 0.6mA of load current. The MAX6043 uses bandgap technology for low-noise performance and excellent accuracy. The MAX6043 does not require an output bypass capacitor for stability, and is stable with capacitive loads up to 100μF. Eliminating the output bypass capacitor saves valuable board area in space-critical applications. The supply-independent, low supply current makes the MAX6043 ideal for battery-operated, high-performance systems.

The MAX6043 is available in a 6-pin SOT23 package and operates over the automotive (-40°C to +125°C) temperature range.


Applications

Analog-to-Digital Converters
Digital-to-Analog Converters
Digital Voltmeters
Voltage Regulators
Threshold Detectors

Features

- ◆ +2.5V, +3.3V, +4.096V, +5.0V, or +10V Output Voltages
- ◆ Excellent Temperature Stability: 15ppm/°C (max)
- ◆ Tight Initial Accuracy: 0.05% (max)
- ◆ Tiny SOT23 Package
- ◆ Wide +4.5V to +40V Supply Voltage Range
- ◆ Low Noise: 4μVp-p (typ at 2.5V Output)
- ◆ Short-Circuit Protected
- ◆ Wide Operating Temperature Range
-40°C to +125°C
- ◆ Stable with Capacitive Loads from 0 to 100μF
- ◆ No External Capacitors Required for Stability

Pin Configuration



Ordering Information

PART	OUTPUT VOLTAGE (V)	TEMPCO (PPM/°C)	INITIAL ACCURACY (%)	TOP MARK
MAX6043AAUT25-T	2.500	15	0.06	ABRZ
MAX6043AAUT25#TG16	2.500	15	0.06	#ACMH
MAX6043BAUT25-T	2.500	20	0.10	ABDQ
MAX6043BAUT25#TG16	2.500	20	0.10	#ACMI
MAX6043CAUT25-T	2.500	65	0.50	ABDR
MAX6043CAUT25#TG16	2.500	65	0.50	#ACMJ
MAX6043AAUT33-T	3.300	15	0.06	ABSA
MAX6043AAUT33#TG16	3.300	15	0.06	#ACMK
MAX6043BAUT33-T	3.300	20	0.10	ABDS
MAX6043BAUT33#TG16	3.300	20	0.10	#ACML

#Denotes an RoHS-compliant device that may include lead that is exempt under the RoHS requirements.
T = Tape and reel.

Ordering Information continued at end of data sheet.

Typical Operating Circuit appears at end of data sheet.

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim's website at www.maximintegrated.com.

MAX6043

Precision High-Voltage Reference in SOT23

ABSOLUTE MAXIMUM RATINGS

IN to GND-0.3V to +42V
 OUTF, OUTS to GND-0.3V to (V_{IN} + 0.3V)
 Continuous Power Dissipation (T_A = +70°C)
 6-Pin SOT23 (derate 9.1mW/°C above +70°C).....727mW
 OUT₁ Short-Circuit Duration5s
 Operating Temperature Range-40°C to +125°C
 Storage Temperature Range-65°C to +150°C

Junction Temperature Range-65°C to +150°C
 Maximum Junction Temperature+150°C
 Lead Temperature (soldering, 10s)+300°C
 Soldering Temperature (reflow)
 RoHS-compliant package.....+245°C
 Packages containing lead(Pb).....+240°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS—V_{OUT} = +2.5V

(V_{IN} = +5V, I_{OUT} = 0, T_A = T_{MIN} to T_{MAX}. Typical values are at T_A = +25°C, unless otherwise noted.) (Note 1)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
OUTPUT					
Output Voltage	I _{OUT} = 0, T _A = +25°C	MAX6043A (0.06%)	2.4985	2.5000	V
		MAX6043B (0.1%)	2.4975	2.5000	
		MAX6043C (0.5%)	2.4876	2.5000	
Output-Voltage Temperature Coefficient (Note 2)	T _A = -40°C to +125°C	MAX6043A_25	3	15	ppm/°C
		MAX6043B_25	5	25	
		MAX6043C_25	10	65	
Line Regulation (Note 4)	4.5V < V _{IN} < 40V	T _A = +25°C	1	6	ppm/V
		T _A = -40°C to +125°C	1.5	10	
Load Regulation (Note 4)	Sourcing, 0 < I _{OUT} < 10mA	T _A = +25°C	8	70	ppm/mA
		T _A = -40°C to +125°C		70	
	Sinking, -0.6mA < I _{OUT} < 0mA	T _A = +25°C	70	900	
		T _A = -40°C to +125°C		900	
OUT Short-Circuit Current	Output shorted to GND		60		mA
	Output shorted to IN		-2		
Thermal Hysteresis	(Note 3)		150		ppm
Long-Term Stability	Δt = 1000hr		150		ppm
DYNAMIC CHARACTERISTICS					
Output Noise Voltage	0.1Hz to 10Hz		4		μV _{P-P}
	10Hz to 1kHz		7		μV _{RMS}
Turn-On Settling Time	To V _{OUT} = 0.05% of final value, C _{OUT} = 50pF		150		μs
INPUT					
Supply Voltage Range	Inferred from line regulation test	4.5		40.0	V
Quiescent Supply Current	I _{OUT} = 0	T _A = +25°C	320	490	μA
		T _A = -40°C to +125°C	370	650	

MAX6043

Precision High-Voltage Reference in SOT23

ELECTRICAL CHARACTERISTICS— $V_{OUT} = +3.3V$

($V_{IN} = +10V$, $I_{OUT} = 0$, $T_A = T_{MIN}$ to T_{MAX} . Typical values are at $T_A = +25^\circ C$, unless otherwise noted.) (Note 1)

PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
OUTPUT						
Output Voltage	I _{OUT} = 0, T _A = +25°C	MAX6043A (0.06%)	3.2980	3.3000	3.3020	V
		MAX6043B (0.1%)	3.2967	3.3000	3.3033	
		MAX6043C (0.5%)	3.2836	3.3000	3.3165	
Output-Voltage Temperature Coefficient (Note 2)	T _A = -40°C to +125°C	MAX6043A_33	3		15	ppm/°C
		MAX6043B_33	5		25	
		MAX6043C_33	10		65	
Line Regulation (Note 4)	5.3V ≤ V _{IN} ≤ 40V	T _A = +25°C	1		6	ppm/V
		T _A = -40°C to +125°C	1.5		10	
Load Regulation (Note 4)	Sourcing, 0 ≤ I _{OUT} ≤ 10mA	T _A = +25°C	23		70	ppm/mA
		T _A = -40°C to +125°C			70	
	Sinking, -0.6mA ≤ I _{OUT} ≤ 0mA	T _A = +25°C	100		900	
		T _A = -40°C to +125°C			900	
OUT Short-Circuit Current	OUT shorted to GND		60			mA
	OUT shorted to IN		-2			
Thermal Hysteresis	(Note 3)		150			ppm
Long-Term Stability	Δt = 1000hr		150			ppm
DYNAMIC CHARACTERISTICS						
Output Noise Voltage	0.1Hz to 10Hz		5.3			μV _{P-P}
	10Hz to 1kHz		9.5			μV _{RMS}
Turn-On Settling Time	To V _{OUT} = 0.05% of final value, C _{OUT} = 50pF		180			μs
INPUT						
Supply Voltage Range	Inferred from line regulation test		5.3		40.0	V
Quiescent Supply Current	I _{OUT} = 0	T _A = +25°C	320		490	μA
		T _A = -40°C to +125°C	380		650	

MAX6043

Precision High-Voltage Reference in SOT23

ELECTRICAL CHARACTERISTICS— $V_{OUT} = +4.096V$

($V_{IN} = +10V$, $I_{OUT} = 0$, $T_A = T_{MIN}$ to T_{MAX} . Typical values are at $T_A = +25^\circ C$, unless otherwise noted.) (Note 1)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
OUTPUT					
Output Voltage	$I_{OUT} = 0$, $T_A = +25^\circ C$	MAX6043A (0.06%)	4.0935	4.0960	4.0985
		MAX6043B (0.1%)	4.0919	4.0960	4.1001
		MAX6043C (0.5%)	4.0755	4.0960	4.1165
Output-Voltage Temperature Coefficient (Note 2)	$T_A = -40^\circ C$ to $+125^\circ C$	MAX6043A_41	3	15	ppm/ $^\circ C$
		MAX6043B_41	5	25	
		MAX6043C_41	10	65	
Line Regulation (Note 4)	$6.1V \leq V_{IN} \leq 40V$	$T_A = +25^\circ C$	1	6	ppm/V
		$T_A = -40^\circ C$ to $+125^\circ C$	1.5	10	
Load Regulation (Note 4)	Sourcing, $0 \leq I_{OUT} \leq 10mA$	$T_A = +25^\circ C$	19	70	ppm/mA
		$T_A = -40^\circ C$ to $+125^\circ C$		70	
	Sinking, $-0.6mA \leq I_{OUT} \leq 0mA$	$T_A = +25^\circ C$	100	900	
		$T_A = -40^\circ C$ to $+125^\circ C$		900	
OUT Short-Circuit Current	OUT shorted to GND		60		mA
	OUT shorted to IN		-2		
Thermal Hysteresis	(Note 3)		150		ppm
Long-Term Stability	$\Delta t = 1000hr$		150		ppm
DYNAMIC CHARACTERISTICS					
Output Noise Voltage	0.1Hz to 10Hz		6.6		μV_{P-P}
	10Hz to 1kHz		12		μV_{RMS}
Turn-On Settling Time	To $V_{OUT} = 0.05\%$ of final value, $C_{OUT} = 50pF$		200		μs
INPUT					
Supply Voltage Range	Inferred from line regulation test	6.1		40.0	V
Quiescent Supply Current	$I_{OUT} = 0$	$T_A = +25^\circ C$	320	490	μA
		$T_A = -40^\circ C$ to $+125^\circ C$	380	650	

MAX6043

Precision High-Voltage Reference in SOT23

ELECTRICAL CHARACTERISTICS— $V_{OUT} = +5.0V$

($V_{IN} = +15V$, $I_{OUT} = 0$, $T_A = T_{MIN}$ to T_{MAX} . Typical values are at $T_A = +25^\circ C$, unless otherwise noted.) (Note 1)

PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
OUTPUT						
Output Voltage	I _{OUT} = 0, T _A = +25°C	MAX6043A (0.06%)	4.9970	5.0000	5.0030	V
		MAX6043B (0.1%)	4.9950	5.0000	5.0050	
		MAX6043C (0.5%)	4.9751	5.0000	5.0250	
Output-Voltage Temperature Coefficient (Note 2)	T _A = -40°C to +125°C	MAX6043A_50	3		15	ppm/°C
		MAX6043B_50	5		25	
		MAX6043C_50	10		65	
Line Regulation (Note 4)	7V ≤ V _{IN} ≤ 40V	T _A = +25°C	1		6	ppm/V
		T _A = -40°C to +125°C	1.5		10	
Load Regulation (Note 4)	Sourcing, 0 ≤ I _{OUT} ≤ 10mA	T _A = +25°C	32		70	ppm/mA
		T _A = -40°C to +125°C			70	
	Sinking, -0.6mA ≤ I _{OUT} ≤ 0mA	T _A = +25°C	130		900	
		T _A = -40°C to +125°C			900	
OUT Short-Circuit Current	OUT shorted to GND		60			mA
	OUT shorted to IN		-2			
Thermal Hysteresis	(Note 3)		150			ppm
Long-Term Stability	Δt = 1000hr		150			ppm
DYNAMIC CHARACTERISTICS						
Output Noise Voltage	0.1Hz to 10Hz		9.5			μV _{P-P}
	10Hz to 1kHz		15			μV _{RMS}
Turn-On Settling Time	To V _{OUT} = 0.05% of final value, C _{OUT} = 50pF		230			μs
INPUT						
Supply Voltage Range	Inferred from line regulation test		7.0		40.0	V
Quiescent Supply Current	I _{OUT} = 0	T _A = +25°C	320		490	μA
		T _A = -40°C to +125°C	380		650	

MAX6043

Precision High-Voltage Reference in SOT23

ELECTRICAL CHARACTERISTICS— $V_{OUT} = +10.0V$

($V_{IN} = +15V$, $I_{OUT} = 0$, $T_A = T_{MIN}$ to T_{MAX} . Typical values are at $T_A = +25^\circ C$, unless otherwise noted.) (Note 1)

PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
OUTPUT						
Output Voltage	I _{OUT} = 0, T _A = +25°C	MAX6043A (0.05%)	9.9950	10.0000	10.0050	V
		MAX6043B (0.1%)	9.9900	10.0000	10.0100	
		MAX6043C (0.5%)	9.9500	10.0000	10.0500	
Output-Voltage Temperature Coefficient (Note 2)	T _A = -40°C to +125°C	MAX6043A_10		3	15	ppm/°C
		MAX6043B_10		5	25	
		MAX6043C_10		10	65	
Line Regulation (Note 4)	12V ≤ V _{IN} ≤ 40V	T _A = +25°C		1	6	ppm/V
		T _A = -40°C to +125°C		1.5	10	
Load Regulation (Note 4)	Sourcing, 0 ≤ I _{OUT} ≤ 10mA	T _A = +25°C		16	70	ppm/mA
		T _A = -40°C to +125°C			70	
	Sinking, -0.6mA ≤ I _{OUT} ≤ 0mA	T _A = +25°C		170	900	
		T _A = -40°C to +125°C			900	
OUT Short-Circuit Current	OUT shorted to GND			60		mA
	OUT shorted to IN			-2		
Thermal Hysteresis	(Note 3)			150		ppm
Long-Term Stability	Δt = 1000hr			150		ppm
DYNAMIC CHARACTERISTICS						
Output Noise Voltage	0.1Hz to 10Hz			19		μV _{P-P}
	10Hz to 1kHz			30		μV _{RMS}
Turn-On Settling Time	To V _{OUT} = 0.05% of final value, C _{OUT} = 50pF			390		μs
INPUT						
Supply Voltage Range	Inferred from line regulation test		12.0		40.0	V
Quiescent Supply Current	I _{OUT} = 0	T _A = +25°C		320	490	μA
		T _A = -40°C to +125°C		390	650	

Note 1: All devices are 100% production tested at $T_A = +25^\circ C$ and guaranteed by design over $T_A = T_{MIN}$ to T_{MAX} as specified.

Note 2: Temperature coefficient is defined as ΔV_{OUT} divided by the temperature range.

Note 3: Thermal hysteresis defined as the change in output voltage at $T_A = +25^\circ C$ before and after cycling the device from T_{MAX} to T_{MIN} .


Note 4: Line and load regulation do not include the effect of self heating.

Precision High-Voltage Reference in SOT23


Typical Operating Characteristics

($V_{IN} = +5V$ for $V_{OUT} = +2.5V$, $V_{IN} = +10V$ for $V_{OUT} = +3.3V$ or $+4.096V$, $V_{IN} = +15V$ for $V_{OUT} = +5V$ or $+10V$, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)


OUTPUT VOLTAGE vs. TEMPERATURE
($V_{OUT} = 2.5V$)




OUTPUT VOLTAGE vs. TEMPERATURE
($V_{OUT} = 10V$)




LOAD REGULATION
(SOURCING, $V_{OUT} = 10V$)




LOAD REGULATION
(SOURCING, $V_{OUT} = 2.5V$)




LOAD REGULATION
(SINKING, $V_{OUT} = 10V$)




LOAD REGULATION
(SINKING, $V_{OUT} = 2.5V$)




LINE REGULATION
($V_{OUT} = 2.5V$)



LINE REGULATION
($V_{OUT} = 10V$)



MINIMUM INPUT-OUTPUT DIFFERENTIAL
vs. LOAD CURRENT ($V_{OUT} = 2.5V$)




MAX6043

Precision High-Voltage Reference in SOT23


Typical Operating Characteristics (continued)

($V_{IN} = +5V$ for $V_{OUT} = +2.5V$, $V_{IN} = +10V$ for $V_{OUT} = +3.3V$ or $+4.096V$, $V_{IN} = +15V$ for $V_{OUT} = +5V$ or $+10V$, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)


**MINIMUM INPUT-OUTPUT DIFFERENTIAL
vs. LOAD CURRENT ($V_{OUT} = 10V$)**




**POWER-SUPPLY REJECTION RATIO
vs. FREQUENCY ($V_{OUT} = 2.5V$)**




**POWER-SUPPLY REJECTION RATIO
vs. FREQUENCY ($V_{OUT} = 10V$)**




**OUTPUT IMPEDANCE
vs. FREQUENCY**




**SUPPLY CURRENT vs. INPUT VOLTAGE
($V_{OUT} = 2.5V$)**




**SUPPLY CURRENT vs. INPUT VOLTAGE
($V_{OUT} = 10V$)**




**SUPPLY CURRENT vs. TEMPERATURE
($V_{OUT} = 2.5V$)**



**SUPPLY CURRENT vs. TEMPERATURE
($V_{OUT} = 10V$)**



**OUTPUT NOISE-VOLTAGE DENSITY
vs. FREQUENCY**




Precision High-Voltage Reference in SOT23


Typical Operating Characteristics (continued)

($V_{IN} = +5V$ for $V_{OUT} = +2.5V$, $V_{IN} = +10V$ for $V_{OUT} = +3.3V$ or $+4.096V$, $V_{IN} = +15V$ for $V_{OUT} = +5V$ or $+10V$, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)


**0.1Hz TO 10Hz OUTPUT NOISE
($V_{OUT} = 2.5V$)**




**0.1Hz TO 10Hz OUTPUT NOISE
($V_{OUT} = 10V$)**




**LOAD TRANSIENT
($V_{OUT} = 2.5V$)**




**LOAD TRANSIENT
($V_{OUT} = 10V$)**



**LOAD TRANSIENT
($V_{OUT} = 2.5V$)**



**LOAD TRANSIENT
($V_{OUT} = 10V$)**




MAX6043

Precision High-Voltage Reference in SOT23


Typical Operating Characteristics (continued)

($V_{IN} = +5V$ for $V_{OUT} = +2.5V$, $V_{IN} = +10V$ for $V_{OUT} = +3.3V$ or $+4.096V$, $V_{IN} = +15V$ for $V_{OUT} = +5V$ or $+10V$, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)


**LOAD TRANSIENT
($V_{OUT} = 2.5V$)**




**LOAD TRANSIENT
($V_{OUT} = 10V$)**




**LOAD TRANSIENT
($V_{OUT} = 2.5V$)**




**LOAD TRANSIENT
($V_{OUT} = 10V$)**




**LINE TRANSIENT
($V_{OUT} = 2.5V$)**




**LINE TRANSIENT
($V_{OUT} = 10V$)**



**TURN-ON TRANSIENT
($V_{OUT} = 2.5V$)**



**TURN-ON TRANSIENT
($V_{OUT} = 10V$)**




Precision High-Voltage Reference in SOT23


Typical Operating Characteristics (continued)

($V_{IN} = +5V$ for $V_{OUT} = +2.5V$, $V_{IN} = +10V$ for $V_{OUT} = +3.3V$ or $+4.096V$, $V_{IN} = +15V$ for $V_{OUT} = +5V$ or $+10V$, $I_{OUT} = 0$, $T_A = +25^\circ C$, unless otherwise noted.)


TURN-ON TRANSIENT
($V_{OUT} = 2.5V$)




TURN-ON TRANSIENT
($V_{OUT} = 10V$)




TURN-OFF TRANSIENT
($V_{OUT} = 2.5V$)




TURN-OFF TRANSIENT
($V_{OUT} = 10V$)




TURN-OFF TRANSIENT
($V_{OUT} = 2.5V$)




TURN-OFF TRANSIENT



LONG-TERM DRIFT
($V_{OUT} = 2.5V$)



LONG-TERM DRIFT
($V_{OUT} = 10V$)



MAX6043

Precision High-Voltage Reference in SOT23

Pin Description

PIN	NAME	FUNCTION
1, 3	I.C.	Internally Connected. Do not connect externally.
2	GND	Ground
4	IN	Positive Power-Supply Input
5	OUTF	Voltage-Reference Force Output. Connect OUTF to OUTS as close to the device as possible. OUTF and OUTS do not require a bypass capacitor for stability.
6	OUTS	Voltage-Reference Sense Input

Applications Information

Bypassing/Output Capacitance

For the best line-transient performance, decouple the input with a 0.1 μ F ceramic capacitor as shown in the *Typical Operating Circuit*. Place the capacitor as close to IN as possible. When transient performance is less important, no capacitor is necessary.

The MAX6043 does not require an output capacitor for stability and is stable with capacitive loads up to 100 μ F. In applications where the load or the supply can experience step changes, a larger output capacitor reduces the amount of overshoot (undershoot) and improves the circuit's transient response. Place output capacitors as close to the device as possible for best performance.

Supply Current

The MAX6043 consumes 320 μ A of quiescent supply current. This improved efficiency reduces power dissipation and extends battery life.

Thermal Hysteresis

Thermal hysteresis is the change in the output voltage at $T_A = +25^\circ\text{C}$ before and after the device is cycled over its entire operating temperature range. Hysteresis is caused by differential package stress appearing across the bandgap core transistors. The typical thermal hysteresis value is 150ppm.

Turn-On Time

The MAX6043 typically turns on and settles to within 0.05% of the preset output voltage in 150 μ s.

Short-Circuited Outputs

The MAX6043 features a short-circuit-protected output. Internal circuitry limits the output current to 60mA when short-circuiting the output.

Temperature Coefficient vs. Operating Temperature Range for a 1 LSB Maximum Error

In a data converter application, the reference voltage of the converter must stay within a certain limit to keep the error in the data converter smaller than the resolution limit through the operating temperature range. Figure 1 shows the maximum allowable reference-voltage temperature coefficient to keep the conversion error to less than 1 LSB, as a function of the operating temperature range ($T_{MAX} - T_{MIN}$) with the converter resolution as a parameter. The graph assumes the reference-voltage temperature coefficient as the only parameter affecting accuracy.

In reality, the absolute static accuracy of a data converter is dependent on the combination of many parameters such as integral nonlinearity, differential nonlinearity, offset error, gain error, as well as voltage-reference changes.

MAX6043

Precision High-Voltage Reference in SOT23





Figure 1. Temperature Coefficient vs. Operating Temperature Range for a 1 LSB Maximum Error

Typical Operating Circuit



MAX6043

Precision High-Voltage Reference in SOT23

Ordering Information (continued)

PART	OUTPUT VOLTAGE (V)	TEMPCO (PPM/°C)	INITIAL ACCURACY (%)	TOP MARK
MAX6043CAUT33#TG16	3.300	65	0.50	#ACMM
MAX6043AAUT41-T	4.096	15	0.06	ABSB
MAX6043AAUT41#TG16	4.096	15	0.06	#ACMN
MAX6043BAUT41-T	4.096	20	0.10	ABDU
MAX6043BAUT41#TG16	4.096	20	0.10	#ACMO
MAX6043CAUT41-T	4.096	65	0.50	ABDV
MAX6043CAUT41#TG16	4.096	65	0.50	#ACMP
MAX6043AAUT50-T	5.000	15	0.06	ABSC
MAX6043AAUT50#TG16	5.000	15	0.06	#ACMQ
MAX6043BAUT50-T	5.000	20	0.10	ABDW
MAX6043BAUT50#TG16	5.000	20	0.10	#ACMR
MAX6043CAUT50-T	5.000	65	0.50	ABDX
MAX6043CAUT50#TG16	5.000	65	0.50	#ACMS
MAX6043AAUT10-T	10.000	15	0.06	ABSD
MAX6043AAUT10#TG16	10.000	15	0.06	#ACMT
MAX6043BAUT10-T	10.000	20	0.10	ABDY
MAX6043BAUT10#TG16	10.000	20	0.10	#ACMU
MAX6043CAUT10-T	10.000	65	0.50	ABDZ
MAX6043CAUT10#TG16	10.000	65	0.50	#ACMV

#Denotes an RoHS-compliant device that may include lead that is exempt under the RoHS requirements.

T = Tape and reel.

Chip Information

PROCESS: BiCMOS

Package Information

For the latest package outline information and land patterns (footprints), go to www.maximintegrated.com/packages. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

PACKAGE TYPE	PACKAGE CODE	OUTLINE NO.	LAND PATTERN NO.
6 SOT23	U6FH-6	21-0058	90-0175

MAX6043

Precision High-Voltage Reference in SOT23

Revision History

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	11/03	Initial release	—
1	5/04	Added future product information, updated the <i>Electrical Characteristics</i> and <i>Typical Operating Characteristics</i> .	1–6, 11, 12
2	8/12	Updated the <i>Ordering Information/Selector Guide</i> , <i>Absolute Maximum Ratings</i> , and the <i>Package Information</i> sections.	1, 14, 15



Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.

Maxim Integrated 160 Rio Robles, San Jose, CA 95134 USA 1-408-601-1000

15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Maxim Integrated:

[MAX6043AAUT10#TG16](#) [MAX6043AAUT25#TG16](#) [MAX6043AAUT33#TG16](#) [MAX6043AAUT41#TG16](#)
[MAX6043AAUT50#TG16](#) [MAX6043BAUT10#TG16](#) [MAX6043BAUT25#TG16](#) [MAX6043BAUT33#TG16](#)
[MAX6043BAUT41#TG16](#) [MAX6043BAUT50#TG16](#) [MAX6043CAUT10#TG16](#) [MAX6043CAUT25#TG16](#)
[MAX6043CAUT33#TG16](#) [MAX6043CAUT41#TG16](#) [MAX6043CAUT50#TG16](#) [REF02DP+](#) [MAX6043AAUT10-T](#)
[MAX6043AAUT25-T](#) [MAX6043AAUT33-T](#) [MAX6043AAUT41-T](#) [MAX6043AAUT50-T](#) [MAX6043BAUT25-T](#)
[MAX6043BAUT33-T](#) [MAX6043BAUT50-T](#) [MAX6043CAUT10-T](#) [MAX6043CAUT50-T](#) [MAX6043BAUT10](#)
[MAX6043BAUT10-T](#) [MAX6043BAUT41-T](#)