

PRODUCT NUMBER
76341-YXXXLF

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 5.

OPTIONAL LETTER
H: HIGH TEMPERATURE PRODUCT.

NUMBER OF POSITIONS: 02 TO 50.

PLATING CODE

3= 0.76µm GOLD ON CONTACT AREA.

3.81µm TIN-LEAD ON TAIL.

4= 5µm TIN-LEAD ON CONTACT AREA.

3.81µm TIN-LEAD ON TAIL.

WHEN SUFFIX "LF" IS REQUIRED, 2µm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-0
LOW TEMPERATURE: COLOR BLUE
HIGH TEMPERATURE: COLOR GREY.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.
5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.
- 4 - TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS
EXAMPLE: 8 POS: $(N \times 2.54) - 0.08 = 20.24$ mm
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY




- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELING:



- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-22-008

- 6 - END STAND-OFFS FOR 1x2 UP TO 1x5 POS
NO END STAND-OFFS FOR 1x6 UP TO 1x50 POS



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family DUBOX
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title
P	F11-0043	JCO	12.02.22	angles	linear		BtB RECEPT. VERT SR TMT
J	F80115	PNZ	98.01.22	±2'		scale 5:1	
K	F10110	GCO	01.01.16	dr	D LEGRAND	04.09.27	dwg no
L	F03-0284	DLE	03.10.07	enr	P NIZZI	04.09.27	sheet 1 of 2
M	F04-0347	DLE	04.09.27	chr	D LEGRAND	04.09.27	size
N	F06-0204	DLE	06.06.20	appd	P NZ	04.09.27	76341
sheet	revision	P	B				A3
index	sheet	1	2				
							type
							CUSTOMER
							Drawing



Fcconnect.com



PDM: Rev:P

STATUS: Released

Printed: Mar 20, 2012

Copyright FCI

mat'l. code SEE SHEET 1				surface ISO 1302		tolerance ISO 406 ISO 1101		projection		product family DUBOX	
ltr	ecn no	dr	date	tolerances unless otherwise specified		otherwise specified				title	
A	F04-0347	DLE	04.09.27	angles		±0.3		mm		BtB RECEPT. VERT SR TMT	
B	F06-0204	DLE	06.06.20	linear				scale 5:1		dwg no	
				±2°						sheet 2 of 2 size	
				dr	D LEGRAND	04.09.27				76341	
				engr	P NIZZI	04.09.27				CUSTOMER	
				chr	D LE	04.09.27				Drawing	
				appd	P NZ	04.09.27					
sheet index	revision										
	sheet										

form: A4