


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT INVENTORY NUMBERING SYSTEM



PANDUIT PART NUMBER	Min. Exp. I.D In. (mm)	Max. Rec. I.D In. (mm)	NOMINAL REC WALL THICKNESS In. (mm)
HST0.4 - - - (Y)	0.400 (10.2)	0.160 (4.1)	0.08 (2.0)
HST0.8 - - - (Y)	0.750 (19.1)	0.220 (5.6)	0.09 (2.3)
HST1.1 - - - (Y)	1.100 (27.9)	0.375 (9.5)	0.12 (3.0)
HST1.5 - - - (Y)	1.500 (38.1)	0.500 (12.7)	0.16 (4.1)
HST2.0 - - - (Y)	2.000 (50.8)	0.666 (16.9)	0.16 (4.1)
HST2.7 - - - (Y)	2.700 (68.6)	.870 (22.1)	0.16 (4.1)
HST3.0 - - - - -	3.000 (76.2)	1.000 (25.4)	0.16 (4.1)
HST3.5 - - - (Y)	3.500 (88.9)	1.200 (30.5)	0.16 (4.1)

(D) (D) (D) (D) (D) (F) (C)

NOTES:

- (B)
1. APPROXIMATE SHRINK RATIO: 3:1 (EXPANDED: RECOVERED 1D)
 2. SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO TABLE 1 FOR THE EXACT MINIMUM EXPANDED AND MAXIMUM RECOVERED I.D.'S.
 3. MATERIAL: CROSSLINKED POLYOLEFIN
 4. COLOR: BLACK AND RED
 5. "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"
 - 1 6. ALL PARTS ARE ROHS COMPLIANT

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
--	----	--	--	1 ADDED NOTE #6 H CHANGED Y:1 (ROHS COMPLIANT) TO INTERNAL CODE F PUT HST3.0 BACK ON DRAWING				
3	2/25/11	LEF		GB0239KM	3		RAMI	
--	----	--	--	2 ADDED Y:ROHS 3 CHANGED NOTE 1 4 ADDED LINES HST2.7 & 3.5 5 DIM. CHANGES 6 REMOVED HST 3.0 LINE	--	--	--	--
2	10/12/10	LEF		GB0239KM	2		RAMI	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP

DIMENSIONS IN BRACKETS ARE METRIC (mm)	
C/D FILENAME/LAYERS G03597HN_DC_GB0239KM/03	
PANDUIT CORP. TINLEY PARK, ILLINOIS	
HST THICK WALL ADHESIVE LINED HEAT SHRINK	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.XX) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (1.XX) ±0.02 (0.5) ANGLES ± 5°	
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY LEF	MAT'L:
DATE 10/12/10	SCALE NONE
CHK'D JVL	DWG A
SEE NOTES	
GB0239KM	
SIZE	