



REV	ECN	APP'D
A	5722	




WHITE MARKING
PER AW-2302



SCALE 1:1

NOTES:

- MATERIALS:**
BODY: POLYETHERIMIDE PER MIL-P-46184.
GROMMET: SILICONE BLEND ELASTOMER.
DIODE: MIL-S-19500 (SEE TABLE)
INTERNAL PIN CONTACT:
COPPER ALLOY, HARD GOLD PLATE PER MIL-G-45204.
- PERFORMANCE SPECIFICATION PER MIL-T-81714.**
(SUBJECT TO LIMITATIONS OF THE
ELECTRONIC COMPONENTS)
TEMPERATURE: -65°C TO 200°C.
INSULATION RESISTANCE: 5000 MEGOHMS MIN AT 25°C.
DIELECTRIC WITHSTANDING VOLTAGE:
1500 VRMS AT SEA LEVEL,
AND 200 VRMS AT 100,000 FT. ALTITUDE.
CURRENT RATING: 7.5A FOR SIZE 20 CONTACTS.
VIBRATION AND SHOCK: PER MIL-T-81714 PARA 3.5.8 & 9.
- MODULE ACCEPTS SOCKET CONTACTS (10) M39029/22-192.
- MODULE TO BE MOUNTED ON M81714/67 RAIL SYSTEM.



1.170 MAX

1.140 MAX



SJE020026
58982
APCD XXXX

DATE CODE
.06 HIGH MARKING
COLOR: WHITE

.672±.010

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd		ELECTRONIC MODULE			
			SPECIFICATION DRAWING		51.1 OHM			
ANSI Y14.5M	.XX ±0.01		DRWN		1/8 W			
UNITS: INCHES	.XXX ±0.005		J. TON 01/17/02					
Pro/E FILE	ANGLES ±1.0°		ENGR		SIZE	DWG NO.		REV
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD, BEVERLY, MA			A. PATRIE 1-14-02		A	SJE020026_C		A
			J. TON 1-14-02		CODE: 58982		SCALE: 2:1	SHEET 1 OF 1