



## General Description

The DSC1001 is a silicon MEMS based CMOS oscillator offering excellent jitter and stability performance over a wide range of supply voltages and temperatures. The device operates from 1 to 150MHz with supply voltages between 1.8 to 3.3 Volts and temperature ranges up to -40°C to 105°C.

The DSC1001 incorporates an all silicon resonator that is extremely robust and nearly immune to stress related fractures, common to crystal based oscillators. Without sacrificing the performance and stability required of today's systems, a crystal-less design allows for a higher level of reliability, making the DSC1001 ideal for rugged, industrial, and portable applications where stress, shock, and vibration can damage quartz crystal based systems.

Available in industry standard packages, the DSC1001 can be "dropped-in" to the same PCB footprint as standard crystal oscillators.

## Block Diagram



## Features

- Frequency Range: 1 to 150MHz
- Exceptional Stability over Temperature
  - $\pm 10$  PPM,  $\pm 25$  PPM,  $\pm 50$  PPM
- Operating voltage
  - 1.7 to 3.6V
- Operating Temperature Range
  - Ext. Industrial -40°C to 105°C
  - Industrial -40°C to 85°C
  - Ext. Commercial -20°C to 70°C
  - Commercial 0°C to 70°C
- Low Operating and Standby Current
  - 5mA Operating (40MHz)
  - 15uA Standby
- Ultra Miniature Footprint
  - 2.5 x 2.0 x 0.85 mm
  - 3.2 x 2.5 x 0.85 mm
  - 5.0 x 3.2 x 0.85 mm
  - 7.0 x 5.0 x 0.85 mm
- MIL-STD 883 Shock and Vibration Resistant
- Pb Free, RoHS, Reach SVHC Compliant
- AEC-Q100 Reliability Qualified

## Benefits

- Pin for pin "drop in" replacement for industry standard oscillators
- Semiconductor level reliability, significantly higher than quartz
- Short mass production lead-times
- Longer Battery Life / Reduced Power
- Compact Plastic package
- Cost Effective

## Applications

- Mobile Applications
- Consumer Electronics
- Portable Electronics
- DVR, CCTV, Surveillance Cameras
- Low Profile Applications
- Industrial Applications

## Absolute Maximum Ratings<sup>1</sup>

| Item           | Min  | Max     | Unit | Condition   |
|----------------|------|---------|------|-------------|
| Input Voltage  | -0.3 | VDD+0.3 | V    |             |
| Junction Temp  | -    | +150    | °C   |             |
| Storage Temp   | -55  | +150    | °C   |             |
| Soldering Temp | -    | +260    | °C   | 40 sec max. |
| ESD            | -    |         | V    |             |
| HBM            |      | 4000    |      |             |
| MM             |      | 200     |      |             |
| CDM            |      | 1500    |      |             |

## Ordering Code



\* See Ordering Information for details

## Recommended Operating Conditions

| Parameter             | Symbol          | Range          |
|-----------------------|-----------------|----------------|
| Supply Voltage        | V <sub>DD</sub> | 1.7 – 3.6V     |
| Output Load           | Z <sub>L</sub>  | R>10KΩ, C≤15pF |
| Operating Temperature | T               | -40 to +105 °C |
| Option 1              |                 | -40 to +85 °C  |
| Option 2              |                 | -20 to +70 °C  |
| Option 3              |                 | 0 to +70 °C    |
| Option 4              |                 |                |

## Specifications (VDD = 1.8 to 3.3v) T<sub>A</sub>=85°C unless otherwise specified

| Parameter                        | Symbol                             | Condition                                                                                    | Min                       | Typ | Max                        | Unit  |
|----------------------------------|------------------------------------|----------------------------------------------------------------------------------------------|---------------------------|-----|----------------------------|-------|
| Frequency                        | f <sub>0</sub>                     | Single Frequency                                                                             | 1                         |     | 150                        | MHz   |
| Frequency Tolerance              | Δf                                 | Includes frequency variations due to initial tolerance, temperature and power supply voltage |                           |     | ±10,±25,±50                | ppm   |
| Aging                            | Δf                                 | 1 year @25°C                                                                                 |                           |     | ±5                         | ppm   |
| Supply Current, standby          | I <sub>DD</sub>                    | T=25°C                                                                                       |                           |     | 15                         | uA    |
| Output Logic Levels              | V <sub>OH</sub><br>V <sub>OL</sub> | -4mA<br>4mA                                                                                  | 0.8*V <sub>DD</sub><br>-  |     | -<br>0.2*V <sub>DD</sub>   | Volts |
| Output logic high                |                                    |                                                                                              |                           |     |                            |       |
| Output logic low                 |                                    |                                                                                              |                           |     |                            |       |
| Output Startup Time <sup>2</sup> | t <sub>SU</sub>                    | T=25°C                                                                                       |                           | 1.0 | 1.3                        | ms    |
| Output Disable Time              | t <sub>DA</sub>                    |                                                                                              |                           | 20  | 100                        | ns    |
| Output Duty Cycle                | SYM                                |                                                                                              | 45                        |     | 55                         | %     |
| Input Logic Levels               | V <sub>IH</sub><br>V <sub>IL</sub> |                                                                                              | 0.75*V <sub>DD</sub><br>- |     | -<br>0.25* V <sub>DD</sub> | Volts |
| Input logic high                 |                                    |                                                                                              |                           |     |                            |       |
| Input logic low                  |                                    |                                                                                              |                           |     |                            |       |

**VDD = 1.8v**

| Parameter                                        | Symbol         | Condition                                         |                                  | Min | Typ                      | Max                      | Unit |
|--------------------------------------------------|----------------|---------------------------------------------------|----------------------------------|-----|--------------------------|--------------------------|------|
| Supply Current, no load                          | $I_{DD}$       | $C_L=0p$<br>$R_L=\infty$<br>$T=25^{\circ}C$       | 1MHz<br>27MHz<br>70MHz<br>150MHz |     | 6.0<br>6.5<br>7.2<br>8.3 | 6.3<br>6.9<br>7.5<br>9.1 | mA   |
| Output Transition time<br>Rise Time<br>Fall Time | $t_R$<br>$t_F$ | $C_L=15pF$ ; $T=25^{\circ}C$<br>20%/80%* $V_{DD}$ |                                  |     | 1.8<br>1.0               | 3<br>3                   | ns   |
| Jitter, Max Cycle to Cycle                       | $J_{CC}$       | $F = 100MHz^3$                                    |                                  |     | 60                       |                          | Ps   |

**VDD = 2.5v**

| Parameter                                        | Symbol         | Condition                                         |                                  | Min | Typ                      | Max                       | Unit |
|--------------------------------------------------|----------------|---------------------------------------------------|----------------------------------|-----|--------------------------|---------------------------|------|
| Supply Current, no load                          | $I_{DD}$       | $C_L=0p$<br>$R_L=\infty$<br>$T=25^{\circ}C$       | 1MHz<br>27MHz<br>70MHz<br>150MHz |     | 6.0<br>6.7<br>7.7<br>9.6 | 6.3<br>7.0<br>8.1<br>10.6 | mA   |
| Output Transition time<br>Rise Time<br>Fall Time | $t_R$<br>$t_F$ | $C_L=15pF$ ; $T=25^{\circ}C$<br>20%/80%* $V_{DD}$ |                                  |     | 1.0<br>0.9               | 2<br>2                    | ns   |
| Jitter, Max Cycle to Cycle                       | $J_{CC}$       | $F = 100MHz^3$                                    |                                  |     | 50                       |                           | ps   |

**VDD = 3.3v**

| Parameter                                        | Symbol         | Condition                                         |                                  | Min | Typ                       | Max                       | Unit |
|--------------------------------------------------|----------------|---------------------------------------------------|----------------------------------|-----|---------------------------|---------------------------|------|
| Supply Current, no load                          | $I_{DD}$       | $C_L=0p$<br>$R_L=\infty$<br>$T=25^{\circ}C$       | 1MHz<br>27MHz<br>70MHz<br>150MHz |     | 6.0<br>6.8<br>8.2<br>10.8 | 6.3<br>7.2<br>8.7<br>12.2 | mA   |
| Output Transition time<br>Rise Time<br>Fall Time | $t_R$<br>$t_F$ | $C_L=15pF$ ; $T=25^{\circ}C$<br>20%/80%* $V_{DD}$ |                                  |     | 1.0<br>0.9                | 2<br>2                    | ns   |
| Jitter, Max Cycle to Cycle                       | $J_{CC}$       | $F = 100MHz^3$                                    |                                  |     | 50                        |                           | ps   |

## Notes:

1. Absolute maximum ratings are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated beyond these limits.
2.  $t_{SU}$  is time to stable output frequency after  $V_{DD}$  is applied.  $t_{SU}$  and  $t_{EN}$  (after EN is asserted) are identical values.
3. Measured over 50k clock cycles.

## Nominal Performance Characteristics

### Supply Current



### Supply Current



### Rise Time



### Fall Time




### Rise Time



### Fall Time




## Output Waveform



## Standby Function

| Standby#<br>(pin 1)  | Output<br>(pin 3) |
|----------------------|-------------------|
| Hi Level             | Output ON         |
| Open<br>(no connect) | Output ON         |
| Low Level            | High Impedance    |

## Test Circuit



## Board Layout (recommended)



## Solder Reflow Profile




| MSL 1 @ 260°C refer to JSTD-020C  |              |
|-----------------------------------|--------------|
| Ramp-Up Rate (200°C to Peak Temp) | 3°C/Sec Max. |
| Preheat Time 150°C to 200°C       | 60-180 Sec   |
| Time maintained above 217°C       | 60-150 Sec   |
| Peak Temperature                  | 255-260°C    |
| Time within 5°C of actual Peak    | 20-40 Sec    |
| Ramp-Down Rate                    | 6°C/Sec Max. |
| Time 25°C to Peak Temperature     | 8 min Max.   |

## Package Dimensions


### 7.0 x 5.0 mm Plastic Package

#### External Dimensions



| No. | Pin Terminal |
|-----|--------------|
| 1   | Standby#     |
| 2   | GND          |
| 3   | Output       |
| 4   | VDD          |

#### Recommended Land Pattern\*





\*Note: The center pad is not connected internally and should be left unconnected or tied to GND.

units: mm [inch]

### 5.0 x 3.2 mm Plastic Package

#### External Dimensions



| No. | Pin Terminal |
|-----|--------------|
| 1   | Standby#     |
| 2   | GND          |
| 3   | Output       |
| 4   | VDD          |

#### Recommended Land Pattern



units: mm [inch]

### 3.2 x 2.5 mm Plastic Package

#### External Dimensions



| No. | Pin Terminal |
|-----|--------------|
| 1   | Standby#     |
| 2   | GND          |
| 3   | Output       |
| 4   | VDD          |

#### Recommended Land Pattern



units: mm [inch]

### 2.5 x 2.0 mm Plastic Package

#### External Dimensions



| No. | Pin Terminal |
|-----|--------------|
| 1   | Standby#     |
| 2   | GND          |
| 3   | Output       |
| 4   | VDD          |

#### Recommended Land Pattern



units: mm [inch]

## Ordering Information

### DSC1001 PTS – xxx.xxxx T

| PART NUMBERING GUIDE                                                                             |                                                                                                                 |                                                                |                 |                                              |
|--------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------|-----------------|----------------------------------------------|
| Package<br>(Plastic QFN)                                                                         | Temperature                                                                                                     | Stability                                                      | Frequency       | Packing Option                               |
| <b>P=A:</b> 7.0x5.0mm<br><b>P=B:</b> 5.0x3.2mm<br><b>P=C:</b> 3.2x2.5mm<br><b>P=D:</b> 2.5x2.0mm | <b>T=C:</b> 0° ~ +70° C<br><b>T=E:</b> -20° ~ +70° C<br><b>T=I:</b> -40° ~ +85° C<br><b>T=L:</b> -40° ~ +105° C | <b>S=1:</b> ±50ppm<br><b>S=2:</b> ±25ppm<br><b>S=5:</b> ±10ppm | <b>XXX.XXXX</b> | <b>Blank:</b> Tubes<br><b>T:</b> Tape & Reel |

Example: DSC1001CE1-123.0000T

The example part number above is a 123.0000MHz oscillator in Plastic 3.2x2.5mm package, with ±50ppm stability over an operating temperature of -20 to +70°C, shipped in Tape and Reel.

### **Disclaimer:**

Discera makes no warranty of any kind, express or implied, with regard to this material, including, but not limited to, the implied warranties of merchantability and fitness for a particular purpose. Discera reserves the right to make changes without further notice to materials described herein. Discera does not assume any liability arising from the application or use of any product or circuit described herein. Discera does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Discera's product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Discera against all charges.