FAX: 773 792-2129

* Please visit the product pages on our website for the most up-to-date product information

PQG® RECEPTACLES ...











PQG3FRA112

PQG3MRA112

PQG3FST112

PQG3MST112

Q-G® 3 pin/contact PC receptacles offer economy, reliability and performance in amplifiers, audio mixing boards, and other outboard gear. Choose receptacles with just the right combination of standard and optional bonus features to tailor the PQG series to your exact needs.

STANDARD FEATURES

- UL 94V-0 plastic materials.
- Circuit #1 "makes" first and "breaks" last during connect/disconnect.
- · Positive mechanical polarization.
- · Minimum PC board space required.
- Integral PC board locating posts.
- Mating/unmating cycles in excess of 10,000.
- Mates with Switchcraft Q-G and other compatible connectors.

OPTIONAL FEATURES

- Positive latch lock or FasDisconnect (female only).
- Shell-to-ground terminal.
- Mounting Plates:
 - A. Backup Mounting Plate with two, M3 x 0.5 threaded holes for faster, more rugged mounting to equipment panel/chassis.
 - B. "Tri-Mounting" Plate...plus two bifurcated pcb retainers with snap-in terminals which perform three valuable functions:
 - 1. Provide ground connection from panel to PCB.
 - 2. Hold connector securely to PCB during wave-soldering.
 - 3. Add strength between panel/chassis and PCB during soldering by "wicking" solder through the PCB and up sides of retainers to assure continuity.
 - C. Two panel grounds are integral with mounting plate.

SPECIFICATIONS

Housing: Black, glass-filled thermoplastic, UL 94V-0. Flange mounting holes are .128 inch diameter Socket Contacts: Copper alloy, electrotinned. Pin Contacts: Copper alloy, electrotinned. Latch Release: Steel, nickel-plated.

Mounting Plate: Copper alloy.

Shell-to-Ground Terminals: Copper alloy, electrotinned.


Latches: Copper alloy, nickel-plated.


Insertion/Withdrawal Forces: 2 pound (nominal). Contact Resistance: .05 ohms per pole (maximum). Dielectric Withstanding Voltage: 1,000 V rms for 1 minute.

Insulation Resistance: 10⁴ MΩ @ 500 V DC. Current Capacity: 10A maximum (carry only).

Operating Temperature: -30°F to 185°F (-34°C to 85°C).

Mechanical Life: 10.000 cycles @ 10 cpm.







NNECTORS & RECEPTACLES

* Please visit the product pages on our website for the most up-to-date product information

PQG® SERIES PART NUMBERING SYSTEM

Q G **SERIES**

PQG-

Composite QG

3 PINS/

CONTACTS

3

GENDER F - Female

M - Male

PC

TERMINALS RA - Right Angle,

Bottom Exit ST - Straight

Rear Exit

LATCHING

0 - None 1 - Latch Lock

2 - Fas-Disconnect (female only)

GROUND TERMINAL

0 - None


1 - Installed


MOUNTING PLATE

0 - None


1 - Plate with two, M3 x 0.5 threaded holes


2 - Plate with two, M3 x 0.5 threaded holes, panel grounds and PCB retainers






















PANEL OPENING

DIMENSIONS ARE FOR REFERENCE ONLY