


THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



BUNDLE SPECIFICATION




- NOTES: UNLESS OTHERWISE SPECIFIED.
- 1.0 PACKAGING SPECIFICATION
 - 1.01 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION.
 - 1.02 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY 10 BUNDLE OR 250 PIECES MAX. PER SHIPPING BOX. CLOSE PLASTIC BAG AND SEAL BOX ALONG 3 SURFACES WITH TAPE.

4	431.80	(17.000)	L=13.00" X W=20.00" X H=9.0
6	457.20	(18.000)	L=13.00" X W=20.00" X H=9.0
8	558.80	(22.000)	L=13.00" X W=25.00" X H=9.0
CONDUCTORS NUMBER OF	MILLIMETERS	INCHES	DIMENSION MAX.
RETRACTED LENGTH 'R'		OUTSIDE SHIPPING BOX	
TABULATION BLOCK			
THIRD ANGLE PROJECTION		I/O INTERCONNECT	
			
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN MILLIMETER (INCHES) 2) TOLERANCES: XX ± 0.20 (0.008) XXX ± 0.35 (0.250)		SANTA ANA, CALIFORNIA	
DR: GETH WYNN E: 06/09/95		TITLE: 26 AWG (12/0.12 mm) BARE COPP 500 FT. EXTENDED, NON-UL, UNSHIELDED, MODULAR CABLE	
CHKD: 		PART NO: 121-X10-0X3	
CHKD: 		CUSTOMER: I/O INTERCONNECT	
CHKD: 		SCALE: NONE	
		SHEET 2 OF 2	

A B C D E F G H

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT, INC. U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT, INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROV.
X10-0X2		I	ECN 387	06/09/95	CT



BUNDLE SPECIFICATION

NOTES: UNLESS OTHERWISE SPECIFIED.

1.0 PACKAGING SPECIFICATION

- 1.01 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION.
- 1.02 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY 10 BUNDLE OR 250 PIECES MAX. PER SHIPPING BOX. CLOSE PLASTIC BAG AND SEAL BOX ALONG 3 SURFACES WITH TAPE.

4	863.60	[34.000]	L=13.00' X W=40.00' X H=9.00
6	1117.60	[44.000]	L=13.00' X W=50.00' X H=9.00
8	1270.00	[50.000]	L=13.00' X W=55.00' X H=9.00
CONDUCTORS	MILLIMETERS	INCHES	DIMENSION MAX
NUMBER OF	RETRACTED LENGTH "R"		OUTSIDE SHIPPING BOX


TABULATION BLOCK

THIRD ANGLE PROJECTION		
I/O INTERCONNECT SANTA ANA, CALIFORNIA		
DR: C. WANG	TITLE: 06/09/95	36 AWG (12/012 MM) BARE COPPER
CHKD: [Signature]	14.00 FT EXTENDED, NON-UL	UNSHIELDED, MODULAR CABLE
CHKD: [Signature]	PART NO: 121-X10-0X2	
CHKD: [Signature]	CUSTOMER: I/O	INTERCONNECT
CHKD: [Signature]	SCALE: NONE	SHEET 2 OF

6/10/95

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT, INC. USA AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT, INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE / REV.	DESCRIPTION	DATE	APPROV.
X10-0X0	D	ECN 387	06/09/95	G.T.



BUNDLE SPECIFICATION

NOTES UNLESS OTHERWISE SPECIFIED.

1.0 PACKAGING SPECIFICATION

1.01 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION.

1.02 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY

10 BUNDLE OR 250 PIECES MAX. PER SHIPPING BOX.

CLOSE PLASTIC BAG AND SEAL BAG ALONG 3 SURFACES


WITH TAPE

4	533.40	(21.000)	L=13.00" X W=25.00" X H=9.00"
6	609.60	(24.000)	L=13.00" X W=25.00" X H=9.00"
8	711.20	(28.000)	L=13.00" X W=30.00" X H=9.00"
CONDUCTORS	MILLIMETERS	INCHES	DIMENSION MAX.
NUMBER OF	RETRACTED LENGTH "R"		OUTSIDE SHIPPING BOX

TABULATION BLOCK

I/O INTERCONNECT 26 AVG (12/0.12 mm) BARE COPPER 7.00 FT. EXTENDED, NON-UL UNSHIELDED, MODULAR CABLE	
DR: CAVI C. VAW CHKD: <i>Valley</i>	TITLE: SANTA ANA, CALIFORNIA DATE: 06/09/95 PART NO: 121-X10-0X0 CUSTOMER: I/O INTERCONNECT SCALE: NONE SHEET: 2 OF 2

THIRD ANGLE PROJECTION




UNLESS OTHERWISE NOTED:

1) DIMENSIONS ARE IN MILLIMETER (INCHES)


2) TOLERANCES:

XX ± 0.20 (0.008)


X.XX ± 6.35 (0.250)



8 CONDUCTOR CABLE



6 CONDUCTOR CABLE



4 CONDUCTOR CABLE

NOTES: UNLESS OTHERWISE SPECIFIED.

- 1.0 MATERIAL AND SPECIFICATIONS
 - 1.01 CONDUCTORS: 26 AWG (12/012 mm) STRANDED BARE COPPER.
 - 1.02 INSULATION: POLYPROPYLENE
 - 1.03 COLOR: PER CALLOUT
 - 1.04 PACKAGING: (SEE PAGE 2)
- 2.0 ELECTRICAL CHARACTERISTICS
 - 2.01 TEMPERATURE & VOLTAGE RATING: 80°C 30 V
 - 2.02 CONDUCTORS RESISTANCE: 148 OHMS/KM MAX. AT 20°C
 - 2.03 INSULATION RESISTANCE: 100 MEGOHMS/KM MIN. AT 20°C
 - 2.04 CAPACITANCE: 15 PF/FT (MAX)
 - 2.05 DIELECTRIC TEST: AC-500V PER 1 MINUTE

121-410-003	4	SILVER SATIN	[0.55] ± 0.0	14.00 ± 1.0
121-410-013	4	BLACK	[0.55] ± 0.0	14.00 ± 1.0
121-410-023	4	WHITE	[0.55] ± 0.0	14.00 ± 1.0
121-610-003	6	SILVER SATIN	[0.55] ± 0.0	14.00 ± 1.0
121-610-013	6	BLACK	[0.55] ± 0.0	14.00 ± 1.0
121-610-023	6	WHITE	[0.55] ± 0.0	14.00 ± 1.0
121-810-003	8	SILVER SATIN	[0.748 ± 0.0	19.00 ± 1.0
121-810-013	8	BLACK	[0.748 ± 0.0	19.00 ± 1.0
121-810-023	8	WHITE	[0.748 ± 0.0	19.00 ± 1.0
1/0 INTERCONNECT PART NUMBER	NUMBER OF CONDUCTORS	COLOR	Ø "A"	

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN MILLIMETER (INCHES)
2) TOLERANCES:
XX ± 0.20 (0.008)
XXX ± 6.35 (0.250)

I/O INTERCONNECT
SANTA ANA, CALIFORNIA

DR: CATH WONG TITLE: 26 AWG (12/012 mm) BARE COPPER
C. WONG 06/09/95 5.00 FT EXTENDED, NON-UL, UNSHIELDED, MODULAR CABLE

CHD: *Karl Berg* PART NO: 121-X10-0X3
CHD: *[Signature]* CUSTOMER: I/O INTERCONNECT
CHD: *[Signature]* SCALE: NONE SHEET 1 OF 1
CHD: *[Signature]*


DATE	REV.	DESCRIPTION	DATE	APPROVED
010-013	G	CON BCS	07/15/78	RJ

DATE	REV.	DESCRIPTION	DATE	APPROVED
010-013	G	CON BCS	07/15/78	RJ

DATE	REV.	DESCRIPTION	DATE	APPROVED
010-013	G	CON BCS	07/15/78	RJ

DATE	REV.	DESCRIPTION	DATE	APPROVED
010-013	G	CON BCS	07/15/78	RJ

THESE DIMENSIONS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS OR SUBASSEMBLY COPIES OR REPRODUCTION IN ANY FORM OR BY ANY MEANS WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS APPLICABLE SUBSIDIARIES.



BUNDLE SPECIFICATION

NOTES: UNLESS OTHERWISE SPECIFIED:

- 1.0 MATERIAL AND SPECIFICATIONS
- 1.10 CONDUCTORS: 26 AWG (0.2/0.12 mm) STAMPED BARE COPPER
- 1.20 INSULATION: POLYPROPYLENE
- 1.30 COLOR: PER CALLOUT
- 1.40 PACKAGING: SEE PAGE 2
- 2.0 ELECTRICAL CHARACTERISTICS
- 2.10 TEMPERATURE & VOLTAGE RATING: 80°C 30 V
- 2.20 CONDUCTORS RESISTANCE: 140 OHMS/KM MAX AT 20°C
- 2.30 INSULATION RESISTANCE: 100 MEGOHMS/KM MIN AT 20°C
- 2.40 CAPACITANCE: 15 PF/FT (500)
- 2.50 DIELECTRIC TEST: AC-500V PER 1 MINUTE
- 3.0 PACKAGING SPECIFICATION
- 3.10 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION
- 3.20 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY 10 BUNDLE OR 250 PIECES MAX PER SHIPPING BOX. CLOSE PLASTIC BAG AND SEAL BOX ALONG 3 SURFACES WITH TAPE.

CONDUCTORS NUMBER OF	MILLIMETERS	RETRACTED LENGTH "IN"	INCHES
4	431.00	(17.000)	L=13.00" X V=28.00" X H=9.00"
6	457.20	(18.000)	L=13.00" X V=28.00" X H=9.00"
8	508.00	(20.000)	L=13.00" X V=28.00" X H=9.00"
10	609.60	(24.000)	L=13.00" X V=28.00" X H=9.00"

CONDUCTORS NUMBER OF

RETRACTED LENGTH "IN"

INCHES

INCHES

INCHES

INCHES

INCHES

INCHES

INCHES

INCHES

INCHES

INCHES

INCHES


INCHES

INCHES

INCHES

INCHES

INCHES



I/O INTERCONNECT

SANTA ANA, CALIFORNIA

26 AWG (0.2/0.12 mm) BARE COPPER
500 FT EXTENDED, NON-UL,
UNSHIELDED, MODULAR CABLE

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

THIRD ANGLE PROJECTION



UNLESS OTHERWISE NOTED:

1) DIMENSIONS ARE IN

2) TOLERANCES

XXX ± 0.20 (0.008)

XXX ± 0.25 (0.010)

XXX ± 0.35 (0.014)

XXX ± 0.50 (0.020)

XXX ± 0.75 (0.030)

XXX ± 1.00 (0.040)

XXX ± 1.50 (0.060)

XXX ± 2.00 (0.080)

XXX ± 3.00 (0.120)

XXX ± 4.00 (0.160)

XXX ± 5.00 (0.200)

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

REV: 07/15/78

DATE: 07/15/78

