

Medium Power Phase Control Thyristors (Stud Version), 22 A



TO-48 (TO-208AA)

FEATURES

- Improved glass passivation for high reliability and exceptional stability at high temperature
- High di/dt and dV/dt capabilities
- Standard package
- Low thermal resistance
- Metric threads version available
- Types up to 1200 V V_{DRM}/V_{RRM}
- Designed and qualified for industrial and consumer level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

PRIMARY CHARACTERISTICS

$I_{T(AV)}$	22 A
V_{DRM}/V_{RRM}	100 V, 200 V, 400 V, 600 V, 800 V, 1000 V, 1200 V
V_{TM}	1.70 V
I_{GT}	60 mA
T_J	-65 °C to +125 °C
Package	TO-48 (TO-208AA)
Circuit configuration	Single SCR

TYPICAL APPLICATIONS

- Medium power switching
- Phase control applications

MAJOR RATINGS AND CHARACTERISTICS

PARAMETER	TEST CONDITIONS	VALUES	UNITS
$I_{T(AV)}$		22	A
	T_C	85	°C
$I_{T(RMS)}$		35	A
I_{TSM}	50 Hz	400	A
	60 Hz	420	
I^2t	50 Hz	793	A ² s
	60 Hz	724	
V_{DRM}/V_{RRM}		100 to 1200	V
t_q	Typical	110	μs
T_J		-65 to +125	°C

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V_{DRM}/V_{RRM} , MAXIMUM REPETITIVE PEAK AND OFF-STATE VOLTAGE ⁽¹⁾ V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK VOLTAGE ⁽²⁾ V	I_{DRM}/I_{RRM} MAXIMUM AT $T_J = T_J$ MAXIMUM mA
VS-22RIA	10	100	150	20
	20	200	300	10
	40	400	500	
	60	600	700	
	80	800	900	
	100	1000	1100	
	120	1200	1300	

Notes

⁽¹⁾ Units may be broken over non-repetitively in the off-state direction without damage, if di/dt does not exceed 20 A/μs

⁽²⁾ For voltage pulses with $t_p \leq 5$ ms



ABSOLUTE MAXIMUM RATINGS						
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES	UNITS
Maximum average on-state current at case temperature	I _{T(AV)}	180° sinusoidal conduction			22	A
					85	°C
Maximum RMS on-state current	I _{T(RMS)}				35	A
Maximum peak, one-cycle non-repetitive surge current	I _{TSM}	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial T _J = T _J maximum	400	A
		t = 8.3 ms			420	
		t = 10 ms	100 % V _{RRM} reapplied		335	
		t = 8.3 ms			355	
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		793	A ² s
		t = 8.3 ms			724	
		t = 10 ms	100 % V _{RRM} reapplied		560	
		t = 8.3 ms			515	
Maximum I ² √t for fusing	I ² √t	t = 0.1 to 10 ms, no voltage reapplied, T _J = T _J maximum			7930	A ² √s
Low level value of threshold voltage	V _{T(TO)1}	(16.7 % x π x I _{T(AV)}) < I < π x I _{T(AV)} , T _J = T _J maximum			0.83	V
High level value of threshold voltage	V _{T(TO)2}	(I > π x I _{T(AV)}), T _J = T _J maximum			0.95	
Low level value of on-state slope resistance	r _{t1}	(16.7 % x π x I _{T(AV)}) < I < π x I _{T(AV)} , T _J = T _J maximum			14.9	mΩ
High level value of on-state slope resistance	r _{t2}	(I > π x I _{T(AV)}), T _J = T _J maximum			13.4	
Maximum on-state voltage	V _{TM}	I _{pk} = 70 A, T _J = 25 °C			1.70	V
Maximum holding current	I _H	T _J = 25 °C, anode supply 6 V, resistive load			130	mA
Latching current	I _L				200	

SWITCHING					
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum rate of rise of turned-on current	$V_{\text{DRM}} \leq 600\text{ V}$	di/dt	$T_J = T_J$ maximum, $V_{\text{DM}} = \text{Rated } V_{\text{DRM}}$ Gate pulse = 20 V, 15 Ω , $t_p = 6\text{ }\mu\text{s}$, $t_r = 0.1\text{ }\mu\text{s}$ maximum $I_{\text{TM}} = (2 \times \text{rated di/dt})\text{ A}$	200	A/ μs
	$V_{\text{DRM}} \leq 800\text{ V}$			180	
	$V_{\text{DRM}} \leq 1000\text{ V}$			160	
	$V_{\text{DRM}} \leq 1600\text{ V}$			150	
Typical turn-on time		t_{gt}	$T_J = 25\text{ }^\circ\text{C}$, at rated $V_{\text{DRM}}/V_{\text{RRM}}$, $T_J = 125\text{ }^\circ\text{C}$	0.9	μs
Typical reverse recovery time		t_{rr}	$T_J = T_J$ maximum, $I_{\text{TM}} = I_{\text{T(AV)}}$, $t_p > 200\text{ }\mu\text{s}$, di/dt = - 10 A/ μs	4	
Typical turn-off time		t_q	$T_J = T_J$ maximum, $I_{\text{TM}} = I_{\text{T(AV)}}$, $t_p > 200\text{ }\mu\text{s}$, $V_R = 100\text{ V}$, di/dt = - 10 A/ μs , dV/dt = 20 V/ μs linear to 67 % V_{DRM} , gate bias 0 V to 100 W	110	

Note

- $t_q = 10\text{ }\mu s$ up to 600 V, $t_q = 30\text{ }\mu s$ up to 1600 V available on special request

BLOCKING				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum critical rate of rise of off-state voltage	dV/dt	$T_J = T_J$ maximum linear to 100 % rated V_{DRM}	100	V/ μs
		$T_J = T_J$ maximum linear to 67 % rated V_{DRM}	300 ⁽¹⁾	

Note

⁽¹⁾ Available with: $dV/dt = 1000\text{ V}/\mu s$, to complete code add S90 i.e. 22RIA120S90



TRIGGERING					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum peak gate power	P _{GM}	T _J = T _J maximum		8.0	W
Maximum average gate power	P _{G(AV)}			2.0	
Maximum peak positive gate current	I _{GM}	T _J = T _J maximum		1.5	A
Maximum peak negative gate voltage	-V _{GM}	T _J = T _J maximum		10	V
DC gate current required to trigger	I _{GT}	T _J = - 65 °C	Maximum required gate trigger current/voltage are the lowest value which will trigger all units 6 V anode to cathode applied	90	mA
		T _J = 25 °C		60	
		T _J = 125 °C		35	
DC gate voltage required to trigger	V _{GT}	T _J = - 65 °C		3.0	V
		T _J = 25 °C		2.0	
		T _J = 125 °C		1.0	
DC gate current not to trigger	I _{GD}	T _J = T _J maximum, V _{DRM} = Rated value		2.0	mA
DC gate voltage not to trigger	V _{GD}	T _J = T _J maximum, V _{DRM} = Rated value	Maximum gate current/voltage not to trigger is the maximum value which will not trigger any unit with rated V _{DRM} anode to cathode applied	0.2	V

THERMAL AND MECHANICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES		UNITS
Maximum operating junction and storage temperature range	T _J , T _{Stg}		-65 to +125		°C
Maximum thermal resistance, junction to case	R _{thJC}	DC operation	0.86		K/W
Maximum thermal resistance, case to heat sink	R _{thCS}	Mounting surface, smooth, flat and greased	0.35		
			TO NUT	TO DEVICE	
Mounting torque		Lubricated threads (Non-lubricated threads)	20 (27.5)	25	lbf · in
			0.23 (0.32)	0.29	kgf · m
			2.3 (3.1)	2.8	N · m
Approximate weight			14		g
			0.49		oz.
Case style		See dimensions - link at the end of datasheet	TO-48 (TO-208AA)		

ΔR_{thJC} CONDUCTION				
CONDUCTION ANGLE	SINUSOIDAL CONDUCTION	RECTANGULAR CONDUCTION	TEST CONDITIONS	UNITS
180°	0.21	0.15	$T_J = T_J$ maximum	K/W
120°	0.25	0.25		
90°	0.31	0.34		
60°	0.45	0.47		
30°	0.76	0.76		

Note

- The table above shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 1 - Current Ratings Characteristics




Fig. 2 - On-State Power Loss Characteristics




Fig. 3 - On-State Power Loss Characteristics




Fig. 4 - Maximum Non-Repetitive Surge Current




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Forward Voltage Drop Characteristics




Fig. 7 - Thermal Impedance Z_{thJC} Characteristics




Fig. 8 - Gate Characteristics

ORDERING INFORMATION TABLE

Device code	VS-	22	RIA	120	M	S90
	1	2	3	4	5	6




- 1 - Vishay Semiconductors product
- 2 - Current code
- 3 - Essential part number
- 4 - Voltage code x 10 = V_{RRM} (see Voltage Ratings table)
- 5 - None = stud base TO-48 (TO-208AA) 1/4" 28UNF-2A
M = stud base TO-48 (TO-208AA) M6 x 1
- 6 - Critical dV/dt:
None = 300 V/ μ s (standard value)
S90 = 1000 V/ μ s (special selection)

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95333



TO-208AA (TO-48)

DIMENSIONS in millimeters (inches)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.