

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
430	A	RELEASED	JWM	11/13/00	JC	11/21/00	DJC	11/21/00

NOTES:

BNC male with 4mm Binding posts

Applications: Adapts BNC female connector to 4mm binding posts to accept spade lugs, wires and banana plugs

SPECIFICATIONS

Insulator: Polyamide (Nylon), Black

Binding Posts Contacts: Brass, Nickel Plated

BNC (m): Brass, Center Contact, Gold Plated

BNC impedance: 50 ohm



Rating:

Voltage: 500V

Current: 3A Max.

Resistance: <0.8 milliohms

Temperature: -20°C ~ 80°C



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE SINCE CONDITIONS OF USE ARE UNPREDICTABLE. THE USER ASSUMES ALL LIABILITY WHATSOEVER IN CONNECTION THEREWITH. THE INFORMATION IS PROVIDED AS IS WITHOUT WARRANTY OF ANY KIND, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. THE USER ASSUMES ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

Tolerances unless otherwise specified: .XX ±.02		DRAWN BY:	DATE:	DRAWING TITLE:			
		Jeff McVicker	11/12/00	BNC(m) w/4mm Binding Posts			
		CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
		JOHN COLE	11/21/00	A	76-005	16F7677.dwg	A
		APPROVED BY:	DATE:	SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1
		Daniel Carey	11/21/00				

TENMA
TECHNOLOGY