



PART NUMBER and LEGEND	LED COLOR			
	POS 1	POS 2	POS 3	POS 4
568-0100-021F	** BLANK **	** BLANK **	GREEN	RED
568-0100-022F	** BLANK **	** BLANK **	GREEN	GREEN
568-0100-132F	** BLANK **	RED	YELLOW	GREEN
568-0100-220F	** BLANK **	GREEN	GREEN	** BLANK **
568-0100-310F	** BLANK **	YELLOW	RED	** BLANK **
568-0101-001F	* RED *	** BLANK **	** BLANK **	RED
568-0101-010F	* RED *	** BLANK **	RED	** BLANK **
568-0101-023F	* RED *	** BLANK **	GREEN	YELLOW
568-0101-000F	* RED *	** BLANK **	** BLANK **	** BLANK **
568-0101-110F	* RED *	RED	RED	** BLANK **
568-0101-011F	* RED *	** BLANK **	RED	RED
568-0101-111F	* RED *	RED	RED	RED
568-0101-112F	* RED *	RED	RED	GREEN
568-0101-122F	* RED *	RED	GREEN	GREEN
568-0101-123F	* RED *	RED	GREEN	YELLOW
568-0101-132F	* RED *	RED	YELLOW	GREEN
568-0101-212F	* RED *	GREEN	RED	GREEN
568-0101-222F	* RED *	GREEN	GREEN	GREEN
568-0101-232F	* RED *	GREEN	YELLOW	GREEN
568-0101-233F	* RED *	GREEN	YELLOW	YELLOW
568-0101-237F	* RED *	GREEN	YELLOW	ORANGE
568-0101-312F	* RED *	YELLOW	RED	GREEN
568-0101-321F	* RED *	YELLOW	GREEN	RED
568-0101-322F	* RED *	YELLOW	GREEN	GREEN
568-0101-323F	* RED *	YELLOW	GREEN	YELLOW
568-0101-332F	* RED *	YELLOW	YELLOW	GREEN
568-0101-333F	* RED *	YELLOW	YELLOW	YELLOW
568-0101-723F	* RED *	ORANGE	GREEN	YELLOW
568-0102-000F	* GREEN *	** BLANK **	** BLANK **	** BLANK **
568-0102-010F	* GREEN *	** BLANK **	RED	** BLANK **
568-0102-020F	* GREEN *	** BLANK **	GREEN	** BLANK **
568-0102-073F	* GREEN *	** BLANK **	ORANGE	YELLOW
568-0102-102F	* GREEN *	RED	** BLANK **	GREEN
568-0102-111F	* GREEN *	RED	RED	RED
568-0102-113F	* GREEN *	RED	RED	YELLOW
568-0102-120F	* GREEN *	RED	GREEN	** BLANK **
568-0102-121F	* GREEN *	RED	GREEN	RED
568-0102-122F	* GREEN *	RED	GREEN	GREEN
568-0102-123F	* GREEN *	RED	GREEN	YELLOW
568-0102-133F	* GREEN *	RED	YELLOW	YELLOW
568-0102-173F	* GREEN *	RED	ORANGE	YELLOW
568-0102-173F	* GREEN *	RED	ORANGE	ORANGE
568-0102-190F	* GREEN *	RED	BLUE (WATER CLEAR)	** BLANK **
568-0102-200F	* GREEN *	GREEN	** BLANK **	** BLANK **
568-0102-201F	* GREEN *	GREEN	** BLANK **	RED
568-0102-211F	* GREEN *	GREEN	RED	RED
568-0102-212F	* GREEN *	GREEN	RED	GREEN
568-0102-213F	* GREEN *	GREEN	RED	YELLOW
568-0102-220F	* GREEN *	GREEN	GREEN	** BLANK **
568-0102-221F	* GREEN *	GREEN	GREEN	RED
568-0102-222F	* GREEN *	GREEN	GREEN	GREEN
568-0102-223F	* GREEN *	GREEN	GREEN	YELLOW
568-0102-227F	* GREEN *	GREEN	GREEN	ORANGE
568-0102-231F	* GREEN *	GREEN	YELLOW	RED
568-0102-232F	* GREEN *	GREEN	YELLOW	GREEN
568-0102-233F	* GREEN *	GREEN	YELLOW	YELLOW
568-0102-311F	* GREEN *	YELLOW	RED	RED
568-0102-312F	* GREEN *	YELLOW	RED	GREEN
568-0102-321F	* GREEN *	YELLOW	GREEN	RED
568-0102-323F	* GREEN *	YELLOW	GREEN	YELLOW
568-0102-331F	* GREEN *	YELLOW	YELLOW	RED
568-0102-332F	* GREEN *	YELLOW	YELLOW	GREEN
568-0102-333F	* GREEN *	YELLOW	YELLOW	YELLOW
568-0102-727F	* GREEN *	ORANGE	GREEN	ORANGE
568-0103-000F	* YELLOW *	** BLANK **	** BLANK **	** BLANK **
568-0103-003F	* YELLOW *	** BLANK **	** BLANK **	YELLOW
568-0103-022F	* YELLOW *	** BLANK **	GREEN	GREEN
568-0103-030F	* YELLOW *	** BLANK **	YELLOW	** BLANK **
568-0103-031F	* YELLOW *	** BLANK **	YELLOW	RED
568-0103-111F	* YELLOW *	RED	RED	RED
568-0103-112F	* YELLOW *	RED	RED	GREEN
568-0103-120F	* YELLOW *	RED	GREEN	** BLANK **
568-0103-122F	* YELLOW *	RED	GREEN	GREEN
568-0103-131F	* YELLOW *	RED	YELLOW	RED
568-0103-200F	* YELLOW *	GREEN	** BLANK **	** BLANK **
568-0103-210F	* YELLOW *	GREEN	RED	** BLANK **
568-0103-220F	* YELLOW *	GREEN	GREEN	** BLANK **
568-0103-222F	* YELLOW *	GREEN	GREEN	GREEN
568-0103-232F	* YELLOW *	GREEN	YELLOW	GREEN
568-0103-312F	* YELLOW *	YELLOW	RED	GREEN
568-0103-330F	* YELLOW *	YELLOW	YELLOW	** BLANK **
568-0103-333F	* YELLOW *	YELLOW	YELLOW	YELLOW




OPERATING CHARACTERISTICS AT 25°C AMBIENT						
CHARACTERISTICS	COLOR	MIN	TYP	MAX	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY	RED	7.4	10.0		mcd	I _r = 10 mA
	YELLOW	7.4	10.0			
	GREEN	4.7	12.6			
	ORANGE	3.4	7.0			
	BLUE	110		310		I _r = 20 mA
FORWARD VOLTAGE	RED		2.0	2.8	V	I _r = 20 mA
	YELLOW		2.1	2.8		
	GREEN		2.1	2.8		I _r = 10 mA
	ORANGE	1.5	2.2	3.0		I _r = 20 mA
REVERSE CURRENT	BLUE		3.5	4.0	µA	V _R = 5 V
	ALL			100		
PEAK WAVELENGTH	RED		635		nm	
	YELLOW		585			
	GREEN		565			
	ORANGE		600			
VIEWING ANGLE	BLUE		470		DEG	
	ALL		60			
VIEWING ANGLE	BLUE		45		DEG	
	ALL		45			



ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT						UNITS
POWER DISSIPATION	100	60	100	135	140	mW
DERATE LINEARLY FROM 50°C / 25°C FOR BLUE	0.4	0.25	0.4	0.5	0.32	mA/°C
CONTINUOUS FORWARD CURRENT	30	20	30	25	30	mA
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 0.1 ms PULSE WIDTH)	120	80	120	90	100	mA
SOLDERING TEMPERATURE (FOR 5 SECONDS)	260					°C
OPERATING TEMPERATURE	-55 TO +100			-35 TO +85		°C
STORAGE TEMPERATURE	-55 TO +100			-35 TO +85		°C



ATTENTION:
OBSERVE PRECAUTIONS FOR
HANDLING ELECTROSTATIC
SENSITIVE DEVICES



REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	—	NEW RELEASE	TWC	TC	N.O.	8-9-05
B	—	ADDED P/N 568-0100-220F; ADDED ESD NOTE 6 & LOGO ON ALL PRODUCTS; CHANGED TITLE DESCRIPTION	TWC	N.O.	MES	6-6-06
C	—	ADDED P/N'S 568-0102-073F AND 568-0102-190F; ADDED BLUE LED SPECS.	TC	N.O.	MES	9-8-06
D	—	ADDED P/N 568-0101-123F & 568-0103-112F	SM	N.O.	MES	11-2-06
E	—	ADDED P/N 568-0100-310F	TC	N.O.	MES	6-27-07
F	—	UPDATED BLUE LED SPECS	KLJ	N.O.	MES	2-7-08
G	—	ADDED P/N 568-0101-132F	KLJ	N.O.	MES	5-1-09
H	—	ADDED P/N'S 568-0103-122F & 568-0101-001F	AJF	KLJ	SM	12-11-09



SCALE 3.000

NOTES:

- LEADS TO FIT INTO HOLES SPACED AS PER HOLE PATTERN.
- WHEN A ZERO APPEARS IN THE LAST 4 DIGITS OF THE PART NUMBER THIS MEANS NO LAMP REQUIRED IN THAT POSITION
- LED LEAD DIMENSIONS SHOWN ARE MEASURED AT HOUSING EXIT.
- PIN NUMBERS FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PARTS.
- DIALIGHT PART NUMBER = 568-010X-XXXX (SEE CHART FOR ALL PART NUMBERS)
- THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING AND STORAGE IN ACCORDANCE WITH IPC-A-610.

RoHS Compliant 568-010x-xxxF Thru hole Quad-level CBI

Part Numbers with the "F" suffix ending are RoHS Compliant.
Example: 568-0100-021F, 568-0103-333F
The bag packaging is marked with "RoHS Compliant" label or equivalent markings.
Parts can be wave soldered, dip soldered or hand soldered using typical lead-free soldering process with max 260°C temp. for 5 sec.

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.		
SCALE: 4.000	DRAWING NUMBER	REV
ALL DIM'S IN: INCHES- $\frac{1}{16}$	C-17278	H
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE STANDARD 3MM QUAD LEVEL CBI	
FRACTIONS: $\pm 1/64$	ROHS COMPLIANT	
DECIMALS (.XX): $\pm .02$	MATERIAL	
DECIMALS (.XXX): $\pm .015$		
ANGLES: $\pm 3^\circ$		
FINISH:		
FSCM	83330	
SHEET	1 OF 1	FAMILY TABLES:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

568-0101-333F	568-0101-322F	568-0102-113F	568-0102-211F	568-0102-173F	568-0102-333F	568-0102-111F
568-0102-312F	568-0102-213F	568-0102-121F	568-0103-200F	568-0102-133F	568-0102-201F	568-0101-312F
568-0100-220F	568-0103-210F	568-0102-332F	568-0102-232F	568-0101-011F	568-0102-177F	568-0101-321F
568-0101-232F	568-0102-102F	568-0101-212F	568-0102-221F	568-0101-000F	568-0101-112F	568-0101-237F
568-0101-010F	568-0103-120F	568-0102-223F	568-0101-023F	568-0103-030F	568-0102-233F	568-0103-031F
568-0103-222F	568-0102-727F	568-0102-020F	568-0102-122F	568-0101-110F	568-0102-100F	568-0101-222F
568-0103-111F	568-0103-220F	568-0103-000F	568-0101-122F	568-0102-311F	568-0102-231F	568-0102-220F
568-0102-123F	568-0100-022F	568-0103-131F	568-0102-200F	568-0103-112F	568-0101-123F	568-0102-000F
568-0102-073F	568-0102-227F	568-0101-113F	568-0102-321F	568-0102-190F	568-0100-310F	