

BZV61 / BZV62

Silicon Power Zener Diode

Description

The BZV61/62 are hermetically sealed 35A-forward current diodes, which are available in different Zener voltages.

Features

- Forward current 35A
- Zener voltages 22V, 27V, 33V or 39V
- Hermetic press-fit package
- Available in different modifications of the package

Applications

- Power supplies
- Rectifier diode in car alternators


Pinout details



BZV61: 1 – cathode; 2 - anode

BZV62: 1 – anode; 2 - cathode

Typical application circuit




Ordering information

Device	Quantity per box	Options
BZV61-22; ...; BZV61-39	500	The package quantities for the different package modifications are included in "PressFitPackageModifications.pdf"
BZV62-22; ...; BZV62-39	500	

Device marking

Devices are identified by type. Colour of marking: BZV61- black, BZV62 – red



BZV61 / BZV62

Absolute maximum ratings (at $T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated)

Parameter			Symbol		Unit	Test condition
Z-current (continuous)	BZV61-22	BZV62-22	I_Z	7.2	A	$T_c = 25^{\circ}\text{C}$
	BZV61-27	BZV62-27		5.8		
	BZV61-33	BZV62-33		4.8		
	BZV61-39	BZV62-39		4.2		
Mean forward current			$I_{F(AV)}$	35	A	sinusoidal, $f = 15 - 1000 \text{ Hz}$
Surge forward current			I_{FSM}	600	A	$T_J = 25^{\circ}\text{C}$, half-sine wave, $\leq 10 \text{ ms}$
				500		$T_J = 175^{\circ}\text{C}$, half-sine wave, $\leq 10 \text{ ms}$
Maximum rated value			$\int i^2 dt$	1800	A^2s	$T_J = 25^{\circ}\text{C}$, half-sine wave, $\leq 10 \text{ ms}$
				1250		$T_J = 175^{\circ}\text{C}$, half-sine wave, $\leq 10 \text{ ms}$
Repetitive peak forward current			$I_{FRM} = \pi * I_{F(AV)}$	110	A	$f = 15 - 1000 \text{ Hz}$
Effective forward current			$I_{F(RMS)}$	55	A	sinusoidal, $f = 15 - 1000 \text{ Hz}$
Junction temperature			T_{Jmax}	175	$^{\circ}\text{C}$	
Storage temperature range			T_{stg}	- 50 to + 150	$^{\circ}\text{C}$	

Thermal resistance


Parameter	Symbol	Value	Unit
Junction to case	$R_{\theta JC}$	0.8	$^{\circ}\text{C/W}$

BZV61 / BZV62

Electrical characteristics (at $T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated)

Parameter			Symbol	Min.	Typ.	Max.	Unit	Test conditions
Z-voltage	BZV61-22	BZV62-22	V_Z	20.8	22	23.3	V	at $I_Z = 100\text{mA}$
	BZV61-27	BZV62-27		25.1	27	28.9		
	BZV61-33	BZV62-33		31	33	35		
	BZV61-39	BZV62-39		37	39	41		
Forward voltage			V_F	-	1.0	1.1	V	$I_F = 35\text{ A}$, measuring time 1ms
Reverse current			I_R	-	-	200	μA	at $V_Z - 5\text{V}$
Dynamical resistance	BZV61-22	BZV62-22	r_z	-	-	2	Ω	at $I_Z = 100\text{mA}$
	BZV61-27	BZV62-27		-	-	3.5		
	BZV61-33	BZV62-33		-	-	5		
	BZV61-39	BZV62-39		-	-	6		
Dynamical resistance (information value)	BZV61-22	BZV62-22	r_z	-	-	200	$\text{m}\Omega$	at $I_Z = 1\text{A}$
	BZV61-27	BZV62-27		-	-	350		
	BZV61-33	BZV62-33		-	-	500		
	BZV61-39	BZV62-39		-	-	700		
Dynamical resistance (information value)	BZV61-22	BZV62-22	r_z	-	-	20	$\text{m}\Omega$	at $I_Z = 10\text{A}$
	BZV61-27	BZV62-27		-	-	35		
	BZV61-33	BZV62-33		-	-	50		
	BZV61-39	BZV62-39		-	-	80		

Packaging details



Package dimensions

Dimensions in millimeters are control dimensions, dimensions in inches are approximate

DIM	Millimeters			Inches		
	MIN	TYP	MAX	MIN	TYP	MAX
A	15,00	15,50	16,00	0,591	0,610	0,630
A1	5,70	6,20	6,70	0,224	0,244	0,264
A2	2,10	2,30	2,50	0,083	0,091	0,098
b	3,10	3,40	3,70	0,122	0,134	0,146
D	15,50	15,70	15,90	0,610	0,618	0,626
D1	12,75	12,80	12,85	0,502	0,504	0,506
D2	12,30	12,70	13,10	0,484	0,500	0,516
L	3,00	3,50	4,00	0,118	0,138	0,157

Europe

Zetex GmbH
Streitfeldstraße 19
D-81673 München
Germany

Telefon: (49) 89 45 49 49 0
Fax: (49) 89 45 49 49 49
europe.sales@zetex.com

Americas

Zetex Inc
700 Veterans Memorial Highway
Hauppauge, NY 11788
USA

Telephone: (1) 631 360 2222
Fax: (1) 631 360 8222
usa.sales@zetex.com

Asia Pacific

Zetex (Asia Ltd)
3701-04 Metroplaza Tower 1
Hing Fong Road, Kwai Fong
Hong Kong

Telephone: (852) 26100 611
Fax: (852) 24250 494
asia.sales@zetex.com

Corporate Headquarters

Zetex Semiconductors plc
Zetex Technology Park, Chadderton
Oldham, OL9 9LL
United Kingdom

Telephone (44) 161 622 4444
Fax: (44) 161 622 4446
hq@zetex.com

For international sales offices visit www.zetex.com/offices

Zetex products are distributed worldwide. For details, see www.zetex.com/salesnetwork

This publication is issued to provide outline information only which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contact or be regarded as a representation relating to the products or services concerned. The company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.