

LOW VOLTAGE HIGH SPEED SWITCHING.


FEATURES

- Low Forward Voltage : $V_{F(3)}=0.42(\text{Typ.})$
- Small Package : USC.

MAXIMUM RATING (Ta=25℃)


CHARACTERISTIC	SYMBOL	RATING	UNIT
Maximum (Peak) Reverse Voltage	V_{RM}	30	V
Reverse Voltage	V_R	30	V
Maximum (Peak) Forward Current	I_{FM}	300	mA
Average Forward Current	I_O	100	mA
Surge Current (10ms)	I_{FSM}	1	A
Power Dissipation	P_D	200*	mW
Junction Temperature	T_j	150	℃
Storage Temperature Range	T_{stg}	-55 ~ 150	℃

* : Mounted on a glass epoxy circuit board of 20×20mm,
pad dimension of 4×4mm.



Marking

Type Name



ELECTRICAL CHARACTERISTICS (Ta=25℃)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Forward Voltage	$V_{F(1)}$	$I_F=1\text{mA}$	-	0.26	0.35	V
	$V_{F(2)}$	$I_F=5\text{mA}$	-	0.30	0.40	
	$V_{F(3)}$	$I_F=100\text{mA}$	-	0.42	0.55	
Reverse Current	I_R	$V_R=30\text{V}$	-	-	15	μA
Total Capacitance	C_T	$V_R=1\text{V}, f=1\text{MHz}$	-	40	-	pF