

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		A	ECO-07-019301	23AUG07	MB	DR

D

D

C




C

B



B

A


A




1977069-2 SHOWN




SWITCH FUNCTION D1
CIRCUIT DIAGRAM



SWITCH FUNCTION D2
CIRCUIT DIAGRAM





PANEL CUT OUT






2.00-4.00[.079-.158]	19.8-0.1 [.780-.004]	13.0+0.1 [.512+.004]
1.25-2.00[.049-.079]	19.4-0.1 [.764-.004]	13.0+0.1 [.512+.004]
0.75-1.25[.030-.049]	19.2-0.1 [.756-.004]	13.0+0.1 [.512+.004]
PANEL THICKNESS	X	Y

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER	03APR2007	Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: mm [INCHES]		CHK D.ROHDE		Tyco Electronics		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -		NAME		
0 PLC ± -		PRODUCT SPEC		POWER ROCKER SWITCH, 13.0mm X 19.2mm		
1 PLC ± 0.30[.012]		NOT APPLICABLE		PANEL CUT-OUT SIZE, DOUBLE POLE, DOUBLE THROW,		
2 PLC ± 0.05[.002]		APPLICATION SPEC		SIX TERMINALS, NON-ILLUMINATED		
3 PLC ± -		NOT APPLICABLE		SIZE CAGE CODE DRAWING NO		
4 PLC ± -		WEIGHT		RESTRICTED TO		
ANGLES ± -		CUSTOMER DRAWING		A200719C=1977069		
FINISH		SCALE		SHEET 1 OF 3		
1		2		REV A		



PANEL CUT OUT



1-1977069-1 SHOWN

2.00-4.00[.079-.158]	19.8-0.1 [.780-.004]	13.0+0.1 [.512+.004]
1.25-2.00[.049-.079]	19.4-0.1 [.764-.004]	13.0+0.1 [.512+.004]
0.75-1.25[.030-.049]	19.2-0.1 [.756-.004]	13.0+0.1 [.512+.004]
PANEL THICKNESS	X	Y

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: M.BINNER CHK: D.ROHDE APVD: _____		03APR2007 Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± - 1 PLC ± 0.30[.012] 2 PLC ± 0.05[.002] 3 PLC ± - 4 PLC ± - ANGLES ± -		POWER ROCKER SWITCH, 13.0mm X 19.2mm PANEL CUT-OUT SIZE, DOUBLE POLE, DOUBLE THROW, SIX TERMINALS, NON-ILLUMINATED	
MATERIAL		FINISH		SIZE	RESTRICTED TO
				CAGE CODE A2 00779	DRAWING NO C-1977069
		WEIGHT -			
CUSTOMER DRAWING				SCALE 3:1	SHEET 2 OF 3
				REV A	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

LEGACY PART NUMBER

X₁X₂

X₃

X₄

X₅X₆

—

X₇X₈

X₉

—

X₁₀

X₁₁

X₁₂

X₁₃

X₁₄

SWITCH TYPE: X₁X₂ = PR — POWER ROCKER

SECONDARY ROCKER COLOR: X₁₂ = Ø — NOT APPLICABLE

NOMINAL PANEL CUT OUT SIZE: X₃ = A — 13.0x19.2[.512x.756]

NUMBER OF POLES: X₄ = D — DOUBLE

SWITCH FUNCTION: X₅X₆ =

D1: ON-ON, WITH OPAQUE, SINGLE COLOR ROCKER BUTTON

D2: ON-(ON), WITH OPAQUE, SINGLE COLOR ROCKER BUTTON

D3: ON-OFF-ON, WITH OPAQUE, SINGLE COLOR ROCKER BUTTON

D4: ON-OFF-(ON), WITH OPAQUE, SINGLE COLOR ROCKER BUTTON

CURRENT RATING: X₇X₈ = 12 — △6

LEGEND TEXT PATTERN: X₁₃ =

Ø

D

E

F

G

- =

I II

- O =

I O II

TERMINAL TYPE: X₉ = E — QC TAB

LEGEND TEXT COLOR: X₁₄ =

Ø — NOT APPLICABLE

G — GREEN

R — RED

B — BLACK

W — WHITE

FRAME COLOR: X₁₀ =

B — BLACK

W — WHITE

ROCKER COLOR: X₁₁ =

B — BLACK

G — GREEN

R — RED

W — WHITE

1

MATERIALS:

ROCKER BUTTON & HOUSING FRAME: NYLON 66, UL 94 V-2.

TERMINAL, ACTIVE CONTACTOR: COPPER ALLOY PER ASTM B152/B152M

PLUNGER: BRASS PER ASTM B036

SPRING: STEEL WIRE PER ASTM A228/A228M

2

FINISH:

PLUNGER: 1.02µm[.000040]MIN NICKEL

3

ELECTRICAL SPECIFICATIONS:

CURRENT AND VOLTAGE: △6

CONTACT RESISTANCE: (INITIAL): <100mΩ

DIELECTRIC STRENGTH (INITIAL): >1000 VAC, 1 MINUTE

INSULATION RESISTANCE (INITIAL): >100MΩ (500 VDC BETWEEN OPEN CONTACTS)

ELECTRICAL LIFE ENDURANCE: >6000 OPERATIONS, VOLTAGE DROP: <100mV

TEMPERATURE RISE AT TERMINALS: <30°C, 6000 OPERATIONS

(AMBIENT CONDITIONS: 25±2°C AND 65±5%R.H)

4

MECHANICAL SPECIFICATIONS:

ACTUATING FORCE: 400g MIN, 1400g MAX

OPERATING LIFE ENDURANCE: >100,000 OPERATIONS

TERMINAL RETENTION FORCE: >6.8kg— QC TAB

5

ENVIRONMENTAL SPECIFICATIONS:

AMBIENT TEMPERATURE: -20°C TO +85°C

HUMIDITY: MAX 85%

SALT SPRAY: NO REMARKABLE RUST ON METAL PARTS

(5% SALT/ 35°C, 24HRS)

SHOCK: NO MECHANICAL DEFECT OR DAMAGE

(500G 11MSEC / X,Y,Z, 3 TIMES)

6

12A@125VAC/6A@250VAC

7

ELECTRICAL RATINGS, APPROVED AGENCY LOGOS, TERMINAL IDENTIFICATION NUMBERS, AND THE TE LOGO MOLDED APPROXIMATELY AS SHOWN ON THE SIDES OF THE SWITCH HOUSING.

8

COMPONENT RECOGNIZED TO US & CANADIAN STANDARDS, UL FILE NO. E46765.

9

ROHS 2002/95/EC COMPLIANT.

2	PRADD4-12F-BB0GW	1-1977069-2
2	PRADD4-12F-BB0FW	1-1977069-1
2	PRADD4-12F-BB000	1-1977069-0
1	PRADD2-12F-BB0EW	1977069-9
1	PRADD2-12F-BB0DW	1977069-8
1	PRADD2-12F-BB000	1977069-7
2	PRADD3-12F-BB0GW	1977069-6
2	PRADD3-12F-BB0FW	1977069-5
2	PRADD3-12F-BB000	1977069-4
1	PRADD1-12F-BB0EW	1977069-3
1	PRADD1-12F-BB0DW	1977069-2
1	PRADD1-12F-BB000	1977069-1
SHEET REF	LEGACY PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	0.30[.012]
2 PLC	±	0.05[.002]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

FINISH

2

DWN
M.BINNER

CHK
D.ROHDE

APVD
-

PRODUCT SPEC
NOT APPLICABLE

APPLICATION SPEC
NOT APPLICABLE

WEIGHT
-

CUSTOMER DRAWING

03APR2007

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
POWER ROCKER SWITCH, 13.0mm X 19.2mm
PANEL CUT-OUT SIZE, DOUBLE POLE,DOUBLE THROW,
SIX TERMINALS, NON-ILLUMINATED

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=1977069	-

SCALE	3:1	SHEET	3	OF	3	REV	A
-------	-----	-------	---	----	---	-----	---

AMP 1471-9 REV 31MAR2000

1977069

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PRADD1-12F-BB0EW](#)