





PRODUCT NUMBER
SEE NOTE 1




mat'l. code NOTE 3				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM	title
A	V12530	SAR	10/8/91		angles	.XX $\pm$.01/.3	4 ROW VERTICAL RECEPT
B	V13313	MRC	12/19/91		linear	.XXX $\pm$.005/.13	HIGH DURABILITY, S.T.B., 0 G.P.
C	V31616	SRS	10/26/93	0'±2'		.XXXX $\pm$.0020/.05	dwg no
D	V40487	GIP	3/8/94	dr	S.ROYER	8/16/91	sheet 1 of 2 size
E	V90521	HTB	2/25/99	enr	S.CLARK	10/8/91	50023 A3
F	V00258	JWS	1/21/00	chr	S.CLARK	10/16/91	type
G	M06-0260	MHT	7/07/06	appd	S.CLARK	10/8/91	Product Customer Drawing
sheet	revision	G	G				
index	sheet	1	2				


PRODUCT NUMBER	DIM.	LENGTH FORMULAS
SEE NOTE 1	DIM A	.100/2.54 X NO. OF COLUMNS + .75/19.1
	DIM B	.100/2.54 X NO. OF COLUMNS + .450/11.43
	DIM C	.100/2.54 X NO. OF COLUMNS - .100/2.54



SECTION X-X



SECTION U-U



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100/2.54 GRID
UNLESS OTHERWISE SPECIFIED)

NOTES:

- ① PRODUCT NUMBERING CODE:
 $50023 - 7 \text{ YYY Z}$
 TAIL LENGTH(NOTE 5)
 NO. OF POSITIONS(NOTE 2)
 PLATING(NOTE 4)
 BASE NUMBER
- ② THIS PRODUCT IS CONFIGURED IN SIZES OF 10 THRU 80 COLUMNS IN INCREMENTS OF ONE. i.e.: 10,11,12,13,.....49,50.
- ③ HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK. CONTACT MATERIAL: BeCu
- ④ PLATING CONTACT AREA OPTIONS:
 7 = 60u"/1.52u GXT
 ALL SOLDER TAILS TIN/LEAD
- ⑤ TAIL LENGTH OPTIONS:
 E = .125±.010 / 3.18±.25
 F = .145±.010 / 3.68±.25
 H = .180±.010 / 4.57±.25
- ⑥ MANUFACTURE'S NAME, P/N AND LOT CODE TO APPEAR ON THIS SURFACE AS PER BUS-12-108.
- ⑦ FOR DOCUMENTATION MENU, SEE BUS-01-057.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified	 scale 1:1	title
G					angles linear .XX±.01/.3		4 ROW VERTICAL RECEPT
					0'±2' .xxx±.005/.13		HIGH DURABILITY, S.T.B., 0 G.P.
					xxxx±.0020/.05		dwg no sheet 2 of 2 size
				dr	S.ROYER 8/16/91		50023 A3
				enr	S.CLARK 10/8/91		
				chr	S.CLARK 10/16/91		
				appd	S.CLARK 10/8/91		
sheet index	revision sheet						type Product Customer Drawing