

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 2036031



LOW PROFILE STRIPS

SLW, CES
SERIES

Mates with:
TLW, TSW, MTLW,
MTSW, EW, ZW

SPECIFICATIONS

For complete specifications
see www.samtec.com?SLW

Insulator Material:

Black G.F. Polyester

Contact Material:

Phosphor Bronze

Plating: Au or Sn over

50μ" (1,27μm) Ni

Current Rating: 3A

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ max

Insertion Depth:

(2,16mm) .085" to

(2,92mm) .115"

Insertion Force:

(Single contact only)

(3,34N) 12oz avg.

(0,64mm) .025" SQ pin

Withdrawal Force:

(Single contact only)

(1,67N) 6 oz avg.

(0,64mm) .025" SQ pin

RoHS Compliant: Yes

Lead-Free Solderable:

Wave only



SLW


1

NO. PINS
PER ROW

01

PLATING
OPTIONROW
OPTION

01 thru 50



-S


= 30μ" (0,76μm) Gold Contact,
Matte Tin tail-S
= Single
Row

-G

= 20μ" (0,51μm) Gold contact,
Gold flash on balance-D
= Double
Row

-T

= Matte Tin



Note: Some lengths,
styles and options are
non-standard, non-returnable.

Mates with:
TLW, TSW, MTLW,
MTSW, EW, ZW, DW

SPECIFICATIONS

For complete specifications
see www.samtec.com?CES

Insulator Material:

Black G.F.

Polyester

Contact Material:

Phosphor Bronze

Plating: Au or Sn over

50μ" (1,27μm) Ni

Current Rating: 1A

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ max

Insertion Depth:

(2,62mm) .103" to

(4,06mm) .160"

Insertion Force:

(Single contact only)

(2,22N) 8 oz avg.

(0,64mm) .025" SQ pin

Withdrawal Force:

(Single contact only)

(1,11N) 4 oz avg.

(0,64mm) .025" SQ pin

RoHS Compliant: Yes

Lead-Free Solderable:

Wave only





CES

1

NO. PINS
PER ROWLEAD
STYLEPLATING
OPTIONROW
OPTIONRA
OPTION

01 thru 50

-01
= (3,25) .128
"A" Dim.-02
= (5,66) .223
"A" Dim.

-S

= 30μ" (0,76μm)
Gold contact,
Matte Tin tail

-S

= Single
Row

-G

= 30μ" (0,76μm)
Gold contact,
Gold flash on
balance

-D


= Double
Row

-T


= Matte Tin

-RA
= Right Angle
version

Style -02 only
Single Row only



Note: Some lengths,
styles and options are
non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047

SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299

SAMTEC NORDIC/BALTIC • Tel: +46-84477280 • Fax: +46-87420413

SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340

SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520

SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61

SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690

SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-5423 4575

SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113

SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315

SAMTEC INDIA • Tel: +91-80-3272 1612 • Fax: +91-80-4152 8187

SAMTEC TAIWAN • Tel: 886-2-2735-6109 • Fax: 886-2-2735-5036

SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502

SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842

SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681

SAMTEC SOUTH AFRICA • Tel: 27 11 454 4317 • Fax: 27 86 6714432

SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745