

1	2	3	4	5
			<p>TECHNICAL CHARACTERISTICS</p> <p>MATERIAL INSULATOR: PBT FLAMMABILITY RATING: UL94-V0 COLOR: WHITE CONTACT MATERIAL: COPPER ALLOY CONTACT TYPE: STAMPED CONTACT PLATING: SELECTIVE GOLD SHIELDING: BRASS NI PLATED QUALITY CLASS: 1500 MATING CYCLES</p> <p>ENVIRONMENTAL OPERATING TEMPERATURE: -40 UP TO +105°C COMPLIANCE: LEAD FREE AND ROHS</p> <p>ELECTRICAL CURRENT RATING: 1.5 A MAX WORKING VOLTAGE: 30 VAC INSULATOR RESISTANCE: >1000 MΩ DIELECTRIC WITHSTANDING VOLTAGE: 750 VAC/MIN CONTACT RESISTANCE: 20 mΩ MAX</p> <p>STANDARD CERTIFIED: E323964</p> <p>SOLDERING JEDEC LEAD FREE WAVE SOLDERING</p> <p>PACKAGING TRAY</p>	
RoHS Compliant				
		PROJECTION: 	GENERAL TOLERANCE .X = +/_ 0.2 .XX = +/_ 0.15	
		APPROVAL: NPr	UNIT: MM SCALE: SHEET: 1/1 DRAW: QL	DESCRIPTION: DUAL USB 2.0 TYPE A VERTICAL WERI PART NO: 614 008 235 023
H	27-OCT-14	REVIEW	QL	
REV	DATE	FILE	BY	SIZE A4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Electronics:](#)

[614008235023](#)