


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn100%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	7-8 tie(5+6+7, 8+9+10), @20°C	0.010 ohms max.
D.C. RESISTANCE	1-3 @20°C	0.500 ohms max., 0.120 typ.
INDUCTANCE	7-8 tie(5+6+7, 8+9+10), 50kHz, 10mVAC, Ls	5.0uH ±10%
SATURATION CURRENT @85°C	20% rolloff from initial	25ADC
CONTINUOUS CURRENT	40°C temp rise from ambient	18A
LEAKAGE INDUCTANCE	7-8 tie(1+3, 5+6+7, 8+9+10), 100kHz, 1.0VAC, Ls	100nH max.
DIELECTRIC	PRI-SEC 1250VAC, 1 second	1000VAC, 1 minute
URNS RATIO	(13-3):(1-13)	1:1, ±1%
URNS RATIO	(1-3):(5-10)	10:1, ±1%
URNS RATIO	(1-3):(6-9)	10:1, ±1%
URNS RATIO	(1-3):(7-8)	10:1, ±1%

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE	PART NO.
		Method: Tray PKG-0838 www.we-online.com/midcom		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	TRANSFORMER	750310349
6B	8/11	SEE REVISION SHEET FOR REVISION LEVEL			eiSos p/n: 750310349	
6A	2/09					

