



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G2	REVISED PER ECN-22-165640	21JUL2022	RK	MF



- | | |
|---|---|
| 1 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING |
| 2 | POINT OF MEASUREMENT FOR PLATING THICKNESS. |
| 3 | ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS |
| 4 | BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN)
OR TO THE LEFT |
| 5 | OBsolete PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |

OBSOLETE



RECOMMENDED HOLE LAYOUT

	SUPERSEDED	3.984	3.900	39	80	4-103149-0
	OBSELETE	3.884	3.800	38	78	3-103149-9
	OBSELETE	3.784	3.700	37	76	3-103149-8
	OBSELETE	3.684	3.600	36	74	3-103149-7
△	SUPERSEDED BY 8-146308-6	3.584	3.500	35	72	3-103149-6
	OBSELETE	3.484	3.400	34	70	3-103149-5
	OBSELETE	3.384	3.300	33	68	3-103149-4
	OBSELETE	3.284	3.200	32	66	3-103149-3
	OBSELETE	3.184	3.100	31	64	3-103149-2
	OBSELETE	3.084	3.000	30	62	3-103149-1
	OBSELETE	2.984	2.900	29	60	3-103149-0
	OBSELETE	2.884	2.800	28	58	2-103149-9
	OBSELETE	2.784	2.700	27	56	2-103149-8
	OBSELETE	2.684	2.600	26	54	2-103149-7
	OBSELETE	2.584	2.500	25	52	2-103149-6
	OBSELETE	2.484	2.400	24	50	2-103149-5
	OBSELETE	2.384	2.300	23	48	2-103149-4
	OBSELETE	2.284	2.200	22	46	2-103149-3
	OBSELETE	2.184	2.100	21	44	2-103149-2
	OBSELETE	2.084	2.000	20	42	2-103149-1
	OBSELETE	1.984	1.900	19	40	2-103149-0
	OBSELETE	1.884	1.800	18	38	1-103149-9
	OBSELETE	1.784	1.700	17	36	1-103149-8
	OBSELETE	1.684	1.600	16	34	1-103149-7
△	OBSELETE	1.584	1.500	15	32	1-103149-6
△	OBSELETE	1.484	1.400	14	30	1-103149-5
△	OBSELETE	1.384	1.300	13	28	1-103149-4
	OBSELETE	1.284	1.200	12	26	1-103149-3
	OBSELETE	1.184	1.100	11	24	1-103149-2
	OBSELETE	1.084	1.000	10	22	1-103149-1
	OBSELETE	.984	.900	9	20	1-103149-0
△	OBSELETE	.884	.800	8	18	103149-9
	OBSELETE	.784	.700	7	16	103149-8
	OBSELETE	.684	.600	6	14	103149-7
	OBSELETE	.584	.500	5	12	103149-6
	OBSELETE	.484	.400	4	10	103149-5
△	OBSELETE	.384	.300	3	8	103149-4
	OBSELETE	.284	.200	2	6	103149-3
△	SUPERSEDED BY 5-146308-2	1.184	1.100	1	4	103149-2
△	OBSELETE	.084	—	—	2	103149-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL CHK T. CLARK		230CT87 230CT87		 TE Connectivity			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		HEADER ASSY, MOD II, BREAKAWAY, DOUBLE ROW, .100X.100LC, RA, WITH .025 SQ POSTS			
INCHES		APVD T. CLARK		290CT87					
		PRODUCT SPEC							
		—							
		APPLICATION SPEC							
		—							
		ANGLES ± —							
MATERIAL: HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK POST: COPPER ALLOY		FINISH :POST: 000000 GOLD IN THE CONTACT AREA, 000100F-000200 MATTE PH-LD ON THE SOLDER PAIL, ALL OVER 000000 NICKEL		WEIGHT —		A1 — C-103149 —			
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 1		REV G2	