














FLOW SOLDER POST CONTACTS
(-1, -3, -5, -7, OUTSIDE ROWS ONLY, AS SHOWN)
(-9, 1- -1, 1- -3, 1- -5, WITH ALL 3 ROWS FULLY LOADED)



RECOMMENDED P. C. BOARD LAYOUT
WIRE WRAP TYPE



TYPE IV

	M55302/130-16	240	IV	240	1-447208-6
	M55302/130-15	240	IV	240	1-447208-5
	M55302/130-14	240	III	240	1-447208-4
	M55302/130-13	240	III	240	1-447208-3
	M55302/130-12	240	II	240	1-447208-2
	M55302/130-11	240	II	240	1-447208-1
	M55302/130-10	240	I	240	1-447208-0
	M55302/130-09	240	I	240	447208-9
	M55302/130-08	160	IV	240	447208-8
	M55302/130-07	160	IV	240	447208-7
	M55302/130-06	160	III	240	447208-6
	M55302/130-05	160	III	240	447208-5
	M55302/130-04	160	II	240	447208-4
	M55302/130-03	160	II	240	447208-3
	M55302/130-02	160	I	240	447208-2
	M55302/130-01	160	I	240	447208-1
REMARKS	MILITARY PART NUMBER	NUMBER OF CONTACTS	TYPE	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 5-4-90 CHK T. SHUEY D. MILLER 6-1-90		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± — 1. PLC ± — 2. PLC ± — 3. PLC ± .005 [0.13] 4. PLC ± — ANGLES ± —		NAME RECEPTACLE ASSEMBLY, BOX, .100 C/L, W/KEYING HARDWARE —	
MATERIAL  SEE TABLE		WEIGHT —		SIZE A1	
		CUSTOMER DRAWING		CAGE CODE 00779	
				DRAWING NO C-447208	
				RESTRICTED TO —	
				SCALE 5:1 SHEET 1 OF 1 REV G	