




LOC	DIST	REVISIONS				
		TP	LTR	DESCRIPTION	DATE	OWN
GP	00	H		REVISED PER ECO-11-009374	24MAY2011	CJV



- 1 MOLDED PARTS: FLAME RETARDANT, 94V-0 RATED, GLASS FILLED NYLON OR POLYESTER, BLACK
CONTACTS: BRASS
HARDWARE: ZINC
- 2 CONTACTS: SEE TABLE
HARDWARE: CLEAR CHROMATE
- 3 GOLD FLASH ON THE MATING SURFACES, .000100 MIN TIN OR TIN-LEAD PLATE ON THE SOLDER END, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE CONTACT.
- 4 .000030 MIN GOLD PLATE ON THE MATING SURFACES, .000100 MIN TIN OR TIN-LEAD PLATE ON THE SOLDER END, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE CONTACT.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL PLATE, .000030 MIN TOTAL ON THE MATING SURFACES, .000100 MIN TIN OR TIN-LEAD PLATE ON THE SOLDER END, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE CONTACT.
- 5 REFER TO APPLICATION SPEC FOR RECOMMENDED P.C. BOARD MOUNTING DIMENSIONS FOR AUTOMATIC INSERTION.



P.C. BOARD MOUNTING DIMENSIONS 5

SUPSD BY 747467-4	WITH SCREWLOCKS	4	747467 -6
OBSOLETE	WITH SCREWLOCKS	3	747467 -5
	WITH INSERTS	4	747467 -4
SUPSD BY 747467-4	WITH INSERTS	3	747467 -3
	WITH .120 DIA HOLE	4	747467 -2
	WITH .120 DIA HOLE	3	747467 -1
REMARKS		FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C RICHARD 7-29-87	TE Connectivity	
		CHK S WELDON 8-3-87		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD B TAYLOR 8-3-87	NAME	
		PRODUCT SPEC	PLUG ASSY, SIZE 1, 9 POSN, RIGHT ANGLE, .590 SERIES, .026 DIA POSTS, AMPLIMITE® HD-20	
MATERIAL	FINISH	APPLICATION SPEC	SIZE	
		ANGLES	CAGE CODE DRAWING NO	
1	2	WEIGHT	A1 00779 747467	
		CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV H	