



VICOR CONFIDENTIAL

THIS DOCUMENT AND THE DATA DISCLOSED
HEREIN OR HEREWITHE IS NOT TO BE REPRODUCED,
USED, OR DISCLOSED IN WHOLE OR IN PART
TO ANYONE WITHOUT PERMISSION OF VICOR CORP.

REV.	DESCRIPTION	DATE	APPROVED
1	RELEASED PER E060599	PEI	03/16/06
2	REVISED PER ECO Request E060019	REJH	10/27/06
3	REVISED PER E080938	SA	5/6/08



NOTES:

1. ASSEMBLY TO BE FREE OF NICKS.
2. WINDINGS TO BE EVENLY SPACED.
3. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION, MAGNETICS SECTION.
4. GENERAL WORKMANSHIP STANDARDS FOR MAGNETIC COMPONENTS PER WS-0002.

TEST	ITEM NO.	WINDING	NO. OF TURNS	INDUCTANCE (uH)
100 KHz Vac = 10mV	2	1 PRIMARY	6	1.70 - 2.15

REF VICOR P/N 32497

DRAWN BY KNIGHT	DATE 02/08/06	VICOR					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ±1/64 .XX= *.01 ± 1° .XXX= *.005							
THIRD ANGLE PROJECTION							
SIZE B	FSCM NO. 67131	DWG NO 32498	REV 3				
SCALE NONE		SHEET 1	OF 1				

DO NOT SCALE DRAWING