







NOTES:

1. PERFORMANCE:

- A) MEETS PERFORMANCE AND ENVIRONMENTAL REQUIREMENTS OF MIL-T-81714/2
B) MODULES ARE TO BE MOUNTED INTO RACK ASSEMBLY M81714/5 OR/16 OR COMMERCIAL EQUIVALENT.
C) DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS AT SEA LEVEL, 200 VRMS AT 100,000 FEET.
D) OPERATING TEMPERATURE: -65 C TO 200 C.
E) CURENT RATING: 7.5 AMPS
F) VIBRATION AND SHOCK: MIL-T-81714 PARAGRAPH 3.5.5 AND 3.5.8

2. MATERIALS:

- A) HOUSING - POLYETHERIMIDE, COLOR: BLACK.
B) GROMMET - SILICONE ELASTOMER, COLOR: BLUE
C) INTERNAL CONTACTS - COPPER ALLOY, GOLD PLATED
D) CONTACT RETAINERS - STAINLESS STEEL.

APCD P/N	SUPPLIED				MARKING		CLASS
	QTY.	MIL. P/N	APCD P/N	QTY.	APCD QPL NO.	MIL. NO	
TJM120606	--	--	--	--	TJM120706	M81714/2-DC2	D
TJM120706	11	M39029/1-101	CNP006000	2			

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd SPECIFICATION DRAWING		TITLE TERMINAL JUNCTION MODULE SZ 20 FEEDBACK, DC2				
ANSI Y14.5M UNITS: INCHES Pro/E FILE	.XX ±0.01 .XXX ±0.005 ANGLES ±2.0°		DRWN A. SWEEZEY 03/09/06						
ORIGINAL 	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., PEABODY, MA		ENGR R. SWAINE 03/01/06		SIZE B	DWG NO. TJM120606		REV C	
			APPD 						
			4-13-06						
			CODE: 58982		SCALE: 3:1		SHEET 1 OF 1		