


RoHS COMPLIANT

REVISIONS

ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	INITIAL DESIGN	2008/09/10	Kevin Kibben/Kiao



ELECTRICAL DATA

1. VSWR:

900MHz	: 1.0758
1.8GHz	: 1.1069
2.4GHz	: 1.1508
3.0GHz	: 1.1197

3. Insertion loss:

900MHz	: - .4934dB
1.8GHz	: - .6824dB
2.4GHz	: - .7853dB
3.0GHz	: - .8740dB

2. Return loss:

900MHz	: - 28.752dB
1.8GHz	: - 25.886dB
2.4GHz	: - 23.061dB
3.0GHz	: - 24.948dB

4. Impedance: 50 ohm

Note: 1) THE ORENTATION SHOULD BE SAME AS SHOW.
2) WASHER AND NUT SHOULD BE BULK PACKED SEPERATE FROM CABLE ASSEMBLY.

bec Bobbintron Electrical Corp.
www.bobbintron.com

TITLE
SMA bulk Jack + 1.13L216 + I-PEX

DWG NO. 080910-03	CUSTOMER P/N 45009575L	UNIT mm	REV. 1
GENERAL TOLERANCES X NA XX NA XXX NA ANGLES NA		SCALE 1 : 1	APPROVALS
		SIZE A4	DRAWN BY: Kevin Kibben/Kiao 2008/09/10
			CHKO BY: Kevin 2008/09/10
(UNLESS OTHERWISE SPECIFIED)		SHEET 1 of 1	APPD BY: Jared 2008/09/10

06	I-PEX MHF Plug	1	20278-111R-13
05	1.13-MIT coaxial cable (Gray)	1	
04	Heatshrink	1	
03	SMA ST bulk Jack	1	
02	Nut	1	
01	Washer	1	
NO	DESCRIPTION	Q'TY	DRAWN NO.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Multi-Tech Systems:

[CASMA-UFL-10](#) [CASMA-UFL-1](#)