




Features

- Single-turn cermet/open-frame
- Rotor design compatible with pick and place and automatic adjustment equipment
- 2 mm size meets EIA/EIAJ standard trimmer footprint
- RoHS compliant* - see [processing information](#) on RoHS compliant surface mount trimmers
- For trimmer applications/processing guidelines, [click here](#)

TC42 - 2 mm SMD Trimpot® Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range
.....100 ohms to 1 megohm
(see standard resistance table)
Resistance Tolerance $\pm 25\%$ std.
Absolute Minimum Resistance
≤ 1K Ohms 20 ohms max.
> 1K Ohms 2 % max. of TR
Contact Resistance Variation .. 5 % max.
Resolution Essentially infinite
Adjustment Angle $240^\circ \pm 20^\circ$

Environmental Characteristics

Power Rating (50 VDC max.)
70 °C 0.1 watt
Temperature Range ... -40 °C to +100 °C
Temperature Coefficient ... ± 250 ppm/°C
Humidity 95 % RH
TRS Max. $\pm 5\%$
Load Life
.....@70 °C rated power 1000 hours
TRS $\pm 5\%$
Rotational Cycling 20 cycles
TRS $\pm 10\%$

Physical Characteristics

Torque..... 0.49 - 7.84 mN-m max.
Mechanical Angle ... Continuous rotation
Marking..... Part marking code
Standard Packaging.. 3000 pcs./7 " reel
Adjustment Tool..... H-90

Aqueous cleaning not recommended.

How To Order

TC42 X - 2 - 103 E

Model _____
Style _____
Standard Product Indicator _____
-2 = Cross Slot Rotor
Resistance Code _____
Embossed Tape Designator _____
E = 3000 pcs./7 " Reel (Standard)

Standard Resistance Table

Resistance (Ohms)	Resistance Code
100	101
200	201
500	501
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
50,000	503
100,000	104
200,000	204
500,000	504
1,000,000	105

Popular distribution values listed in boldface.


*RoHS Directive 2002/95/EC Jan 27, 2003 including Annex.

"Trimpot" is a registered trademark of Bourns, Inc.


Specifications are subject to change without notice.

Customers should verify actual device performance in their specific applications.


Product Dimensions



Recommended Land Pattern



Packaging Specifications



DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

