

6 OBsolete PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI		ON SOLDER TAIL, ALL OVER 0.00127 [0.000050] NICKEL.		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. T. HOFFMAN 21-8-95		STE TE Connectivity	
				CHK. 4-12-95		APVD. G. DUBNICZKI 4-12-95			
		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		HEADER ASSEMBLY, MOD II, BREAKAWAY, HIGH TEMPERATURE,RIGHT ANGLE, DOUBLE ROW, .100 X.100 C/L, W/.025 SQUARE POSTS	
				0 PLC ± - 1 PLC ± - 2 PLC ± 0.51[.02] 3 PLC ± 0.127[.005] 4 PLC ± 0.0127[.0005] ANGLES ± -		0 PLC ± - 1 PLC ± - 2 PLC ± 0.51[.02] 3 PLC ± 0.127[.005] 4 PLC ± 0.0127[.0005] ANGLES ± -		PRODUCT SPEC — APPLICATION SPEC —	
MATERIAL 4		FINISH SEE TABLE		WEIGHT —		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
				CUSTOMER DRAWING		A1 00779 C=146309		—	
						SCALE 4:1		SHEET 1 OF 1	
								REV A.3	

4805 (3/11)