

750850-3 Product Details



750850-3

TE Internal Number: 750850-3

 [Active](#)

.050 Series Cable Connectors (SCSI)

[Not EU RoHS or ELV Compliant](#) ([Find RoHS Compliant Alternates](#))

Product Highlights:

- Hardware
- Hardware Type = Backshell Kit
- 26 Positions
- Cable Insulation Diameter = 7.11 - 7.87 mm
- With Mating Connector Lock

[View all Features](#)

Documentation & Additional Information

Product Drawings:

- [BACKSHELL KIT, 26 POSITION, PLUG, UNKEYED, SLIMLINE, A...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [AMPLIMITE SUBMINATURE D TYPE CONNECTORS](#) (PDF, English)
- [AMPLIMITE Subminiature D Connectors - .050 Series Co...](#) (PDF, English)

Product Specifications:

- [Connector, AMPLIMITE, .050 Series, Slimline](#) (PDF, English)
- [Connector, AMPLIMITE, .050 Series, Slimline](#) (PDF, Japanese)

Application Specifications:

- [AMPLIMITE .050 Series Slimline Connectors](#) (PDF, English)

Instruction Sheets:

- [Manual Arbor Frame Assembly 58024-1](#) (PDF, English)
- [Manual Arbor Frame Assembly 91085-2](#) (PDF, English)
- [AMP* REPAIR TOOL 58430-1 FOR AMPLIMITE* .050-SERIES ...](#) (PDF, English)
- [Hand Crimping Tool Frame Assembly 543344-1 \(Used to ...](#) (PDF, English)
- [Installation and Use of Mass Termination Tooling](#) (PDF, English)
- [Tooling Kit](#) (PDF, English)
- [Die Holder Assemblies](#) (PDF, English)
- [AMP AMPLIMITE .050 SERIES CRIMPER ASSEMBLY 856684-1](#) (PDF, English)
- [Die Assembly 90437-1](#) (PDF, English)
- [Tooling Assy Used w/Miniature Applicator Frame](#) (PDF, English)

CAD Files:

- None Available

[List all Documents](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Hardware
- Number of Positions = 26
- [Mating Connector Lock](#) = With
- [Mating Connector Lock Type](#) = Male Jackscrew

Body Related Features:

- Cable Insulation Diameter (mm [in]) = 7.11 - 7.87 [0.280 - 0.310]

Industry Standards:

• Mating Connector: ESH Type = Male Jackscrew • Shielded = Yes • Product Series = Slimline • Mating Polarization Type = Unkeyed • Backshell Material = Copper-Nickel Alloy • Color = Gray • Jackscrew Material = Steel Mechanical Attachment: • Hardware Type = Backshell Kit • Jackscrew Plating = Tin over Copper	• RoHS/ELV Compliance = Not ELV/RoHS compliant • Lead Free Solder Processes = Not relevant for lead free process Conditions for Usage: • Terminate To = Wire Packaging Related Features: • Packaging Method = Individual Kit Other: • Brand = AMP
--	--