







LOC	DIST	REVISIONS				
		REV	DESCRIPTION	DATE	BY	APP'D
CM	0	E1	REVISED PER ECO-11-004587	11MAR11	RK	HMR

1. INSULATION RANGE: 1.09–2.79 [.043–.110]
WIRE RANGE: 0.2–0.9 mm (24–18) AWG.
2. 0.00203 [.000080] MIN BRIGHT TIN–LEAD OVER
0.00127 [.000050] MIN NICKEL.
3. 0.00076 [.000030] MIN THICK GOLD STRIPES IN
LOCALIZED PLATE AREA ON BEAM AND DIMPLE OVER
0.00127 [.000050] MIN THICK NICKEL OVER ENTIRE
CONTACT.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
5. 0.00203 [.000080] MIN BRIGHT TIN OVER
0.00127 [.000050] MIN NICKEL.




SECTION B–B

SECTION C–C



3–DIMENSIONAL MODELS
NTS



5	3–770522–1
3	770522–2
2	770522–1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 17MAY3006	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK J. ELLIS 17MAY2006	NAME RECEPTACLE, SL-156, LOOSE PIECE	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. ELLIS 17MAY2006	PRODUCT SPEC	
0. PLC ± .005		APPLICATION SPEC		SIZE
1. PLC ± .005		WEIGHT		CAGE CODE
2. PLC ± .005		DRAWING NO		RESTRICTED TO
3. PLC ± .005		A1 00779		—
4. PLC ± .005		C=770522		—
ANGLES		CUSTOMER DRAWING		SCALE
FINISH		10:1		SHEET
—		1		OF
—		1		REV
—		E1		—