



MATED WITH: PASSEND ZU: —	LOC	DIST	REVISIONS						
	A1	—	P	LTR	DESCRIPTION	DATE	DWN	APVD	
PROJECT NR., 87-9187				D8	REVISED PER ECR-11-025934	29DEC11	RK	HMR	



Bemerkungen

NOTES

- 1  Werkzeuggestrenngrat max. 0.5 hoch und 0.02 dick zulässig
(sonst kein Grat zulässig)
BURRS MAX. 0.5 HIGH AND 0.02 THICK PERMITTED
(NO BURRS ELSE PERMITTED)
- 2 Einzelheiten der Ausführung bleiben dem Hersteller überlassen
DETAILS OF DESIGN ARE LEFT TO MANUFACTURER
- 3 Passend für Kammer: $\phi 6.4\text{mm}$
SUITABLE FOR CAVITY: $\phi 6.4\text{mm}$
- 4 Passend für Isolationsdurchmesser: 3 – 3.7mm
SUITABLE FOR INSULATION DIAMETER: 3 – 3.7mm
- 5 Bestückungshilfe für Einzelleiterabdichtung siehe: TE CONNECTIVITY:965702
INSERTER FOR SINGLE WIRE SEAL SEE :
- 6 Keine Luftlöcher zulässig
NO AIR BUBBLES PERMITTED



M 1:1

D6

DIMENSIONS:		DWN	17 APR 97	MATERIAL		FINISH			
mm		P. Gaupp		—		—			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 0015 ISO 2768 ISO 15001 - 160 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		CHK	21 APR 97	TE TE Connectivity					
		D. Kuempel							
		APVD		—		NAME			
		PRODUCT SPEC		108-18263-1		2.5mm System, Einzeldichtung			
APPLICATION SPEC		114-18031		2.5MM SYSTEM, SINGLE WIRE SEAL					
		WEIGHT	—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		A4		00779	C-828985		—		
		CUSTOMER DRAWING				SCALE	5:1	SHEET	1 of 1