

SOLDER TAIL





Fig. 1

Terminal Style 2,5,6,7

- Allows for maximum air circulation under the ICs.
- Sockets are XY stackable.
- Socket pins feature closed-end construction eliminating any solder wicking problems.
- Series 694 use MM #0132, #0135, #0255, #0442, #0548, #0552-1, #0552-2, #1401 or #8855 pins. See pages 126, 127, 134, 139 and 140 for details.
- Direct visibility for soldering, inspection and repair.



For RoHS compliance
select ◇ plating code.

LOW PROFILE




Fig. 2

Terminal Style 4

ULTRA LOW PROFILE




Fig. 3

Terminal Style 0,3,1

REDUCED BARRELL




Fig. 4

Terminal Style 8

Total number of pins				Quantity per tube
	A	B	C	
6	7,6	7,62	10,1	67
8	10,1	7,62	10,1	50
14	17,7	7,62	10,1	28
16	20,3	7,62	10,1	25
18	22,8	7,62	10,1	22
20	25,3	7,62	10,1	20
22	27,8	7,62	10,1	18
24	30,4	7,62	10,1	16
24	30,4	10,16	12,7	16
24	30,5	15,24	17,7	16
28	35,5	15,24	17,7	14
32	40,6	15,24	17,7	12
40	50,8	15,24	17,7	10

Ordering Information

**XX= Plating Code
See Below**

**RoHS
2002/95/EC**

694-XX-306-00-67Y000
694-XX-308-00-67Y000
694-XX-314-00-67Y000
694-XX-316-00-67Y000
694-XX-318-00-67Y000
694-XX-320-00-67Y000
694-XX-322-00-67Y000
694-XX-324-00-67Y000

694-XX-424-00-67Y000

694-XX-624-00-67Y000
694-XX-628-00-67Y000
694-XX-632-00-67Y000
694-XX-640-00-67Y000

Socket Pin Information

↓	Terminal Length	Body Diameter		Fig. #	
Y = 0	3,45	0,97		3	
Y = 1	3,45	0,97		3	
Y = 2	3,18	0,51		1	
Y = 3	4,32	0,97		3	
Y = 4	4,19	1,35		2	
Y = 5	3,63	0,51		1	
Y = 6	4,57	0,51		1	
Y = 7	6,99	0,51		1	
Y = 8	3,94	0,86		4	
SPECIFY PLATING CODE XX=		93	99	43 ◇	44 ◇
Sleeve (Pin)		5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn	5,08µm Sn
Contact (Clip)		0,76µm Au	5,08µm Sn/Pb	0,76µm Au	5,08µm Sn