

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION ,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

E

REV PER 063A-0541-00

25SEP00

JR

TM

1

WIRE INSULATION DIA IS 3.18-3.50  
[.125-.138]

RING "A"  
COLOR: NONE

RING "B"  
COLOR: NONE

SLEEVE

2.67  
[.105]

7.21  
[.284]

3.56  
[.140]  
REF 2 PLC

13.34  
[.525] MAX

TEFLON ASTM D-1710

SLEEVE

COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290

RING "B"

COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290

RING "A"

MATERIAL / FINISH

DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN  
JR RUTH  
31MAY00

CHK  
R HERSEY  
31MAY00

APVD  
T MICHIELUTTI  
31MAY00

AMP

AMP Incorporated  
Harrisburg, PA 17105-3608

DIMENSIONS:  
MM [INCHES]

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ±-  
1 PLC ±-  
2 PLC ±0.40 [.015]  
3 PLC ±-  
4 PLC ±-  
ANGLES ±-

PRODUCT SPEC  
-  
APPLICATION SPEC  
-  
WEIGHT  
-

PRE-INSULATED SPARE WIRE CAP

MATERIAL  
SEE TABLE

FINISH  
SEE TABLE

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C- 328861

RESTRICTED TO  
-

CUSTOMER DRAWING

SCALE  
10:1

SHEET  
1 OF 1

REV  
E

AMP 1470-19 REV 11JUN97

25-SEP-00 13:56:29 amp13469 /home/amp13469/ednmod