




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
F		REVISED PER ECR-16-013298	02JUN2017	FL	SY



- NOTES:**
- 1 MATERIAL CONTACTS; PHOSPHORBRONZE
MATERIAL SHIELDS ; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
 - 2 GENERAL CONTACT PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1,27µm NICKEL MIN. AND ACTION PIN: 0,5µm TIN
MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
REFERENCE FOR EACH DASH NUMBER.
 - 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
 - 4 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.
 - 5 REDUCED CROSS-TALK SHIELD: GOLD FLASH OVER 1,27 µm
NICKEL MIN.
 - 6 ASSEMBLY PRINTED WITH P/N AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE
OR ON THE BACK SIDE.
 - 7 HOLE PATTERN FOR FEMALE CONNECTOR TYPE B
125 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
 - 8 ROW "f" 13 PLATED THROUGH HOLES FOR UPERSHIELD
 - 9 PLATED SPOT ONLY ON COMPONENT SIDE, FORMING
ONE CONTACT WITH PLATED THROUGH HOLES OF ROW C
 - 10 SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED
ADHESIVE TAPE OR ADHESIVE
 - 11. BASIC P.N. LOWERSHIELD: 5338110



RECOMMENDED P.C.B. HOLE LAY-OUT
 COMPONENT SIDE AS SHOWN
 SCALE 2,5:1



P.C.B. HOLE DIM. ACTION PIN
 FOR DETAILS SEE
 APPLICATION SPECIFICATION

OBSELETE	2 4 5	1	5352345-4
	2 3 5	1	5352345-1
	FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN K.N.KIRAN 24AUG2004	TE Connectivity
CHK B.MOOIJ 22MAR2005	
APVD B.MOOIJ 22MAR2005	NAME
PRODUCT SPEC 108-19082	Z-PACK 2mm HM TYPE B PRE-SHIELDED RECEPTACLE WITH RED.CROSS-TALK SHIELDS
APPLICATION SPEC 114-19029	SIZE A2
WEIGHT 0.000000	CAGE CODE 00779
CUSTOMER DRAWING	DRAWING NO C=5352345
	RESTRICTED TO -
	SCALE 5:1
	SHEET 1 of 1
	REV F