


By accepting this proprietary Huck drawing, recipient agrees not to reproduce or disclose any part thereof to any others without the written permission of Huck International, Inc.

REV	DESCRIPTION	DATE
A	RELEASE	5-19-94
B	EXTENSION P/N 124360 WAS 115829	10-31-94
C	ADDED NOTE 2	1-26-95
D	FILE OBSOLETE, SS BY 99-3310B/F/P	05-01-95

NOTES:

- 1 SHIP WITH DRIVING ANVIL P/N 124185 IN SEPARATE BAG.
- 2 ADAPTER ASSEMBLY P/N 119327 AVAILABLE FOR USE WITH CHERRY TOOL MODEL G743.



MATERIAL:	-	SPEC: -	TOLERANCES UNLESS OTHERWISE SPECIFIED	HUCK INTERNATIONAL, INC., I.S.D. 85 GRAND STREET, P.O. BOX 2270 KINGSTON, NEW YORK 12401		
HARDNESS:	-			NOSE ASSEMBLY -06 MAGNATITE		
HEAT TREAT:	-	SPEC: -	.XX, .XXX ±			
SURF. TREAT:	-	SPEC: -	INT. COR. RADII			
SURFACE FINISH NOT TO EXCEED	Ra		BREAK EDGES	DET: T.L.	CK:	DATE: 5-19-94
IDENTIFICATION PER SPEC 42-311: ★ ETCH			ANGLES ±	DATE: 5-19-94	SCALE: 2/1	
SURFACES TO BE	◎, //, ⊕, ⊥, & ▽ WITHIN		T.I.R.	FINAL ASSY: 2400 TOOL	FOC.	
					FAC.	

FORM: KE104 REV B

B

99-3310