

Frequency Mixers

LEVEL 7 (+7 dBm LO, up to +1 dBm RF)

Models

TUF-1
 TUF-1SM

T-74-09-01



computer-automated performance data

typical production unit / for data of other models consult factory

mixer conversion loss and isolation

RF MHz	LO MHz	Conversion Loss (dB)			Isolation L-R (dB)			Isolation L-I (dB)		
		LO + 4 dBm	LO + 7 dBm	LO + 10 dBm	LO + 4 dBm	LO + 7 dBm	LO + 10 dBm	LO + 4 dBm	LO + 7 dBm	LO + 10 dBm
2.000	32.000	7.09	6.81	6.58	87.30	81.85	77.21	68.80	72.15	73.61
4.000	34.000	6.68	6.40	6.19	78.00	76.35	73.81	66.70	68.25	68.21
5.000	35.000	6.62	6.34	6.12	75.70	74.35	72.61	65.80	66.65	66.71
10.000	40.000	6.54	6.25	6.02	69.63	69.58	68.44	62.53	62.18	61.74
20.000	50.000	6.46	6.21	5.98	64.30	64.25	64.03	58.40	57.65	56.43
50.000	80.000	6.36	6.13	5.95	57.56	57.73	57.67	52.41	50.60	49.26
81.733	51.733	6.44	6.16	5.95	53.47	53.89	54.19	48.78	46.89	45.69
100.000	70.000	6.48	6.18	5.96	51.89	52.31	52.63	47.30	45.35	44.00
161.467	131.467	6.34	6.08	5.91	48.63	49.28	49.54	43.72	42.03	40.89
200.000	170.000	6.15	6.03	5.89	47.02	47.46	47.65	41.84	40.24	39.02
241.200	211.200	6.17	6.04	5.90	46.01	46.41	46.63	40.25	38.76	37.49
281.067	251.067	6.18	6.04	5.90	44.63	45.16	45.38	38.53	37.18	36.02
300.000	270.000	6.35	6.09	5.92	44.31	44.55	44.64	38.08	36.84	35.72
320.933	290.933	6.31	6.08	5.92	43.71	44.04	43.87	37.13	35.94	34.79
400.667	370.667	6.18	5.99	5.86	42.32	42.93	42.99	33.91	33.45	32.72
480.400	450.400	6.28	6.06	5.90	40.18	40.46	40.80	31.33	30.91	30.51
500.000	470.000	6.33	6.11	5.95	39.89	40.16	40.42	31.07	30.63	30.27
560.133	530.133	6.35	6.15	5.99	39.63	39.99	40.02	29.59	29.30	28.68
580.067	550.067	6.41	6.19	6.02	39.64	40.02	40.17	29.36	29.24	28.71
600.000	570.000	6.45	6.26	6.10	39.55	39.76	39.73	28.83	28.69	28.09

mixer VSWR

φ detection

FREQ. (MHz)	VSWR RF port			VSWR LO port			VSWR IF port			FREQ. (MHz)	max DC output mV	DC offset mV
	LO + 4 dBm	LO + 7 dBm	LO + 10 dBm	LO + 4 dBm	LO + 7 dBm	LO + 10 dBm	LO + 4 dBm	LO + 7 dBm	LO + 10 dBm			
2.000	1.53	1.56	1.58	1.90	2.71	3.80	1.34	1.19	1.09	2.000	-230.82	-0.05
4.000	1.28	1.31	1.34	1.82	2.64	3.73	1.34	1.19	1.10	4.000	-231.66	-0.01
5.000	1.22	1.25	1.29	1.81	2.62	3.70	1.34	1.19	1.09	5.000	-230.98	-0.07
10.000	1.10	1.15	1.20	1.67	2.47	3.54	1.35	1.19	1.10	10.000	-230.48	0.02
20.000	1.04	1.11	1.17	1.71	2.51	3.57	1.35	1.19	1.10	20.000	-225.17	0.02
50.000	1.02	1.10	1.16	1.67	2.46	3.50	1.36	1.20	1.12	50.000	-238.30	0.02
100.000	1.09	1.13	1.17	1.64	2.41	3.42	1.39	1.24	1.16	81.733	-244.03	-0.01
109.640	1.11	1.14	1.18	1.62	2.37	3.36	1.39	1.25	1.17	100.000	-251.23	0.04
169.440	1.19	1.20	1.24	1.61	2.31	3.24	1.44	1.31	1.24	161.467	-233.45	0.06
217.280	1.25	1.27	1.29	1.60	2.29	3.19	1.49	1.36	1.30	200.000	-234.93	0.03
265.120	1.32	1.33	1.36	1.61	2.26	3.14	1.55	1.43	1.37	241.200	-250.57	0.14
300.000	1.38	1.38	1.40	1.63	2.28	3.16	1.63	1.52	1.46	281.067	-248.51	0.07
324.920	1.41	1.42	1.44	1.65	2.30	3.17	1.62	1.48	1.42	300.000	-239.16	0.10
372.760	1.49	1.50	1.51	1.68	2.31	3.19	1.71	1.57	1.51	320.933	-239.97	0.14
420.600	1.58	1.58	1.59	1.71	2.32	3.16	1.80	1.66	1.59	400.667	-252.65	0.37
468.440	1.66	1.66	1.67	1.78	2.33	3.12	1.89	1.74	1.68	480.400	-232.77	0.59
500.000	1.72	1.71	1.72	1.79	2.33	3.11	1.95	1.80	1.73	500.000	-226.52	0.58
540.200	1.79	1.77	1.78	1.84	2.35	3.10	2.03	1.88	1.80	560.133	-225.65	0.94
588.040	1.88	1.86	1.86	1.86	2.36	3.12	2.12	1.97	1.89	580.067	-227.84	0.87
600.000	1.90	1.88	1.88	1.88	2.38	3.14	2.14	1.99	1.91	600.000	-231.92	0.89



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
 Distribution Centers/NORTH AMERICA 800-654-7949 417-335-5935 Fax 417-335-5945 EUROPE 44-252-835094 Fax 44-252-837010

2 to 600 MHz

Mini-Circuits

ULTRA-REL™ MIXERS

5-YR. GUARANTEE*

mixer harmonic intermodulation

(relative to desired IF output)

T-74-09-01

RF ORDER HARMONIC	RF CAL	0	1	2	3	4	5	6	7	8	9	10
0	-	-	4	22	13	36	36	34	23	38	57	41
1	-	21	+0	27	12	30	19	39	44	36	37	36
2	96	66	51	61	50	70	49	60	62	> 74	59	59
3	> 96	> 75	> 75	> 75	> 75	75	67	> 75	71	> 74	> 74	71
4	95	74	> 75	> 75	72	74	> 76	74	74	> 75	> 75	> 74
5	> 95	> 74	73	> 75	> 76	> 75	> 75	> 75	> 75	> 75	> 74	74
6	> 96	> 74	> 53	> 74	72	> 75	> 75	75	> 75	75	> 75	> 75
7	> 96	> 75	73	> 74	> 75	> 75	74	> 76	> 75	> 75	74	> 76
8	> 96	> 75	> 74	72	> 74	> 75	> 75	> 75	75	75	> 76	> 76
9	> 95	74	> 75	> 74	> 74	> 74	> 74	> 74	> 75	> 75	74	> 75
10	95	> 76	> 75	> 75	> 75	73	> 74	73	> 75	> 75	> 76	> 75
		0	1	2	3	4	5	6	7	8	9	10
		Harmonic LO Order										







RF ORDER HARMONIC	RF CAL	0	1	2	3	4	5	6	7	8	9	10
0	-	-	13	34	26	54	48	43	36	60	65	58
1	-	16	+0	28	11	31	25	42	44	40	42	40
2	95	61	40	52	41	58	41	59	54	66	51	56
3	95	55	49	50	45	52	47	58	50	56	62	53
4	> 96	73	62	62	59	64	57	74	60	68	65	80
5	> 95	79	76	67	65	63	64	67	60	72	59	75
6	> 95	84	73	83	75	77	76	81	73	75	72	83
7	> 95	> 84	> 84	84	84	82	79	> 85	> 85	82	84	84
8	> 97	> 85	> 85	> 84	> 84	> 85	> 85	> 85	> 85	84	> 85	82
9	> 96	> 84	> 84	> 84	> 84	80	> 84	> 85	> 85	82	> 86	84
10	> 96	84	82	82	83	> 85	> 84	> 82	> 85	82	> 85	85
		0	1	2	3	4	5	6	7	8	9	10
		Harmonic LO Order										

test condition: RF IN: 490.10 MHz; -14.94 DBM
LO IN: 460.01 MHz; +7.01 DBM
IF OUT: 30.09 MHz; -20.78 DBM

test condition: RF IN: 490.10 MHz; -5.03 DBM
LO IN: 460.01 MHz; +7.01 DBM
IF OUT: 30.09 MHz; -10.93 DBM

typical performance curves

(production unit)



In Stock...Immediate Delivery