


SCHOTTKY BARRIER RECTIFIERS
REVERSE VOLTAGE – 30 to 45 Volts
FORWARD CURRENT – 30 Amperes

FEATURES

- Metal of silicon rectifier, majority carrier conduction
- Guard ring for transient protection
- Low power loss, high efficiency
- High current capability, low VF
- High surge capability
- Plastic package has UL flammability classification 94V-0
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

MECHANICAL DATA

- Case: TO-220AB molded plastic
- Polarity : As marked on the body
- Weight: 0.08 ounces, 2.24 grams
- Mounting position: Any
- Max. mounting torque=0.5 N.m(5.1 Kgf.cm)

TO-220AB


TO-220AB		
DIM.	MIN.	MAX.
A	14.40	15.20
B	9.65	10.67
C	2.54	3.43
D	5.84	6.86
E	8.26	9.28
F	-	4.20
G	12.70	14.73
H	2.29	2.79
I	0.51	1.14
J	0.30	0.64
K	3.53 $\varnothing$	4.09 $\varnothing$
L	3.56	4.83
M	1.14	1.40
N	2.03	2.92
O	1.14	1.70
All Dimensions in millimeter		

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

PARAMETER	SYMBOL	SBL3030CT	SBL3040CT	SBL3045CT	UNIT
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	30	40	45	V
Maximum RMS Voltage	V_{RMS}	21	28	31	V
Maximum DC Blocking Voltage	V_{DC}	30	40	45	V
Average Rectified Output Current @TC=95°C	I_F	30			A
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load	I_{FSM}	250			A
Maximum Forward Voltage (Note 1) $I_F=15A@T_J=25^\circ C$	V_F	0.55			V
Maximum DC Reverse Current at Rated DC Blocking Voltage $T_J=25^\circ C$ $T_J=100^\circ C$	I_R	0.5 50			mA
Typical Junction Capacitance per element (Note 2)	C_J	450			pF
Typical thermal resistance Junction to Case (Note 3)	$R_{\theta JC}$	1.8			°C/W
Operating junction temperature range	T_J	-55 to +125			°C
Storage temperature range	T_{STG}	-55 to +150			°C

Note :

- (1) 300us Pulse Width, 2% Duty Cycle.
- (2) Measured at 1.0MHz and applied reverse voltage of 4.0 V_{DC} .
- (3) Thermal Resistance Junction to Case, device mounted on L200xW200xH2mm_copper heat sink.

REV.4, May-2012, KTHC62

FIG.1- FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3- TYPICAL REVERSE CHARACTERISTICS




FIG.4- TYPICAL FORWARD CHARACTERISTICS




FIG.5- TYPICAL JUNCTION CAPACITANCE





FIG.6- DC REVERSE VOLTAGE DERATING CURVE



Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.