


PRODUCT NUMBER
51760-ABBCCDDEF_ _ _ NOTE: ③
SEE NOTE 1



spec ref		*		dr		Julia Wang	2008/09/29	projection	MM	size	A4	scale	1:1
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng	Vicking Liu			2017/03/07	ecn noELX-DG-26294-1		
ISO 406						chr	Fancy Zhang			2017/03/07			
ISO 1101						appr	Pei-Ming Zheng			2017/03/08	product family		
surface		linear	0.X	±0.3	Amphenol FCI	titleRA REC w/GUIDE PIN POWER / SIGNAL / POWER				dwg no51760			revN
ISO 1302	0.XX		±0.13										
	0.XXX		±0.051										
angular		0°	±2°	cat. no.		-			Product - Customer Drw			sheet 1 of 3	

PRODUCT NUMBER	DIM	LENGTH FORMULAS (SEE NOTE 10)
51760-ABBCCDDEF_--- NOTE: ③	DIM "A"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .250 [6.35] x BB + .650 [16.51] (NOTE 10)
SEE NOTE 1	DIM "B"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .250 [6.35] x BB + .350 [8.89]
	DIM "C"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .250 [6.35] x BB + .300 [7.62]
	DIM "D"	.250 [6.35] x DD + .375 [9.53] Δ
	DIM "E"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .450 [11.43]
	DIM "F"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .250 [6.35] x BB + .680 [17.27]
	DIM "G"	.250 [6.35] x DD + .225 [5.72]
	DIM "H"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .250 [6.35]

CONNECTOR NOTES

- ① PRODUCT NUMBER CODE:
51760 - A BB CCC DD E F LF
- NO THIS SUFFIX: 100u"/2.54um SnPb ON PCB INTERFACE
ADD THIS SUFFIX: 78u"/2.00um Sn OR 5u" Au ON PCB INTERFACE
RETENTION TO PCB (NOTE 8)
TAIL OPTIONS (NOTE 7)
NUMBER OF LEFT END POWER CONTACTS (NOTE 6)
NUMBER OF SIGNAL CONTACTS (NOTE 5)
NUMBER OF RIGHT POWER CONTACTS (NOTE 4)
PLATING (NOTE 3)
BASE NUMBER

- ② HOUSING MATERIAL: GLASS FILLED V-O HIGH TEMP THERMO PLASTIC.
SIGNAL CONTACT MATERIAL: COPPER ALLOY
POWER CONTACT MATERIAL: COPPER ALLOY
- ③ PLATING OPTION:
1: SEE IN PRINT 10064183 FOR PLATING SPEC OF 51760-ABBCCDDEF; 51760-ABBCCDDEFLF
- ④ RIGHT END POWER CONTACTS, 01 TO 20 AVAILABLE.
MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR
- ⑤ SIGNAL CONTACTS, 004 TO 148 AVAILABLE FOR SOLDER TO BOARD.
020 TO 148 AVAILABLE FOR PRESS-FIT TO BOARD.
- ⑥ LEFT END POWER CONTACTS, 01 TO 20 AVAILABLE.
MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR
- ⑦ TAIL OPTIONS:
A = .135 ±.010 [3.43 ±.25] SOLDER TO BOARD
B = .090 +.005 / -.010 [2.29 +0.13 / -.25]
SOLDER TO BOARD
C = .154 ±.010 [3.91 ±.25] PRESS-FIT TO BOARD
- ⑧ RETENTION TO PCB OPTIONS:
A = BOARD LOCK (REQUIRES .098 +.002/-.001 [2.49 +0.05/-0.03] THRU HOLE IN PCB
MOUNTING FOOT HEIGHT: .220 [5.59]
NOT AVAILABLE FOR PRESS-FIT

B = .150 [3.81] THRU HOLE (REQUIRES .158 ±0.003 [4.01 ±0.08] THRU HOLE IN PCB).
MOUNTING FOOT HEIGHT
.160 [4.06]

- ⑨ **ALWAYS AVAILABLE FOR PRESS-FIT**
MANUFACTURE'S NAME, P/N, AND DATE CODE
TO APPEAR ON THIS SURFACE.
- ⑩ THE MAXIMUM OVERALL LENGTH (DIM A) OF A PART
IS 8.00 [203.2]
11. PRODUCT SPECIFICATION GS-12-149
12. APPLICATION SPECIFICATION BUS-20-067.
13. FOR PRESS-FIT CONNECTORS USE FCI CAM TOOL 430140-XXX
TO APPLY CONNECTOR TO PCB.

PCB NOTES:

14. ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.
15. ALL THROUGH HOLES ARE LOCATED WITH A
TRUE POSITION OF .004 [0.10]
16. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- ⑪ $\varnothing 0.0453 \pm .001$ [1.151 ±0.02] DRILLED HOLES PLATED WITH
0.0003 [0.007] MIN SnPb OVER 0.001 [1.03] TO .003 [0.08]
PLATING TO ACHIEVE A .040 ±.003 [1.02 ±0.08] HOLE.
18. Δ THE VOID CORING IN BETWEEN POWER MODULES, SIGNAL MODULES
AND END MODULES ARE OPTIONAL AND THE SHAPE MAY BE DIFFERENT
FOR OPTIMIZING THE MOLDING PROCESS. THE VOID CORING WILL NOT
EFFECT TO PRODUCT FUNCTION.
19. Δ A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.





surface	linear	0.X	±0.3
		0.XX	±0.13
		0.XXX	±0.051
ISO 1302	angular	0°	±2°


dr	Julia Wang	2008/09/29
eng	Vicking Liu	2017/03/07
chr	Fancy Zhang	2017/03/07
appr	Pei-Ming Zheng	2017/03/08

projection	size	scale
	A4	1:2
product family	ecn no	ELX-DG-26294-1
PwrBlade	rel level	Released

Amphenol FCI	title	RA REC w/GUIDE PIN POWER / SIGNAL / POWER	dwg no	51760	rev	N
	cat. no.	-	Product - Customer Drw		sheet 2 of 3	

PRODUCT NUMBER
51760-ABBCCDEF_... NOTE: ③
SEE NOTE 1



dr	Julia Wang	2008/09/29	projection 	MM 	size	A4	scale	1:1	
eng	Vicking Liu	2017/03/07			ecn no				ELX-DG-26294-1
chr	Fancy Zhang	2017/03/07			rel level				Released
appr	Pei-Ming Zheng	2017/03/08	product family		PwrBlade				
Amphenol FCI			title		RA REC w/GUIDE PIN		rev		
			POWER / SIGNAL / POWER		dwg no		51760		
			cat. no.		-		Product - Customer Drw		
							sheet 3 of 3		