




PRODUCT NUMBER
88952-XY
88952-XYLF



PLATING IN CONTACT AREA		
DASH NUMBER	PERFORMANCE LEVEL	NOTES
-NIYY	TELCORDIA CO (NXT)	-
-IYY	TELCORDIA CO	-
-2YY	TELECOM CLASS	-
-3YY	IEC CLASS I	-
-5YY	TELCORDIA UE	-
-NIYYLF	TELCORDIA CO IEC CLASS I	SEE NOTE 8
-IYYLF	TELCORDIA CO	SEE NOTE 8
-2YYLF	TELECOM CLASS	SEE NOTE 8
-5YYLF	TELCORDIA UE	SEE NOTE 8

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCJ	
ltr	ecn no.	dr	date	linear	0.X ±0.3	COPY	projection	title	www.fciconnect.com
T	V06-0569	DCH2	06-06-13	linear	0.XX ±0.13			METRAL SIGNAL HEADER	
U	DG09-0256	TER	2009-08-19	linear	.XXX ±.051			2 MOD. 4 ROW STB	
-	-	-	-	angles	0° ±2°				
N	V21670	TAB	07/18/02	dr	T.BRUNGARD	11/19/99		product family	METRAL
P	V03-1059	DAI	09/24/03	enr	M.STRAWER	11/19/99		code	213
R	V05-0193	LP	04/08/05	chr	M.STRAWER	11/19/99		size	dwg no
S	V06-0123	DAI	02/09/06	appd	M.STRAWER	02/29/00		88952	1 of 6
sheet index	revision	U	U	U	U	U	U		
	sheet	1	2	3	4	5	6		


This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCJ. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCJ. Copyright FCJ.



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE

SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY (SIGNAL STB)		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.25
2	5.75	4.25
3	6.50	4.25
4	7.25	4.25
5	5.00	3.30
6	5.75	3.30
7	6.50	3.30
8	7.25	3.30
9	5.00	2.65
10	5.75	2.65
11	6.50	2.65
12	7.25	2.65
13	8.00	4.25

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0. X $\pm$ 0.3		COPY			title METRAL SIGNAL HEADER 2 MOD. 4 ROW STB	
U					0. XX $\pm$ 0.13						
					. XXX $\pm$.051						
				angles	0° $\pm$ 2°						
				dr	T.BRUNGARD	11/19/99			product family		code
				engr	M. STRAWSER	11/19/99			size	dwg no	213
				chr	M. STRAWSER	11/19/99	scale		A	88952	sheet
				appd	M. STRAWSER	02/29/00	1:1				2
sheet index	revision sheet										

cage code 22526

Pro/E

PDM: Rev:U

STATUS: Released

Printed: Nov 30, 2009



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X01 SEE NOTE 9 LEAD FREE OPTION	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X06 SEE NOTE 9 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X11 SEE NOTE 9 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	1	1	1	1	1	1	1	1	1	1
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X02 SEE NOTE 9 LEAD FREE OPTION	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X07 SEE NOTE 9 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X12 SEE NOTE 9 LEAD FREE OPTION	D	4	4	4	4	4	4	4	4	4	4
	C	3	3	3	3	3	3	3	3	3	3
	B	2	2	2	2	2	2	2	2	2	2
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X03 SEE NOTE 9 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X08 SEE NOTE 9 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X13 SEE NOTE 9 LEAD FREE OPTION	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1
	B	3	3	3	3	3	3	3	3	3	3
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X04 SEE NOTE 9 LEAD FREE OPTION	D	4	4	4	4	4	4	4	4	4	4
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X09 SEE NOTE 9 LEAD FREE OPTION	D	4	4	4	4	4	4	4	4	4	4
	C	4	4	4	4	4	4	4	4	4	4
	B	4	4	4	4	4	4	4	4	4	4
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X15 SEE NOTE 9 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	1	1	1	1	1	1	1	1	1	1
	B	2	2	2	2	2	2	2	2	2	2
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X05 SEE NOTE 9 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X10 SEE NOTE 9 LEAD FREE OPTION	D	1	1	1	1	1	1	1	1	1	1
	C	2	2	2	2	2	2	2	2	2	2
	B	3	3	3	3	3	3	3	3	3	3
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X16 SEE NOTE 9 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	3	3	3	3	3	3	3	3	3	3
	B	4	4	4	4	4	4	4	4	4	4
	A	3	3	3	3	3	3	3	3	3	3

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3			projection		title METRAL SIGNAL HEADER 2 MOD. 4 ROW STB	
U					0.XX ±0.13						
					.XXX ±.051						
				angles	0° ±2°				product family METRAL	code 213	
				dr	T.BRUNGARD	11/19/99					
				enrg	M.STRAWSE	11/19/99					
				chr	M.STRAWSE	11/19/99					
				appd	M.STRAWSE	02/29/00	scale		1:1	size A	sheet 3
sheet	revision										
index	sheet										

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
88952-X17 SEE NOTE 9 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	3	3	3	3	3	3	3	3	3	3	3	3

[illegible][illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
88952-X33 SEE NOTE 9 LEAD FREE OPTION	D	7	7	7	7	7	7	7	7	7	7	7	7
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	7	7	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
88952- X34 SEE NOTE 9 LEAD FREE OPTION	D	8	8	8	8	8	8	8	8	8	8	8	8
	C	7	7	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7	7	7
	A	8	8	8	8	8	8	8	8	8	8	8	8

[illegible][illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
88952-X37 SEE NOTE 9 LEAD FREE OPTION	D	7	7	7	7	7	7	7	7	7	7	7	7
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	5	5	5	5	5	5	5	5	5	5	5	5

[illegible][illegible][illegible][illegible][illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
88952-X43 SEE NOTE 9 LEAD FREE OPTION	D	5	5	5	5	5	5	5	5	5	5	5	5
	C	5	5	5	5	5	5	5	5	5	5	5	5
	B	7	7	7	7	7	7	7	7	7	7	7	7
	A	5	5	5	5	5	5	5	5	5	5	5	5

[illegible][illegible]



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X46 SEE NOTE 9 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	7	7	7	7	7	7	7	7	7	7
	B	8	8	8	8	8	8	8	8	8	8
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X47 SEE NOTE 9 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X61 SEE NOTE 9 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	9	9	9	9	9	9	9	9	9	9
	B	9	9	9	9	9	9	9	9	9	9
	A	9	9	9	9	9	9	9	9	9	9

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X62 SEE NOTE 9 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	9	9	9	9	9	9	9	9	9	9
	B	9	9	9	9	9	9	9	9	9	9
	A	11	11	11	11	11	11	11	11	11	11

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X63 SEE NOTE 9 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	11	11	11	11	11	11	11	11	11	11

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X64 SEE NOTE 9 LEAD FREE OPTION	D	12	12	12	12	12	12	12	12	12	12
	C	11	11	11	11	11	11	11	11	11	11
	B	11	11	11	11	11	11	11	11	11	11
	A	12	12	12	12	12	12	12	12	12	12

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X65 SEE NOTE 9 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	11	11	11	11	11	11	11	11	11	11
	B	11	11	11	11	11	11	11	11	11	11
	A	11	11	11	11	11	11	11	11	11	11

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X66 SEE NOTE 9 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	10	10	10	10	10	10	10	10	10	10

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X67 SEE NOTE 9 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	9	9	9	9	9	9	9	9	9	9

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X68 SEE NOTE 9 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	9	9	9	9	9	9	9	9	9	9
	B	9	9	9	9	9	9	9	9	9	9
	A	9	9	9	9	9	9	9	9	9	9

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X69 SEE NOTE 9 LEAD FREE OPTION	D	12	12	12	12	12	12	12	12	12	12
	C	12	12	12	12	12	12	12	12	12	12
	B	12	12	12	12	12	12	12	12	12	12
	A	12	12	12	12	12	12	12	12	12	12

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X70 SEE NOTE 9 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	10	10	10	10	10	10	10	10	10	10
	B	11	11	11	11	11	11	11	11	11	11
	A	12	12	12	12	12	12	12	12	12	12

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X71 SEE NOTE 9 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	9	9	9	9	9	9	9	9	9	9
	B	11	11	11	11	11	11	11	11	11	11
	A	11	11	11	11	11	11	11	11	11	11

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X72 SEE NOTE 9 LEAD FREE OPTION	D	12	12	12	12	12	12	12	12	12	12
	C	11	11	11	11	11	11	11	11	11	11
	B	10	10	10	10	10	10	10	10	10	10
	A	9	9	9	9	9	9	9	9	9	9

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X73 SEE NOTE 9 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	9	9	9	9	9	9	9	9	9	9
	B	11	11	11	11	11	11	11	11	11	11
	A	9	9	9	9	9	9	9	9	9	9

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCJ www.fcjconnect.com		
lfr	ecn no.	dr	date	linear	0.X ±0.3			projection		title METRAL SIGNAL HEADER 2 MOD. 4 ROW STB		
U					0.XX ±0.13							
					.XXX ±.051							
				angles	0° ±2°			 scale 1:1	product family METRAL		code 213	
				dr	T.BRUNGARD	11/19/99						
				enr	M.STRAWSE	11/19/99						
				chr	M.STRAWSE	11/19/99						
				appd	M.STRAWSE	02/29/00						
sheet	revision									size 88952		sheet 5
index	sheet											



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X75 SEE NOTE 9 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	9	9	9	9	9	9	9	9	9	9
	B	10	10	10	10	10	10	10	10	10	10
	A	9	9	9	9	9	9	9	9	9	9

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X80 SEE NOTE 9 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	4	4	4	4	4	4	4	4	4	4
	B	13	13	13	13	13	13	13	13	13	13
	A	13	13	13	13	13	13	13	13	13	13

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X81 SEE NOTE 9 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	13	13	13	13	13	13	13	13	13	13
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X82 SEE NOTE 9 LEAD FREE OPTION	D	13	13	13	13	13	13	13	13	13	13
	C	13	13	13	13	13	13	13	13	13	13
	B	13	13	13	13	13	13	13	13	13	13
	A	13	13	13	13	13	13	13	13	13	13

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X83 SEE NOTE 9 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10
	B	11	11	11	11	11	11	11	11	11	11
	A	10	10	10	10	10	10	10	10	10	10

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
88952-X84 SEE NOTE 9 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	8	8	8	8	8	8	8	8	8	8
	A	6	6	6	6	6	6	6	6	6	6

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON SOLDER TO BOARD:
88952 -XXX IS SnPb
88952-XXYLF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXPLF
- PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-074
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.
- FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.
EXAMPLE: 88952-X0ILF
- ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI www.fciconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
U				angles	0.XX ±0.13					METRAL SIGNAL HEADER 2 MOD. 4 ROW STB	
					.XXX ±.051					product family	
				dr	0° ±2°					METRAL	
				enrg	T.BRUNGARD 11/19/99			MM		code	
				chr	M.STRAWSE 11/19/99			scale		213	
				appd	M.STRAWSE 02/29/00			1:1		sheet	
sheet		revision								6	
index		sheet									