



LOC	DIST	P	F	REVISIONS						
				ZONE	LTR	DESCRIPTION			DATE	APPD
AA	22				A	REV; EC 0210-0791-95			06MAY96	DS
										JT



- 1 MATERIALS:
HOUSING-PCT POLYESTER, BLACK, IR
REFLOW COMPATIBLE, UL 94V-0.
TERMINALS 0.33 [.013] THICK PHOS
BRONZE PLATED WITH 1.27μm [.000050]
HARD GOLD IN LOCALIZED AREA AND 3.81μm
[.000150] THICK TIN-LEAD IN SOLDER
AREA OVER 1.27μm [.000050] MINIMUM
THICK NICKEL UNDERPLATE.
SHIELD-0.25 [.010] THICK COPPER ALLOY
PLATED WITH 2.03μm [.000080] MINIMUM
TIN-LEAD OVER 2.54μm [.000100] MINIMUM
COPPER.
- 2 JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS,PART 68 SUBPART F.
3. DIMENSIONS ARE NOMINAL UNLESS OTHER-
WISE SPECIFIED.



SUGGESTED PC BOARD LAYOUT
VIEW SHOWN IS TOP (COMPONENT SIDE) OF PC BOARD

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

					PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± 0.13 [.005] ANGLES ± - MATERIAL 1		DR 7-21-93 S.MAYBERRY		AMP AMP Incorporated Harrisburg, PA 17105-3608		
		CHK 8-3-93 B.FOX				
		APPD 8-3-93 G.REED		NAME MODULAR JACK ASSEMBLY,10 POSITION, KEYED,SIDE ENTRY,LOW PROFILE, FULLY SHIELDED,PRINTED CIRCUIT GROUND		
		APPD 8-3-93 M.MILLER				
		PRODUCT SPEC -				
FINISH 1		APPLICATION SPEC -		SIZE C	CAGE CODE 00779	DRAWING NO C=558068
		WEIGHT -		SCALE 4:1		SHEET 1 OF 1